

TA-UC-PDQC65-01-W

3-port 65 W GaN USB PowerDelivery fast charger, white

- 65 W of power for your smartphone or laptop
- Type-C port or standard USB port for fast charging most smartphones
- Supports both USB PD and QC 3.0 fast charging protocol
- GaN technology enables a more compact energy efficient design



Features

- 3-port 65 W USB fast charger: supports both QC 3.0 and PowerDelivery (PD) specification
- GaN technology: compact design and increased energy efficiency
- Type-C ports support 65 W PD, Type-A port supports 27 W QC 3.0
- Intelligent over-current, over-voltage, short circuit and overheat protection

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

96
0.078
16.55
40x90x120 mm
550x460x310 mm
CN
8716309128674
8504408390

Certificates



Specifications

Input voltage: 100 V 240 V ~, up to 1.5 A (Max. 360 W)

Standby power consumption: <0.3W

USB-C1/C2 output: 5 V / 3 A, 9 V / 3 A, 12 V / 3 A, 15 V / 3 A, 20 V / 3.25 A

USB-A output: 5 V / 3 A, 9 V / 3 A, 12 V / 2.25 A

USB-C1+USB-C2 output: 45 W (5 V / 3 A, 9 V / 3 A, 12 V / 3 A, 15 V / 3 A, 20 V / 2.25 A) +20 W (5 V / 3 A, 9 V / 2.22 A, 12 V / 1.67 A, 15 V / 1.33 A, 20 V / 1 A), 65 W total max.

USB-C1+USB-A: 45 W (5 V / 3 A, 9 V / 3 A, 12 V / 3 A, 15 V / 3 A, 20 V / 2.25 A) +18 W (5 V / 3 A, 9 V / 2 A, 12 V / 1.5 A), 63 W total max.

USB-C2+USB-A: 5V / 4.8 A, 24 W max.

USB-C1+(USB-C2+USB-A): 45 W (5 V / 3 A, 9 V / 3 A, 12 V / 3 A, 15 V / 3 A, 20 V / 2.25 A) + 15 W (5 V / 3 A), 60 W total max.

Output protection: short circuit, over-voltage, overcharge, overheat

Dimensions: 39 mm x 106 mm x 34 mm

Net weight: 124 g

System requirements

NOTE: If both ports are used simultaneously, total output is limited to: 5V/2A
iPhone fast charging is only supported on iPhone 8 or newer