




N = Number of poles
Dim L=(N-1)x7.0+5.0
Dim P=(N-1)x7.0

	Dim L	Dim P
2p-4p	±0.20	
6p-8p	±0.30	
10p-12p	±0.40	

SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

- Material:
- Item ① Insulator(lever): Thermoplastic (UL94V-0)
 - Item ② Insulator(housing): Thermoplastic (UL94V-0)
 - Item ③ Side contact pin: PhBz.Tin plated.
 - Item ④ Center contact pin: PhBz.Tin plated.
 - Item ⑤ Side Cover : Thermoplastic (UL94V-0)
 - Item ⑥ Insulator(Board): Thermoplastic (UL94V-0)

- Electrical:
- | | |
|-------|-----|
| cULus | VDE |
|-------|-----|
- Voltage rating: 300V 250V
 - Current rating: 6A 6A
 - Wire range: 0.5-0.75 mm²
 - Solid wire(AWG): 16-22
 - Stranded wire(AWG): 16-22
 - Wire strip length: 8.5-10.0mm
 - Withstanding Voltage: 1.6KV 2 KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 260°C ±5°C/5 Sec
 - Safety Approval:
 - Critical dimension:

HC xx 10 x 0 xxxx G RoHS compliant (lead<4%) In copper Alloy

NO of poles


02 2 poles	Body Color	0000 Standard @ Logo
04 4 poles	0 Black (RAL9005)	000A Standard ANY Logo
...	2 Red (RAL3001/D)	
12 12 poles	3 Orange(RAL2011/P)	Any special item by customer request,
	4 Yellow(RAL1018/A)	please contact sales department.
	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7004/P)	
	9 White(RAL1102)	
	C Multiple colors	

ANYTEK

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

CUSTOMER COPY

TITLE		HC - 7.0mm Series 变数P	
PART NO.	HCxx10x0xxxxG	DWG NO.	8HC0218
APPROVED	CHECKED	DESIGNED	DRAWN
		Da cheng 2013.12.28	Da cheng 2013.12.28
SHEET: 01/01		REV.: B	



N = Number of poles
Dim L=(N-1)x7.0+5.0
Dim P=(N-1)x7.0

	Dim L	Dim P
3p-5p	±0.20	
7p-9p	±0.30	
11p	±0.40	

SIGN	DATE	DESCRIPTION	APPROVER
△	01/26'07	The Soldering temperature from 245° to 250°	Aaron
△	01/26'07	Add "VDE" stipulation	Aaron
△	12/25'08	Add "TUV" stipulation	Tony
△	5/06'10	Electrical changed	Runner
△	6/03'10	Structure changed	Cheng Bo
△	12/25'10	How to order is changed	Runner
△	6/25'12	Plastic core material reduced	Guoxue
△	12/28'13	update the drawing	Da cheng

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY Y!!!

Material:

- Item ① Insulator(lever): Thermoplastic (UL94V-0)
- Item ② Insulator(housing): Thermoplastic (UL94V-0)
- Item ③ Side contact pin: PhBz.Tin plated.
- Item ④ Center contact pin: PhBz.Tin plated.
- Item ⑤ Side Cover : Thermoplastic (UL94V-0)
- Item ⑥ Insulator(Board): Thermoplastic (UL94V-0)

- △△△ Electrical: cULus VDE
- Voltage rating: 300V 250V
 - Current rating: 6A 6A
 - Wire range: 0.5-0.75 mm²
 - Solid wire(AWG): 16-22
 - Stranded wire(AWG): 16-22
 - Wire strip length: 8.5-10.0mm
 - Withstanding Voltage: 1.6KV 2 KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 260°C ±5°C/5 Sec
 - Safety Approval:
 - Critical dimension:

- HC xx 10 x 0 xxxx G
- △ NO of poles
 - 03 3 poles
 - 05 5 poles
 -
 - 11 11 poles
 - △ Body Color
 - 0 Black (RAL9005)
 - 2 Red (RAL3001/D)
 - 3 Orange(RAL2011/P)
 - 4 Yellow(RAL1018/A)
 - 5 Green(RAL6018/T)
 - 6 Blue (RAL5015/A)
 - 8 Grey(RAL7004/P)
 - 9 White(RAL1102)
 - C Multiple colors
 - RoHS compliant (lead<4%) In copper Alloy
 - 0000 Standard @ Logo
 - 000A Standard ANY Logo
 - Any special item by customer request, please contact sales department.

ANYTEK

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

CUSTOMER COPY

TITLE				HC - 7.0mm Series 單數P			
PART NO.		HCxx10x0xxxxG		DWG NO.		8HC0201	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
		Da cheng	Da cheng			X.	±0.50
		2013.12.28	2013.12.28			X.X	±0.30
						X.XX	±0.10
SHEET: 01/01				REV.: H		X°	±1°