




|                                                                                                                                                                                                                                                  |                                             |                                                                                                                             |                                       |                                                                                                                                                                       |                                                                             |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|---------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------|
| Da 0,5 a 3                                                                                                                                                                                                                                       | Oltre 3 fino a 6                            | Oltre 6 fino a 30                                                                                                           | Oltre 30 fino a 120                   | Oltre 120                                                                                                                                                             |                                                                             |
| ± 0,1                                                                                                                                                                                                                                            | ± 0,1                                       | ± 0,2                                                                                                                       | ± 0,3                                 | ± 0,5                                                                                                                                                                 |                                                                             |
| <div>RESERVED PROPERTY</div> <div>The present drawing cannot be reproduced or communicated to 3d parties, even partially, without the authorization of ITALTRONIC Srl. Italtronic reserves to protect its own rights according to the law.</div> |                                             | <div></div> <div>Dimension in mm</div> | <div>SHEET NR.</div> <div>1 / 1</div> | <div>DRAWING BY</div> <div></div> <div>Manual modification are not allowed</div> | <div>GENERAL TOLERANCE</div> <div>UNI EN 22768/1</div> <div>Media (m)</div> |
|                                                                                                                                                                                                                                                  |                                             | <div>Date:</div> <div>30/08/2011</div>                                                                                      | <div>Replace nr.</div>                |                                                                                                                                                                       |                                                                             |
| <div>Drawed:</div> <div>Mazzucato F.</div>                                                                                                                                                                                                       | <div>Checked:</div> <div>Mazzucato F.</div> | <div>Scale:</div>                                                                                                           |                                       |                                                                                                                                                                       |                                                                             |



UN PARTNER PER IL FUTURO

Denomination:




Coperchio Railbox Standard 10 mm






**ITALTRONIC S.R.L.**  
VIA AUSTRIA 25/D 35127  
PADOVA - ITALY  
[www.italtronic.com](http://www.italtronic.com)

Drawing nr.

**R-03489-00**








## KIT ASSEMBLY 45






|                                                                                                                                                            |                                                                                                                                                                                                   |                       |                                                                      |                          |                               |
|------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|----------------------------------------------------------------------|--------------------------|-------------------------------|
| General Tolerance UNI EN 22768/1 Media (m)                                                                                                                 |                                                                                                                                                                                                   |                       |                                                                      |                          | Sheet:                        |
| from 0.5 to 3<br>± 0.1                                                                                                                                     | from 3 to 6<br>± 0.1                                                                                                                                                                              | from 6 to 30<br>± 0.2 | from 30 to 120<br>± 0.3                                              | from 120 to 400<br>± 0.5 | 1                             |
| Scale:<br><br>1:1                                                                                                                                          | Drawed:<br><br>R.N.                                                                                                                                                                               | Checked:<br><br>R.N.  | Date:<br><br>07/06/2024                                              | Material:<br><br>PC/ABS  | Process:<br><br>INJECTION     |
| <br>Dimension in mm                                                   | The present drawing cannot be reproduced or communicated by parties, even partially, without the authorization of ITALTRONIC. ITALTRONIC reserves to protect its own rights according to the law. |                       | Derived from:                                                        | Weight:<br><br>25,31 gr  | Cod. Mold:<br><br>ST.10011022 |
| <br><b>italtronic</b><br>enclosures for electronics<br>italtronic.com |                                                                                                                                                                                                   |                       | Description:<br>BASE RAILBOX XT VERTICAL<br>BASE RAILBOX XT VERTICAL |                          |                               |
| Drawing nr.:                                                                                                                                               |                                                                                                                                                                                                   |                       | Rev.:                                                                |                          |                               |
| 2 110 00126                                                                                                                                                |                                                                                                                                                                                                   |                       | 01 A2                                                                |                          |                               |










KIT ASSEMBLY 22.5








KIT ASSEMBLY 45





| General Tolerance UNI EN 22768/1 Media (mm)                                                                                           |                                                                                                                                                                                                          |                       |                                                      |                          | Sheet:                |
|---------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|------------------------------------------------------|--------------------------|-----------------------|
| from 0.5 to 3<br>± 0.1                                                                                                                | from 3 to 6<br>± 0.1                                                                                                                                                                                     | from 6 to 30<br>± 0.2 | from 30 to 120<br>± 0.3                              | from 120 to 400<br>± 0.5 | 1                     |
| Scale:<br>2:1                                                                                                                         | Drawed:<br>R.N.                                                                                                                                                                                          | Checked:<br>R.N.      | Date:<br>05/11/2024                                  | Material:<br>PC/ABS      | Process:<br>INJECTION |
| <br>Dimension in mm                              | The present drawing cannot be reproduced or communicated to 3d parties, even partially, without the authorization of ITALTRONIC SpA. Italtronic reserves to protect its own rights according to the law. |                       | Derived from:                                        |                          | Weight:<br>1.34 gr    |
| <br>enclosures for electronics<br>italtronic.com |                                                                                                                                                                                                          |                       | Description:<br>GANCIO RAILBOX XT<br>HOOK RAILBOX XT |                          |                       |
| Drawing nr.:<br>2_110_00136                                                                                                           |                                                                                                                                                                                                          |                       |                                                      |                          | Rev.:<br>00           |
|                                                                                                                                       |                                                                                                                                                                                                          |                       |                                                      |                          | A3                    |




| General Tolerance UNI EN 22768/1 Media (m)                                                                                                                                               |                                                                                                                                                                                                                 |               |                |                 | Sheet:                                                                   |  |  |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|----------------|-----------------|--------------------------------------------------------------------------|--|--|
| from 0.5 to 3                                                                                                                                                                            | from 3 to 6                                                                                                                                                                                                     | from 6 to 30  | from 30 to 120 | from 120 to 400 | 1                                                                        |  |  |
| ± 0.1                                                                                                                                                                                    | ± 0.1                                                                                                                                                                                                           | ± 0.2         | ± 0.3          | ± 0.5           |                                                                          |  |  |
| Scale:                                                                                                                                                                                   | Drawn:                                                                                                                                                                                                          | Checked:      | Date:          | Material:       | Process:                                                                 |  |  |
| 1:1                                                                                                                                                                                      | M.S.                                                                                                                                                                                                            | R.N.          | 01/09/2023     | PC              | INJECTION                                                                |  |  |
| <br>Dimension in mm                                                                                   | <p>The present drawing cannot be reproduced or communicated to 3d parties, even partially, without the authorization of ITALTRONIC Srl. Italtronic reserves to protect its own rights according to the law.</p> | Replaces the: | Derived from:  | Weight:         | Cod. Mold:                                                               |  |  |
|                                                                                                                                                                                          |                                                                                                                                                                                                                 | R-00166-02    | --             | 3.01 gr         | ST.1009002                                                               |  |  |
| <div><div><b>italtronic</b></div><div>enclosures for electronics</div><div>italtronic.com</div></div> |                                                                                                                                                                                                                 |               |                |                 | Description:                                                             |  |  |
|                                                                                                                                                                                          |                                                                                                                                                                                                                 |               |                |                 | SPORTELLO FRONTALE RAILBOX 17 MM<br>FRONT HINGED TRANSPARENT PANEL 17 MM |  |  |
| Drawing nr.:                                                                                                                                                                             |                                                                                                                                                                                                                 |               |                |                 | Rev.:                                                                    |  |  |
| 2_110_00072                                                                                                                                                                              |                                                                                                                                                                                                                 |               |                |                 | 00                                                                       |  |  |
|                                                                                                                                                                                          |                                                                                                                                                                                                                 |               |                |                 | A4                                                                       |  |  |







| General Tolerance UNI EN 22768/1 Media (m)                                    |                      |                       |                         |                          | Sheet:      |
|-------------------------------------------------------------------------------|----------------------|-----------------------|-------------------------|--------------------------|-------------|
| from 0.5 to 3<br>± 0.1                                                        | from 3 to 6<br>± 0.1 | from 6 to 30<br>± 0.2 | from 30 to 120<br>± 0.3 | from 120 to 400<br>± 0.5 | 1           |
| Scale:                                                                        | Drawn:               | Checked:              | Date:                   | Material:                | Process:    |
| 1:1                                                                           | R.N.                 | R.N.                  | 12/06/2024              | PC/ABS                   | INJECTION   |
| Derived from:                                                                 |                      |                       |                         | Weight:                  | Cod. Mold:  |
|                                                                               |                      |                       |                         | 23.90 gr                 | ST.10001025 |
| Description:<br>DISTANZIALE RAILBOX XT VERTICAL<br>SPACER RAILBOX XT VERTICAL |                      |                       |                         |                          | Rev.:       |
| Drawing nr.:<br>2_110_00129                                                   |                      |                       |                         |                          | 00 A2       |




SECTION A-A






| General Tolerance UNI EN 22768/1 Media (m)                                                                                              |                                                                                                                                                                                                                 |                                                                                    |                         |                          | Sheet:                       |  |
|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------|--------------------------|------------------------------|--|
| from 0.5 to 3<br>± 0.1                                                                                                                  | from 3 to 6<br>± 0.1                                                                                                                                                                                            | from 6 to 30<br>± 0.2                                                              | from 30 to 120<br>± 0.3 | from 120 to 400<br>± 0.5 | 1                            |  |
| Scale:<br><br>1:1                                                                                                                       | Drawed:<br><br>M.S.                                                                                                                                                                                             | Checked:<br><br>R.N.                                                               | Date:<br><br>09/08/2023 | Material:<br><br>PC/ABS  |                              |  |
| <br>Dimension in mm                                  | <p>The present drawing cannot be reproduced or communicated to 3d parties, even partially, without the authorization of ITALTRONIC Srl. Italtronic reserves to protect its own rights according to the law.</p> | Replaces the:<br><br>R-00142-00                                                    | Derived from:<br><br>-- | Weight:<br><br>2.56 gr   | Cod. Mold:<br><br>ST.1009100 |  |
| <br>enclosures for electronics<br><br>italtronic.com |                                                                                                                                                                                                                 | Description:<br>PANNELLO INTERNO RAILBOX 17 MM CON SEDI LED<br>INTERNAL PANEL 17MM |                         |                          |                              |  |
|                                                                                                                                         |                                                                                                                                                                                                                 | Drawing nr.:<br><br>2_110_00043                                                    |                         |                          |                              |  |
|                                                                                                                                         |                                                                                                                                                                                                                 | Rev.:<br><br>00                                                                    |                         |                          |                              |  |
|                                                                                                                                         |                                                                                                                                                                                                                 | A4                                                                                 |                         |                          |                              |  |




### KIT ASSEMBLY 22.5



### KIT ASSEMBLY 45



| General Tolerance UNI EN 22768/1 Media (m)                                                                                            |                      |                       |                                                                                                           |                          | Sheet:                    |
|---------------------------------------------------------------------------------------------------------------------------------------|----------------------|-----------------------|-----------------------------------------------------------------------------------------------------------|--------------------------|---------------------------|
| from 0.5 to 3<br>± 0.1                                                                                                                | from 3 to 6<br>± 0.1 | from 6 to 30<br>± 0.2 | from 30 to 120<br>± 0.3                                                                                   | from 120 to 400<br>± 0.5 | 1                         |
| Scale:<br>2:1                                                                                                                         | Drawed:<br>R.N.      | Checked:<br>R.N.      | Date:<br>07/06/2024                                                                                       | Material:<br>PC/ABS      | Process:<br>INJECTION     |
| <br>Dimension in mm                              |                      | Derived from:         |                                                                                                           | Weight:<br>0.98 gr       | Cod. Mold:<br>ST.10001024 |
| <br>enclosures for electronics<br>italtronic.com |                      |                       | Description:<br>COPRIFESSURA FRATTURABILE RAILBOX XT VERTICAL<br>HOLE COVER RAILBOX XT VERTICAL BREAKABLE |                          |                           |
| Drawing nr.:<br>2_110_00128                                                                                                           |                      |                       |                                                                                                           |                          | Rev.:<br>00 A3            |