

SIGN	DATE	DESCRIPTION	APPROVER
△	03/29'12	Add is cULus	Chen Bo
△	03/29'12	The dimension C & D & E are added	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item a Terminal(housing): Thermoplastic (UL94V-0)
- Item b Terminal(cover): Thermoplastic (UL94V-0)
- Item c Male contact pin of short: Copper Tin plated
- Item d Male contact pin of long: Copper Tin plated

Electrical:

cULus

- Voltage rating: 300V
- Current rating: 12A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

- Safety Approval: 
- Critical dimension: 

KE xx 7 3 x 3 xxxx G

No. OF POLES

04: 2×2 POLES

06: 2×3 POLES

:

:

48: 2×24 POLES




RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark

COLOR

Any special item by
customer request.
please contact sales
department.

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)



SECTION

P=P


N = Number of poles
Dim L=N×5.0+2.8
Dim B=(N-1)×5.0
Dim C=(N-1)×5.0+5.4
Dim D=(N-1)×5.0+5.4
Dim E=(N-1)×5.0

Poles	Dim L	Dim B	Dim C	Dim D	Dim E
2×2-2×6p	±0.15	±0.15	+0.05 -0.05	+0.05 -0.05	±0.15
2×7-2×12p	±0.25	±0.25	+0.10 -0.05	+0.10 -0.05	±0.25
2×13-2×18p	±0.35	±0.35	+0.20 -0.05	+0.20 -0.05	±0.35
2×19-2×24p	±0.40	±0.40	+0.25 -0.10	+0.25 -0.10	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		KE 5.0mm With latch holder Series 2×2P-2×24P (90°-Right-angle) DIP type					
PART NO.	KExx73x3xxxxG			DWG NO.	8KE0105		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Chen Bo	Chen Bo			UNIT: mm	X. ±0.50
		04/14'12	04/14'12			SCALE: NONE	X.X ±0.30
SHEET: 01/01		REV.: C					X.XX ±0.10
							X° ±1°