




RoHS Compliant

Section P-P

Dim.A=(N-1)x3.81+14.20				
Dim.B=(N-1)x3.81				
Dim.C=(N-1)x3.81+4.60				
Poles	2P~6P	7P~12P	13P~18P	19P~24P
Dim.A	+/-0.20	+/-0.25	+/-0.30	+/-0.35
Dim.B	+/-0.15	+/-0.20	+/-0.25	+/-0.30
Dim.C	+/-0.20	+/-0.25	+/-0.30	+/-0.35

REV	SIGN	DATE	DESCRIPTION	APPROVER
C	△	02/29'12	The real product doesn't comply with the drawing, remove this step	Aaron
D	△	11/26-20	Add RoHS Compliant and Amphenol logo	Chen Bo
	△	11/26-20	Change the electrical specification	Chen Bo
	△	11/26-20	Add the cULus safety certification icon	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item② :Terminal housing:Thermoplastic (UL94 V-0)
- Item⑤ :With flange screw: Steel, Zinc plated, M2.5"+/-"

Electrical (Match with AO 3.81 series)

- Voltage rating: 300V
- Current rating: 7A
- Stranded wire:0.5~1.0mm² (18-20AWG)
- Withstanding Voltage: 1.6KV
- Safety Approval:
- Critical dimension: ▲

KI xx 30 x 2 xxxx G

No. of poles
02 2 CONTACTS
03 3 CONTACTS
... ..
24 24 CONTACTS

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

G RoHS compliant
(lead<4%)
In copper Alloy

0000:"@ "Logo (Standard)
000A:"ANYTEK"Logo
Any special item by
customer request,
please contact sales
department.



Amphenol ANYTEK				CUSTOMER COPY			
TITLE KI 3.81 Series 2P~24P Body (With flange & W/o high profile)				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
PART NO.	Klxx30x2xxxxG			DWG NO.	8KI0003		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Chen Bo 11/26-20	Chen Bo 11/26-20		UNIT: mm	X.	±0.5
					SCALE: NONE	X.X	±0.3
				SHEET: 01/01	REV.: D	X.XX	±0.1
						X°	±1°