





RoHS Compliant



N = Number of poles

Dim A=Nx5.08

Dim B=(N-1)x5.08



Dim. Poles	Dim A	Dim B
2-6p	±0.20	±0.20
7-12p	±0.25	±0.25
13-16p	±0.30	±0.30
17-24p	±0.40	±0.35

REV	SIGN	DATE	DESCRIPTION	APPROVER
C	△	10/27'09	Dim.A and Dim.B tolerance table changed.	Kind
D	△	2010.03.31	Add the 2p mark	Jacke
E	△	11/26-20	Add RoHS Compliant and Amphenol logo	Chen Bo
	△	11/26-20	Change the electrical specification	Chen Bo
	△	11/26-20	Add the cULus safety certification icon	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

Material:

- Terminal housing:Thermoplastic (UL94 V-0)

Electrical (Match with AO 5.08 series)

- Voltage rating: 300V
- Current rating: 8A
- Stranded wire: 0.5~1.0mm² (18-20AWG)
- Withstanding Voltage: 1.6KV
- Safety Approval:
- Critical dimension: ▲

KI xx 50 x 0 xxxx G

No. of poles
02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

G RoHS compliant
(lead<4%)
In copper Alloy

0000:"@ "Logo (Standard)
000A:"ANYTEK"Logo
Any special item by
customer request,
please contact sales
department.



Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		KI 5.08 SERIES (W/o flange)			
PART NO.	KIxx50x0xxxxG			DWG NO.	8KI0101
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Chen Bo 11/26-20	Chen Bo 11/26-20		Tolerance
					X. ±0.50
					X.X ±0.30
					X.XX ±0.10
					X° ±1°
SHEET: 01/01		REV.: E			