



RoHS Compliant



Dim.L = N x 5.08
Dim.B = (N-1) x 5.08
N= number of poles

poles	2P-6P	7P-12P	13P-18P	19P-24P
Dim.				
Dim.L	±0.15	±0.20	±0.30	±0.40

Rev.	DATE	DESCRIPTION	APPROVER
E	10/29-21	ECN202110013	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- (a) Terminal body(metal housing): Brass(CuZn),Tin plated
- (b) Terminal screw: Steel Zinc plating "-" slot type
- (c) Wire guard: Stainless steel
- (d) Insulator (housing):Thermoplastic (UL 94V-0)

Electrical cULus

- Voltage rating: 250VAC
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 14-22
- Stranded wire(AWG): 14-22
- Torque: 3.5Lb-In
- Screw: M3
- Wire strip length: 4-5mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Wave Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus
- Critical dimension: ▲
- Reference dimension: (×)The dimensions of pitch are just for reference, take the actual assembly result as a judgment when inserting the terminal block into the PCB hole.

TB xx 2 1 x x xxxx G

POLES

02 02 POLES
03 03 POLES
...
24 24 POLES

Color

0 Black (RAL9005)
1 Red (RAL3001/D)
2 Orange(RAL2011/P)
3 Yellow(RAL1018/A)
4 Green(RAL6018/T)
5 Blue (RAL5015/A)
6 Grey(RAL7035/D)
7 White(RAL1102)
C Green(RAL6018/U)

DIM A Length
0 4.4mm
1 3.8mm
2 3.5mm

RoHS compliant
(lead<4%)
In copper Alloy
0000:"@Logo (Standard)
000A:"ANYTEK"Logo
Any special item by
customer request,
please contact sales
department.

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TB 5.08 series 1-interlock “-”					
PART NO.	TBxx21xxxxxxG			DWG NO.	8TB0203		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Guoxue 2021.10.29	Guoxue 2021.10.29		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
							X.XX ±0.10
				SHEET: 01/01		REV.: E	X° ±1°