




N = Number of poles
Dim A=Nx5.08
Dim B=(N-1)x5.08

	Dim A	Dim B
2-6p	±0.15	±0.15
7-12p	±0.20	±0.20
13-18p	±0.30	±0.30
19-24p	±0.40	±0.40



SIGN	DATE	DESCRIPTION	APPROVER
△	11/28'06	Electrical changed	Tony
△	04/30'09	Add VDE Standard	Eris
△	04/30'09	The tolerance of dimension is changed	Eris
△	04/30'09	Temperature changed from -33'105°C to -40'115°C	Eris
△	09/14'09	Add chamfer	Aaron
△	09/22'11	Structure changed	ChenMing
△	06/25'13	update the drawing	Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item② Clamp: Brass,Ni plated
- Item⑤ Terminal screw: Steel Zinc plating "-" slot type.
- Item③ Wire guard solder pin: Brass, Tin plated
- Item④ Terminal housing: Thermoplastic (UL94V-0)

△ △ Electrical:	cULus/VDE
● Voltage rating:	300V/250V
● Current rating:	15A/10A
● Wire range:	0.34~4.0mm ²
● Solid wire(AWG):	12-24
● Stranded wire(AWG):	12-24
● Torque:	3.5 Lb-In / 0.4 N.m
● Screw:	M2.5
● Wire strip length:	6-7mm
● Withstanding Voltage:	1.6 KV/2 KV
△ ● Operating temperature:	-40°C to +115°C
△ ● Soldering temperature:	260°C±5°C/5 Sec
● Safety Approval:	cULus VDE
● Critical dimension:	

△ TG xx 51 x x B xxx G

No. of poles end
stackable design
02 2 POLES
03 3 POLES
...
24 24 POLES

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

Dim L
0 4.5mm
3 3.2mm

RoHS compliant
(lead<4%)
In copper Alloy

000:"@ "Logo (Standard)
00A:"ANYTEK"Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TG 5.08 Series 2P-24P Long Interlock type								
PART NO.	TGxx51xxBxxxG			DWG NO.	8TG0201				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Guoxue 2013.07.19	Guoxue 2013.07.19					UNIT: mm	X.
					SCALE: NONE	X.X	±0.30		
				SHEET: 01/01	REV: H	X.XX	±0.10		
						X°	±1°		