







P.C.B Layout



SECTION P-P

DIMENSION

Dim L	N×7.62
Dim B	(N-1)×7.62
Dim C	(N-1)×7.62

N=Number of contacts

Poles	Tolerance
2p-5p	±0.20
6p-12p	±0.30
13p-16p	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	12/10`13	change the electrical specification	Chen Bo
△	12/10`13	change the product number	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal(housing): Thermoplastic (UL 94 - V0)
- Item ② Contact pin: Copper, Tin plated

Electrical:

- Voltage rating:300V
- △1● Current rating:41A
- Withstanding Voltage:1.6 KV
- Operating temperature:-40°C to +115°C
- △1● Soldering temperature:260°C±5°C/5 Sec
- Safety Approval:
- Critical dimension:

△ VCxx00xCxxxxG

No. OF POLES
02: 2 POLES
...

16: 16 POLES

COLOR

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)

G RoHS compliant
(lead<4%)In copper Alloy
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VC 7.62 Series 2P-16P Close Right angle down (Three tail type)						
PART NO.	VCxx00xCxxxxG			DWG NO.	8VC0103		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Chen Bo 12/10`13	Chen Bo 12/10`13				
SHEET: 01/01				UNIT: mm	X. ±0.50		
REV.: C				SCALE: NONE	X.X ±0.30		
					X.XX ±0.10		
					X° ±1°		