


## RECOMMENDED PANEL MOUNTING

| PANEL THICKNESS | X ± 0.05    |
|-----------------|-------------|
| 0.75-1.25       | 29.6-29.7   |
| 1.25-2.00       | 30.1-30.2   |
| 2.00-3.00       | 30.45-30.55 |





## SWITCH FUNCTION

| POS. 1 | POS. 2 |
|--------|--------|
|        |        |
| ON     | OFF    |
| 1-1a   | OPEN   |



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4  
X.XX = ± 0.25
3. TERM. NOS. FOR REF. ONLY
- ▲ 4. RATING: 20A 125VAC, 16A 250VAC UL APPROVED
5. ELECTRICAL LIFE: OVER 10,000 CYCLES
6. MECHANICAL LIFE: OVER 30,000 CYCLES
7. CONTACT RESISTANCE: <20 mΩ (INITIAL)
8. DIELECTRIC STRENGTH: >1500V 1 min
9. INSULATION RESISTANCE: >1,000 mΩ @ 500V DC
- ▲ 10. LAMP VOLTAGE: 125VAC NEON
11. OPERATING TEMPERATURE: TERMINAL SIDE -20°C to 85°C  
ROCKER SIDE -20°C to 55°C
12. ▲ DENOTES CRITICAL PARAMETER



| REV | ECO NO     | DESCRIPTION                     | DATE     | BY | E-SWITCH®          |                |       |             | OBJECT ID |
|-----|------------|---------------------------------|----------|----|--------------------|----------------|-------|-------------|-----------|
| B   | ECO-100524 | REMOVE VDE/ENEC RATING AND LOGO | 02/03/22 | JS | TITLE R4JBLKRILFF1 |                |       |             | 000016428 |
|     |            |                                 |          |    | SCALE 1:1          | DATE 12/3/2015 | DR MW | DWG M041011 | REV B     |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED