




P.C.B. LAYOUT

[illegible]

SIGN	DATE	DESCRIPTION	APPROVER
	1/29/07	Soldering temperature changed from 245° to 250°	Tony
	2010.01.22	Add the tolerance table	Jacke
	2010.01.22	The demension is changed from 1.60mm to 1.10mm	Jacke
	2010.01.22	The demension is changed from 0.40mm to 0.20 ~ 0.30mm	Jacke
	2010.03.31	The material is changed from Brass to Copper	Jacke
	2010.03.31	The dimension is revised from 20.9mm to 28.0mm	Jacke
	2014.10.09	Add the colour code & update the drawing	Evan
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item a Short contact pin: Copper Tin plated
- Item b Long contact pin: Copper Tin plated
- Item c Terminal(housing): Thermoplastic (UL94 V-0)
- Item d Terminal(cover): Thermoplastic (UL94 V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C

- ▲ ▲ ● Soldering temperature: 260°C±5°C/5 Sec
 ● Safety Approval: us
 ● Critical dimension: 

VL xx 1 1 x 1 xxxx G

No. OF POLES

04: 2x2 POLES

48: 2x24 POLES

—G: RoHS compliant
(lead<4%)
In copper Alloy

— 0000: “@” Logo (Standard)

000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.

- △ 0 Black (RAL9005)
 2 Red (RAL3001/D)
 3 Orange(RAL2011/P)
 4 Yellow(RAL1018/A)
 5 Green(RAL6018/T)
 6 Blue (RAL5015/A)
 8 Grey(RAL7035/D)
 9 White(RAL1102)
 C Green(RAL6018/U)

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VL-3.5MM Double level 90° Series						
PART NO.	VLxx11x1xxxxG			DWG NO.	8VL0002		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Evan 2014.10.09	Evan 2014.10.09		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV: G	X.XX ±0.10	
						X° ±1°	