





RoHS Compliant



P.C.B LAYOUT (Top View)



MATERIALS ELECTRICAL
RATED VOLTAGE & CURRENT: 300 V, 15 A
WITHSTAND VOLTAGE: AC 2000 V/Min
INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
OPERATING TEMPERATURE RANGE: -40 °C ~ +115 °C
SCREW TORQUE VALUE: 5.2 Lb-In.
WIRE RANGE: 14 ~ 22 AWG
1) MOLDED PARTS: THERMOPLASTIC, UL 94 V-0 BLACK
2) TERMINAL: BRASS, 0.8t, Tin PLATED
3) TERMINAL SCREWS: STEEL, M3
Wave Soldering temperature: 260°C ± 5°C / 5 Sec
Critical dimension:
APPROVAL: cULus

PART No.: YK 303xx 0 x x 00G

NO. OF POLES
02: 2 POLES
03: 3 POLES
04: 4 POLES
20: 20 POLES

G: RoHS compliant (lead < 4%)
in copper alloy

MARK
0: "@" MAK
1: "ANY" MAK

TERMINAL & SCREW PLATED
0: TERMINAL & SCREW: G/F
1: TERMINAL: G/F, SCREW: Zinc
2: TERMINAL: Sn, SCREW: G/F
3: TERMINAL: Sn, SCREW: Zinc

DIM	TOL			
	2P-4P	5P-10P	11P-16P	17P-20P
Dim A	(N-1) × 7.62 + 9.54	± 0.20	± 0.30	± 0.40
Dim B	(N-1) × 7.62	± 0.20	± 0.30	± 0.40



Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-303 W/o Flange & W/o cover Series					
PART NO.	YK303xx0xx00G			DWG NO.	8YK0001-303		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Guoxue 2018.08.10	Guoxue 2018.08.10		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					REV.: E		X.XX ±0.10
				SHEET: 01/01		X° ±1°	