





RoHS Compliant



P.C.B LAYOUT(Top View)

N = Number of poles
Dim A=N×8.25+2.0
Dim B=(N-1)×8.25

	Dim A	Dim B
2P-3P	±0.30	±0.30



Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	2014.06.11	The first release	Guoxue
C	△	2018.02.02	Add the TUV	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY Y!!!

△ MATERIALS ELECTRICAL	cULus	TUV
RATED VOLTAGE & CURRENT:	300 V, 20 A	300V 32A
WITHSTAND VOLTAGE:	AC 2000 V/Min	
INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 500 V	
OPERATING TEMPERATURE RANG:	-40 °C ~ +115 °C /-40°C~+105°C	
SCREW TORQUE VALUE:	7 Lb-In. / 0.8N.m	
WIRE RANGE:	22 - 12 AWG / 0.34-4.0mm²	
1) MOLDED PARTS:	POLYIMIDE 66, UL 94 V-0 BLACK	
2) TERMINAL:	BRASS, 0.8t	
3) TERMINAL SCREWS:	STEEL, M3	
4) COVER MATERIAL:	PC	

△ APPROVAL: cULus △
Critical dimension: ▲

YK 402 xx 0 x x 00G

NO. OF POLES ————
02: 2 POLES
03: 3 POLES

——— G:RoHS compliant(lead<4%)
in copper alloy
MARK
0: "@" MARK
1: "ANY" MARK

——— TERMINAL & SCREW PLATED
0: TERMINAL & SCREW: G/F
1: TERMINAL: G/F, SCREW: Zinc
2: TERMINAL: Sn, SCREW: G/F
3: TERMINAL: Sn, SCREW: Zinc

Amphenol ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE	YK-402 W/O Flange & W/O Cover Series (2P-3P)						
PART NO.	YK402xx0xx00G			DWG NO.	8YK0009-402		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Guoxue 2018 02 01	Guoxue 2018.02.01	UNIT: mm SCALE: NONE SHEET: 01/01			X. ±0.50
							X.X ±0.30
							X.XX ±0.10
						REV.: C	X° ±1°

