


P.C. MOUNTING






CIRCUIT: SPDT

O.P. (MM)	P.T. (MM)
10.8±0.8	2.0 MAX.

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- ▲ 3. RATING: 3A @ 125 VAC UL
1.5A @ 250 VAC UL
- ▲ 4. OPERATING FORCE: 30 $\pm$ 10 GRAMS
5. OPERATING TEMP: -25°C TO 75°C
6. ELECTRICAL LIFE: 10,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES MIN.
8. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
9. DIELECTRIC STRENGTH: 500VAC - 1 MINUTE
10. ▲ DENOTES CRITICAL PARAMETER.
11. PACKAGED IN TRAYS, 120 PIECES PER TRAY.



REV	ECO NO	DESCRIPTION	DATE	BY	 OBJECT ID 000021326				
D	ECO-102030	PRINT UPDATE	07/03/23	JS					
					TITLE SS0750302F030P1A				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 4:1	DATE 6/24/2008	DR BLR	DWG Q971010	REV D