

Fully insulated push-on female connectors, NCI ... BPCV type

FEATURES & BENEFITS


- ☒ female push-on connector with long PVC insulating sleeve
- low-cost version for less demanding applications, without internal Cu sleeve
- ☒ insulating sleeve: enhances resistance to vibrations, mitigates short-circuit risk
- ☒ sleeve colours facilitate cross-section identification

LOGISTIC DATA

Quantity in package [pcs]	100
---------------------------	-----

MECHANICAL DATA

Insulation	polyvinyl chloride (PVC)
Material	brass
Surface	tin-plated
Operating temperature [°C]	-5 ÷ +60



Type	Index Ergom	Cross-section [mm²]	Insulation colour	Size	d	L ₁	L ₂	Weight [kg]
NCI 4,8-1/0,5 BPCV (100 PCS)	E10KN-03010400201	0,75÷1	red	4,8x0,5	1,7	20,5	6,5	0,08
NCI 4,8-1/0,8 BPCV (100 PCS)	E10KN-03010400301			4,8x0,8		22,0	7,2	0,1
NCI 6,3-1/0,8 BPCV (100 PCS)	E10KN-03010400601			6,3x0,8		20,0	6,5	0,08
NCI 4,8-2,5/0,5 BPCV (100 PCS)	E10KN-03010400401	1,5÷2,5	blue	4,8x0,5	2,3	22,0	7,2	0,12
NCI 4,8-2,5/0,8 BPCV (100 PCS)	E10KN-03010400501			4,8x0,8		24,0	7,2	0,15
NCI 6,3-2,5/0,8 BPCV (100 PCS)	E10KN-03010400701			6,3x0,8				
NCI 6,3-6/0,8 BPCV (100 PCS)	E10KN-03010400801	4÷6	yellow	6,3x0,8	3,4			