

Female push-on connectors, N type

FEATURES & BENEFITS



female push-on connector, as per DIN, with galvanic tin plating, for manual installation

LOGISTIC DATA


Quantity in package [pcs] 100

MECHANICAL DATA

Material brass
Surface tin-plated

NOTE!

Spoiled terminals, NT - on request



ERC

Type	Index Ergom	Cross-section [mm ²]	Size	s	L ₁	L ₂	a ₁	a ₂	w ₁	w ₂	Weight [kg]
N 2,8-0,5/0,5 (100 PCS)	E10KN-01010100150	0,2÷0,5	2,8 x 0,5	0,30	14,0	6,0	5,5	2,7	2,3	3,4	0,02
N 2,8-0,5/0,8 (100 PCS)	E10KN-01010100250		2,8 x 0,8								
N 2,8-1/0,5 (100 PCS)	E10KN-01010100350	0,5÷1	2,8 x 0,5	0,30	14,0	6,0	5,5	2,9	2,4	3,8	0,03
N 2,8-1/0,8 (100 PCS)	E10KN-01010100401		2,8 x 0,8								
N 4,8-1/0,5 (100 PCS)	E10KN-01010100501		4,8 x 0,5	0,35	15,6		6,0	3,4	3,1	4,5	0,05
N 4,8-1/0,8 (100 PCS)	E10KN-01010100600		4,8 x 0,8								
N 4,8-2,5/0,5 (100 PCS)	E10KN-01010100700	1,5÷2,5	4,8 x 0,5	0,35	15,6	6,0	6,0	3,4	3,8	5,2	0,06
N 4,8-2,5/0,8 (100 PCS)	E10KN-01010100800		4,8 x 0,8								
N 6,3-1/0,8 (100 PCS)	E10KN-01010100900	0,5÷1	6,3 x 0,8	0,40	19,2	7,4	8,8	4,7	3,0	4,5	0,08
N 6,3-2,5/0,8 (100 PCS)	E10KN-01010101000	1,5÷2,5	6,3 x 0,8	0,35	19,2	7,6	8,8	4,7	3,8	5,5	0,08
N 6,3-6/0,8 (100 PCS)	E10KN-01010101201	4÷6	6,3 x 0,8	0,40	19,2	7,4	8,8	4,7	5,4	6,0	0,09