


KNA Spade terminal

for multi-wire Cu cables



Without insulation
 Material: galvanically tinned copper
 Tubular part according to DIN 46234

Cross section [mm²]	For screw M	Symbol	s [mm]	d ₁ [mm]	d ₃ [mm]	l [mm]	a [mm]	r [mm]	Weight [g/pce]	Unit [pcs]	Crimping tools
0,5 ÷ 1	3	KNA 3-1	0,8	1,6	6	11	5	4,5	0,50	100	
	4	KNA 4-1			8	12		4,5	0,60		
	5	KNA 5-1			10	14		6,5	0,75		
	6	KNA 6-1 *			11	17		7,6	0,95		
1,5 ÷ 2,5	3	KNA 3-2,5	0,8	2,3	6	11	5	4,5	0,55	100	PR33 RA16 ETA66 PP8 PP19
	3,5	KNA 3,5-2,5			6	11		4,5	0,50		
	4	KNA 4-2,5-A *			6,8	12		4,5	0,69		
	4	KNA 4-2,5			8	12		4,5	0,65		
	5	KNA 5-2,5			10	14		6,5	0,90		
	6	KNA 6-2,5			11	16		7	1,00		
	8	KNA 8-2,5			14	17		10	1,20		
4 ÷ 6	4	KNA 4-6	1	3,6	8	14	6	4,5	1,40	100	PR33, RA16 ETA66 PP8, PP19
	5	KNA 5-6			10	15		6,5	1,60		
	6	KNA 6-6			11	16		7	1,70		
	8	KNA 8-6			14	19		10	2,20		
10	5	KNA 5-10	1,1	4,5	10	17	8	6,5	2,35	100	EPZC300, EPZ300, GZ300, HR300, PRZ240, G0300, HRZ300, GU120, HR100-U, PR240, R50, PP19, RA16
	6	KNA 6-10			11	17		7,5	2,30		
	8	KNA 8-10			14	19		10	2,80		

* – outside DIN standard