







Dimension A&B

DIM A	N/2×5.08
DIM B	(N/2-1)×5.08

N=Number of contacts

Poles	A&B Tolerance
2×2P-2×6P	±0.15
2×7P-2×12P	±0.25
2×13P-2×18P	±0.35
2×19P-2×24P	±0.40



SIGN	DATE	DESCRIPTION	APPROVER
△	01/18'07	Soldering temperature changed from 245° to 250°	Tason
△	01/18'07	Part NO is Changed	Tason
△	11/11'11	Structure changed	ChenMing
△	11/11'11	The dimension is changed from 0.5	ChenMing
△	11/11'11	The dimension is added	ChenMing
△	11/11'11	The dimension is changed from	ChenMing
△	11/11'11	The dimension is changed from 23.1	ChenMing
△	11/11'11	The dimension is changed from 12.8	ChenMing
1/26 CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Clamp : Brass ,Ni plated
- Item 3 Wire guard solder pin : Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- △ ● Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus
- Critical dimension:

△ YM xx 41 x 0 xxxx G

04 2x2 CONTACTS
06 2x3 CONTACTS
...
48 2x24 CONTACTS

0 Black
5 Green
6 Blue
8 Grey

0000:"@Logo (Standard) Pb < 40,000ppm
000A:"ANYTEK"Logo (RoHS)
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YM-5.08mm -L Series			
PART NO.	YMxx41x0xxxxG			DWG NO.	8YM0101
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
			ChenMing 2011.11.11		Tolerance
					X. ±0.50
					X.X ±0.30
					X.XX ±0.10
					X° ±1°
				SHEET: 01/01	REV.: E