

Servo cable | PUR | chainflex® CF270.UL.D



10 million
Double strokes guaranteed



10 x d
Bend radius, e-chain®



10m
Travel distance, e-chain®

- For medium duty applications
- PUR outer jacket
- Shielded
- Oil-resistant and coolant-resistant
- Notch-resistant
- Flame-retardant
- Hydrolysis and microbe-resistant
- PVC and halogen-free

Dynamic information

	Bend radius	e-chain® linear	minimum 10 x d
		flexible	minimum 8 x d
		fixed	minimum 5 x d
	Temperature	e-chain® linear	-25°C up to +80°C
		flexible	-40°C up to +80°C (following DIN EN 60811-504)
		fixed	-50°C up to +80°C (following DIN EN 50305)
	v max.	unsupported	10m/s
		gliding	2m/s
	a max.		50m/s²
	Travel distance		Unsupported travels and up to 10m for gliding applications, Class 2

Cable structure

	Conductor	Multi core: Stranded conductor in bending-resistant version consisting of bare copper wires (following DIN EN 60228). Single core: Conductor cable consisting of pre-leads (following DIN EN 60228).
	Core insulation	Multi core: Mechanically high-quality, especially low-capacitance XLPE mixture. Single core: Mechanically high-quality TPE mixture.
	Core structure	Power cores and control pair elements wound with a short pitch length around a high tensile strength centre element.
	Core identification	Power cores: Black cores with white numbers, one green-yellow core. 1. Core: U / L1 / C / L+ 2. Core: V / L2 3. Core: W / L3 / D / L- 1 control pair: Black cores with white numbers. 1. Control core: 4 2. Control core: 5 2 control pairs: Black cores with white numbers. 1. Control core: 5 2. Control core: 6 3. Control core: 7 4. Control core: 8
	Element shield	Bending-resistant braiding made of tinned copper wires.
	Intermediate layer	Foil taping over the outer layer.
	Overall shield	Bending-resistant braiding made of tinned copper wires. Coverage linear approx. 55%, optical approx. 80%
	Outer jacket	Low-adhesion, halogen-free, highly abrasion resistant PUR mixture, adapted to suit the requirements in e-chains® (following DIN EN 50363-10-2) Colour: Pastel orange (similar to RAL 2003)

Electrical information

	Nominal voltage	600/1,000V (following DIN VDE 0298-3) 1,000V (following UL)
	Testing voltage	4,000V (following DIN EN 50395)

Basic requirements
Travel distance
Oil resistance
Torsion

low	1	2	3	4	5	6	7	highest
unsupported	1	2	3	4	5	6	≥ 400m	
none	1	2	3	4	highest			
none	1	2	3	4	±360°			

Class 4.2.3.1

Properties and approvals

	UV resistance	Medium
	Oil resistance	Oil-resistant (following DIN EN 50363-10-2), Class 3
	Offshore	MUD-resistant following NEK 606 - status 2016
	Flame-retardant	According to IEC 60332-1-2, Cable Flame, VW-1, FT1, FT2 / Horizontal Flame
	Silicone-free	Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)
	Halogen-free	Following DIN EN 60754
	PFAS-free	Use of PFAS-free materials according to the content of the REACH directive and its rules for the production and processing of chemical substances
	UL verified	Certificate No. V293650: “igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year”
	UL/CSA AWM	See data sheet for details ► www.igus.eu/CF270ULD
	NFPA	Following NFPA 79-2018, chapter 12.9
	REACH	In accordance with regulation (EC) No. 1907/2006 (REACH)
	Lead-free	Following 2011/65/EC (RoHS-II/RoHS-III)
	Cleanroom	According to ISO Class 1. The outer jacket material of this series complies with CF77.UL.05.12.D - tested by IPA according to standard DIN EN ISO 14644-1
	DESINA	According to VDW, DESINA standardisation
	CE	Following 2014/35/EU

Guaranteed service life (details see page 28-29)

Double strokes*	5 million	7.5 million	10 million
Temperature, from/to [°C]	R min. [x d]	R min. [x d]	R min. [x d]
-25/-15	12.5	13.5	14.5
-15/+70	10	11	12
+70/+80	12.5	13.5	14.5

* Higher number of double strokes? Service life calculation online ► www.igus.eu/chainflexlife

Typical application areas



- For medium duty applications, Class 4
- Unsupported travels and up to 10m for gliding applications, Class 2
- Almost unlimited resistance to oil, Class 3
- No torsion, Class 1
- Indoor and outdoor applications without direct sun radiation
- Machining units/machine tools, low temperature applications



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



Servo cable | PUR | chainflex® CF270.UL.D

Class 4.2.3.1

Basic requirements
Travel distance
Oil resistance
Torsion

low	1	2	3	4	5	6	7	highest
unsupported	1	2	3	4	5	6	≥ 400m	
none	1	2	3	4	highest			
none	1	2	3	4	±360°			



Example image

Part No.	Number of cores and conductor nominal cross section [mm²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
1 control pair shielded				
CF270.UL.15.15.02.01.D	(4G1.5+(2x1.5)C)	11.5	146	190
CF270.UL.25.15.02.01.D	(4G2.5+(2x1.5)C)C	13.0	195	248
CF270.UL.40.15.02.01.D	(4G4.0+(2x1.5)C)C	15.0	260	328
CF270.UL.60.15.02.01.D	(4G6.0+(2x1.5)C)C	16.5	350	430
CF270.UL.100.15.02.01.D	(4G10+(2x1.5)C)C	19.0	541	624
CF270.UL.160.15.02.01.D	(4G16+(2x1.5)C)C	22.0	786	900
2 control pairs shielded				
CF270.UL.07.03.02.02.D	(4G0.75+2x(2x0.34)C)C	11.0	96	151
CF270.UL.10.07.02.02.D	(4G1.0+2x(2x0.75)C)	12.5	139	200
CF270.UL.15.07.02.02.D	(4G1.5+2x(2x0.75)C)C	12.5	162	210
CF270.UL.25.15.02.02.D	(4G2.5+2x(2x1.5)C)C	15.5	265	322
CF270.UL.40.15.02.02.D	(4G4.0+2x(2x1.5)C)C	16.5	322	403
CF270.UL.60.15.02.02.D	(4G6.0+2x(2x1.5)C)C	18.5	407	505
CF270.UL.100.15.02.02.D	(4G10+2x(2x1.5)C)C	21.0	604	703
CF270.UL.160.15.02.02.D	(4G16+2x(2x1.5)C)C	24.0	857	997
CF270.UL.250.15.02.02.D	(4G25+2x(2x1.5)C)C	27.5	1219	1422
without control pair				
CF270.UL.07.04.D	(4G0.75)C	8.0	47	81
CF270.UL.10.06.D	(6G1.0)C	9.5	87	133
CF270.UL.15.04.D	(4G1.5)C	9.0	78	116
CF270.UL.25.04.D	(4G2.5)C	10.5	129	173
CF270.UL.40.04.D	(4G4.0)C	12.5	193	255
CF270.UL.60.04.D	(4G6.0)C	14.5	297	356
CF270.UL.100.04.D	(4G10)C	17.0	495	551
CF270.UL.160.04.D	(4G16)C	20.5	755	819
CF270.UL.250.04.D	(4G25)C	25.0	1117	1256
CF270.UL.350.04.D	(4G35)C	28.0	1597	1696
Spindle cable/Single core				
CF270.UL.60.01.D	(1x6.0)C	7.5	72	95
CF270.UL.100.01.D	(1x10)C	8.5	114	145
CF270.UL.160.01.D	(1x16)C	9.5	178	209
CF270.UL.250.01.D	(1x25)C	11.0	269	304
CF270.UL.350.01.D	(1x35)C	13.0	374	419
CF270.UL.500.01.D	(1x50)C	15.0	525	579
CF270.UL.700.01.D	(1x70)C	17.0	751	804

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.
G = with green-yellow earth core x = without earth core

Order example: **CF270.UL.40.15.02.01.D** - to your desired length (0.5m steps)
CF270.UL.D chainflex® series .40 Code nominal cross section .15 Code nominal cross section signal pairs
.02 Identification pairs .01 Number of pairs

Order online ► www.igus.eu/CF270ULD


Delivery time 24hrs or today.
Delivery time means time until goods are shipped.



Cables available in the chainflex® CASE

Simple savings on delivery, storage space and re-ordering with the chainflex® CASE - ship'n store by igus®.

More on this on page 24/25 and online: www.igus.eu/cf-case



Linear robot with chainflex® servo and measuring system cables, short travel distance



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year

