

Control cable | PVC | chainflex® CF140.UL



10 million
Double strokes guaranteed



7.5 x d
Bend radius, e-chain®



50m
Travel distance, e-chain®

- For medium duty applications
- PVC outer jacket
- Shielded
- Flame-retardant

Dynamic information

	Bend radius	e-chain® linear	minimum 7.5 x d
		flexible	minimum 6 x d
		fixed	minimum 4 x d
	Temperature	e-chain® linear	+5°C up to +70°C
		flexible	-5°C up to +70°C (following DIN EN 60811-504)
		fixed	-15°C up to +70°C (following DIN EN 50305)
	v max.	unsupported	3m/s
		gliding	2m/s
	a max.		20m/s²
	Travel distance		Unsupported travels and up to 50m for gliding applications, Class 4

Cable structure

	Conductor	Finely stranded conductor consisting of bare copper wires (following DIN EN 60228).
	Core insulation	Mechanically high-quality TPE mixture.
	Core structure	Number of cores < 12: Cores wound in a layer with short pitch length. Number of cores ≥ 12: Cores wound in bundles which are then wound around a high tensile strength centre element, all with optimised short pitch lengths and directions. Especially low-torsion structure.
	Core identification	Cores < 0.5mm²: Colour code in accordance with DIN 47100. Cores ≥ 0.5mm²: Black cores with white numbers, one green-yellow core.
	Inner jacket	PVC mixture adapted to suit the requirements in e-chains®.
	Overall shield	Bending-resistant braiding made of tinned copper wires. Coverage linear approx. 55%, optical approx. 80%
	Outer jacket	Low-adhesion PVC mixture, adapted to suit the requirements in e-chains® (following DIN EN 50363-4-1). Colour: Silver-grey (similar to RAL 7001)
	CFRIP®	Strip cables faster: a tear strip is moulded into the inner jacket Video ► www.igus.eu/CFRIP

Electrical information

	Nominal voltage	300/500V (following DIN VDE 0298-3) 300V (following UL)
	Testing voltage	2,000V (following DIN EN 50395)

EPLAN download, configurators ► www.igus.eu/CF140UL

4-years guarantee ... more than 1,350 cable types from stock ... no cutting charges

Class 4.4.1.1

Properties and approvals

	Flame-retardant	According to IEC 60332-1-2, Cable Flame, VW-1, FT1, FT2 / Horizontal Flame
	Silicone-free	Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)
	PFAS-free	Use of PFAS-free materials according to the content of the REACH directive and its rules for the production and processing of chemical substances
	UL verified	Certificate No. V293650: “igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year”
	UL/CSA AWM	See data sheet for details ► www.igus.eu/CF140UL
	NFPA	Following NFPA 79-2018, chapter 12.9
	REACH	In accordance with regulation (EC) No. 1907/2006 (REACH)
	Lead-free	Following 2011/65/EC (RoHS-II/RoHS-III)
	Cleanroom	According to ISO Class 1. The outer jacket material of this series complies with CF130.15.07 - tested by IPA according to standard DIN EN ISO 14644-1
	CE	Following 2014/35/EU

Guaranteed service life (details see page 28-29)

Double strokes*	5 million		7.5 million		10 million	
	< 10m	≥ 10m	< 10m	≥ 10m	< 10m	≥ 10m
Temperature, from/to [°C]	R min. [x d]	R min. [x d]	R min. [x d]	R min. [x d]	R min. [x d]	R min. [x d]
+5/+15	10	12.5	11	13.5	12	14.5
+15/+60	7.5	10	8.5	11	9.5	12
+60/+70	10	12.5	11	13.5	12	14.5

* Higher number of double strokes? Service life calculation online ► www.igus.eu/chainflexlife

Typical application areas

- For medium duty applications, Class 4
- Unsupported travels and up to 50m for gliding applications, Class 4
- Without influence of oil, Class 1
- No torsion, Class 1
- Preferably indoor applications
- Wood/stone processing, packaging industry, feeding, handling, adjusting devices

Basic requirements
Travel distance
Oil resistance
Torsion

low	1	2	3	4	5	6	7	highest
unsupported	1	2	3	4	5	6	7	≥ 400m
none	1	2	3	4	highest			
none	1	2	3	4	±360°			



UL-verified chainflex® guarantee ... www.igus.eu/ul-verified

Control cable | PVC | chainflex® CF140.UL

Strip cables 50% faster with CFRIP® tear strip

igus® chainflex® CF140.UL

Example image

New

Part No.	Number of cores and conductor nominal cross section [mm²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF140.02.12.UL	(12x0.25)C	10.5	72	133
CF140.03.05.UL	(5x0.34)C	7.5	36	72
CF140.05.03.UL	(3G0.5)C	7.0	33	72
CF140.05.04.UL	(4G0.5)C	7.5	38	81
CF140.05.05.UL	(5G0.5)C	8.0	45	91
CF140.05.18.UL	(18G0.5)C	14.5	147	258
CF140.05.36.UL	(36G0.5)C	18.5	258	468
CF140.07.03.UL	(3G0.75)C	8.0	42	85
CF140.07.04.UL	(4G0.75)C	8.5	51	102
CF140.07.05.UL	(5G0.75)C	9.0	61	115
CF140.07.07.UL	(7G0.75)C	10.0	83	152
CF140.07.12.UL	(12G0.75)C	13.0	136	263
CF140.07.18.UL	(18G0.75)C	15.5	194	359
CF140.07.25.UL	(25G0.75)C	18.0	261	479
CF140.10.02.UL	(2x1.0)C	8.0	35	86
CF140.10.03.UL	(3G1.0)C	8.5	51	105
CF140.10.04.UL	(4G1.0)C	9.0	62	118
CF140.10.05.UL	(5G1.0)C	9.5	74	136
CF140.10.07.UL	(7G1.0)C	10.5	104	176
CF140.10.12.UL	(12G1.0)C	14.0	166	300
CF140.10.18.UL	(18G1.0)C	16.5	240	413
CF140.10.25.UL	(25G1.0)C	19.5	325	562
CF140.15.03.UL	(3G1.5)C	9.0	68	126
CF140.15.04.UL	(4G1.5)C	9.5	86	146
CF140.15.05.UL	(5G1.5)C	9.5	108	168
CF140.15.07.UL ¹⁷⁾	(7G1.5)C	11.5	144	226
CF140.15.12.UL	(12G1.5)C	16.0	233	387
CF140.15.18.UL	(18G1.5)C	19.0	346	463
CF140.15.25.UL	(25G1.5)C	22.5	464	737
CF140.15.36.UL	(36G1.5)C	26.5	663	1150
CF140.25.03.UL	(3G2.5)C	10.5	106	202
CF140.25.04.UL	(4G2.5)C	11.5	140	210


¹⁷⁾ When using the cables with "7G1.5mm²" and "7G2.5mm²" minimum bend radius must be 17.5xd with gliding travel distance ≥ 5m.

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.
G = with green-yellow earth core x = without earth core

Class 4.4.1.1

Basic requirements
Travel distance
Oil resistance
Torsion

low	1	2	3	4	5	6	7	highest
unsupported	1	2	3	4	5	6	≥ 400m	
none	1	2	3	4	highest			
none	1	2	3	4	±360°			



chainflex® CF140.UL in a feeder application. e-chain®: easychain®



Cables available in the chainflex® CASE

Simple savings on delivery, storage space and re-ordering with the chainflex® CASE - ship'n store by igus®.

More on this on page 24/25 and online: www.igus.eu/cf-case



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year