


Single-unit and dual-unit types suit a variety of controls



■ Typical Specifications



Items	Specifications
Total resistance tolerance	±20%
Maximum operating voltage	50V AC, 10V DC
Total rotational angle	300° ±5°
Rotational torque	2 to 25mN·m
Operating life	15,000 cycles
Operating temperature range	-10°C to +70°C

■ Product Line

Number of resistor elements	Control part orientation	Shaft type	Length of the shaft L ₁ (mm)	Center detent	Total resistance (k Ω)	Resistance taper	Minimum order unit (pcs.)		Products No.	Drawing No.			
							Japan	Export					
Single-unit	Horizontal	Flat	15	Without	10	1B	1,000	2,000	RK09L1120A5F	1			
				With					RK09L1120036				
			20	Without					RK09L1120A0Z				
				With					RK09L112003S				
	Vertical		15	Without					RK09L1140A5L	2			
				With					RK09L114001E				
			20	Without					RK09L1140A2U				
				With					RK09L114001T				
Dual-unit	Horizontal for tone		15	With		15A			RK09L122002H	3			
			25						RK09L122002L				
	Horizontal for vol.		15	Without					RK09L12B0A4S		4		
			25						RK09L12B0A1V				
	Vertical for tone		15	With					1B	RK09L1240015		4	
			20							RK09L1240019			
	Vertical for vol.		15	Without					15A	RK09L12D0A1W	4		
			20							RK09L12D0A1T			

■ Note

Other varieties are also available. Refer to "Other Specifications" (P.284).

■ Packing Specifications









Tray

Number of packages (pcs.)		Export package measurements (mm)
1 case /Japan	1 case /export packing	
1,000	2,000	479×369×181

Refer to P.284 for other specifications.
 Refer to P.284 for attached parts.
 Refer to P.285 for ordering products not listed.
 Refer to P.311 for soldering conditions.

■ Dimensions

Unit:mm

No.	Photo	Style	PC board mounting hole dimensions (Viewed from mounting side)															
1	Single-shaft, single-unit Horizontal RK09L1120 	<table><tr><td>L₁</td><td>15</td><td>20</td></tr><tr><td>L_B</td><td>5</td><td>7</td></tr><tr><td>ℓ₁</td><td>7</td><td>12</td></tr></table>  Shaft shown in full C.C.W position	L ₁	15	20	L _B	5	7	ℓ ₁	7	12							
L ₁	15	20																
L _B	5	7																
ℓ ₁	7	12																
2	Single-shaft, single-unit Vertical RK09L1140 	<table><tr><td>L₁</td><td>12.5</td><td>15</td><td>20</td><td>25</td></tr><tr><td>L_B</td><td>5</td><td>5</td><td>7</td><td>7</td></tr><tr><td>ℓ₁</td><td>7</td><td>7</td><td>12</td><td>12</td></tr></table>  Shaft shown in full C.C.W position	L ₁	12.5	15	20	25	L _B	5	5	7	7	ℓ ₁	7	7	12	12	
L ₁	12.5	15	20	25														
L _B	5	5	7	7														
ℓ ₁	7	7	12	12														
3	Single-shaft, dual-unit Horizontal RK09L1220 (For tone) RK09L12B0 (For vol.) 	<table><tr><td>L₁</td><td>15</td><td>25</td></tr><tr><td>L_B</td><td>5</td><td>7</td></tr><tr><td>ℓ₁</td><td>7</td><td>12</td></tr></table>  Shaft shown in full C.C.W position	L ₁	15	25	L _B	5	7	ℓ ₁	7	12							
L ₁	15	25																
L _B	5	7																
ℓ ₁	7	12																
4	Single-shaft, dual-unit Vertical RK09L1240 (For tone) RK09L12D0 (For vol.) 	<table><tr><td>L₁</td><td>15</td><td>20</td></tr><tr><td>L_B</td><td>5</td><td>7</td></tr><tr><td>ℓ₁</td><td>7</td><td>12</td></tr></table>  Shaft shown in full C.C.W position	L ₁	15	20	L _B	5	7	ℓ ₁	7	12							
L ₁	15	20																
L _B	5	7																
ℓ ₁	7	12																

Rotary
Potentiometers
Slide
Potentiometers

Metal Shaft

Insulated
ShaftKnob
OperatingThrough
Shaft Type

Ring Type

■ Dimensions of Bushing and Fixing Lug

Unit:mm



9mm Size Metal Shaft Snap-in Type / Other Specifications

In addition to the Product Line, we accommodate the following specifications. Combinations not included in the Product Line are treated as semi-standard products.

Total Resistance Variety



Total resistance (k Ω)	5	10	20	50	100
--------------------------------	---	----	----	----	-----

Resistance Taper

Resistance taper	15A	1B	3B	15C
------------------	-----	----	----	-----

Shaft Variety

Unit:mm



Detail dimensions

L ₁	L _B	l ₁
12.5	5	7
15	5	7
17.5	5	7
20	7	12
25	7	12

Note

Marked are specifications recommended by Alps Alpine.

9mm Size Metal Shaft Snap-in Type / Attached Parts

The following parts are included with the product.

Unit:mm

Nut	Washer

9mm Size Metal Shaft Snap-in Type / Ordering Products Not Listed

In addition to the Product Line, we accommodate the following specifications. Combinations not included in the Product Line are treated as semi-standard products. Please refer to the notation example below.

Sample Part Number

R K 0 9 L 1 1 4 0 — **F 1 5** — **C 0** — **B 1 0 3**

Model type

Code	Model type
112	Single-unit Horizontal
114	Single-unit Vertical
122	Dual-unit Horizontal for tone
124	Dual-unit Vertical for tone
12B	Dual-unit Horizontal for vol.
12D	Dual-unit Vertical for vol.

Shaft type

Code	Shaft type
F	Flat

* Only available in flat format.

Length of the shaft L₁ (mm)

Code	Length of the shaft	Code	Length of the shaft	Code	Length of the shaft
12	12.5	17	17.5	25	25
15	15	20	20	—	—

Detent



Code	Center detent
C0	Without
C1	With

Resistance taper

Code	Resistance taper	Code	Resistance taper
A	15A	V	3B
B	1B	C	15C

B: For tone & general (model type : 112, 114, 122, 124)

V: For vol. (model type : 112, 114, 12B, 12D)



Total resistance

Code	Total resistance (k Ω)	Code	Total resistance (k Ω)
502	5	503	50
103	10	104	100
203	20	—	—

Note

Marked are specifications recommended by Alps Alpine.

Metal Shaft Potentiometers

List of Varieties

Type		9mm size			
Series		RK09L		RK0971	RK0972
		Single-shaft			Dual-shaft
Number of resistor elements		Single/dual			Dual
Photo					
Control part orientation		Horizontal	Vertical	Horizontal	
Fixing method of bushing		Screw			
Operating temperature range		-10℃ to +70℃		-20℃ to +70℃ -40℃ to + 85℃ (Vehicle-compatible)	
Operating life		15,000 cycles			
Available for automotive use		—	—	○	○
Life cycle (availability)					
Electrical performance	Total resistance (k Ω)	10, 20, 50, 100			
	Resistance taper	15A, 1B, 3B, 15C			
	Rated Power	0.05W			
	Residual resistance	R≤10kΩ 20Ω max. 10kΩ<R≤50kΩ 30Ω max. 50kΩ<R Nominal total resistance of 0.1% or less			
	Maximum attenuation (Volume control)	5kΩ≤R< 10kΩ 70dB min. 10kΩ≤R< 50kΩ 80dB min. 50kΩ≤R 90dB min.		5kΩ≤R< 10kΩ 70dB min. 10kΩ≤R< 50kΩ 80dB min. 50kΩ≤R<100kΩ 90dB min. 100kΩ≤R 100dB min.	
	Gang error applicable to Dual-unit parts for audio volume control purposes	-40dB to 0dB 3dB max.			
	Insulation resistance	100MΩ min. 250V DC			
	Voltage proof	300V AC for 1 minute			
	Center-taps	Without		Without / With	
Mechanical performance	Detent	Without, Center			
	Stopper strength	0.5N·m		0.5N·m (With push-lock mechanism: 0.4N·m)	
	Push-pull strength	80N max.		100N max.	
	Vibration	10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z and for 2 hours respectively			
Shaft style		Flat type			Inner-shaft: flat type Outer-shaft: slotted type
Terminal style		Insertion			
Attached switch		—	—	Rotary switch Push-on switch Push-lock switch	—
Page		282		286	287

Metal Shaft Potentiometers Soldering Conditions	311
Potentiometers Cautions	384
Potentiometers Measurement and Test Methods	386
Potentiometers Resistance Taper	388

Notes

1. For the switch attached, the single-shaft or inner shaft of the dual-shaft type can be chosen.
2. The operating temperature range for automotive applications can be raised upon request. Please contact us for details.
3. ○ Indicates applicability to some products in the series.

Reference for Manual Soldering

Series		Tip temperature	Soldering time	No. of solders
RK09L, RK097		350°C max.	3s max.	1 time
RK271		350°C max.	5s max.	1 time
RK501		350±10°C	5 ⁺¹ ₀ s	1 time
RK163		350°C max.	5s max.	1 time
RK168	Potentiometer terminal	300°C max.	3s max.	1 time
	Motor terminal	350°C max.	2s max.	

Reference for Dip Soldering

Series	Preheating		Dip soldering		No. of solders
	Soldering surface temperature	Heating time	Soldering temperature	Soldering time	
RK09L, RK097	100°C max.	2 min. max.	260±5°C	5±1s	2 times max.
RK501	120±10°C	2 min. max.	260±5°C	5±1s	2 times