














Temperature Guide & Tip Specifications SSC-Series

Max Temperature	MFR & SP200 Series	Application
675°F/357°C	SSC-6	Temperature Sensitive
775°F/413°C	SSC-7	Most Standard
	Compatible with: SP200, MFR-1160 Systems, SP-HC1 and MFR-H6-SSC Handpieces	

Please note the above temperatures are the maximum temperatures of the heater. The idle temperature is dependent on the geometry of the cartridge (up to 15°C lower)

Chisel	MFR & SP200 Series	
	SSC-671A	Chisel, (W x L)
	SSC-771A	1.0 mm x 9.1 mm (0.04" x 0.36")
	SSC-625A	Chisel, (W x L) Cone 30°
	SSC-725A	1.0 mm x 11 mm (0.04" x 0.43")
	SSC-638A	Chisel (W x L) 30°
	SSC-738A	1.5 mm x 10 mm (0.06" x 0.40")
	SSC-637A	Chisel (W x L) 30°
	SSC-737A	1.78 mm x 9.9 mm (0.07" x 0.40")
	SSC-672A	Chisel, (W x L)
	SSC-772A	1.78 mm x 9.9 mm (0.07" x 0.39")
	SSC-636A	Chisel 30°, (W x L)
	SSC-736A	2.5 mm x 9.9 mm (0.10" x 0.39")
Conical	MFR & SP200 Series	
	SSC-645A	Conical, Sharp, Long Reach, (Ø x L),
	SSC-745A	0.4 mm x 19 mm (0.016" x 0.75")
	SSC-622A	Conical, Sharp, (Ø x L),
	SSC-722A	0.51 mm x 11.4 mm (0.02" x 0.45")
	SSC-626A	Conical, Sharp Bent 30°, (Ø x L),
	SSC-726A	0.51 mm x 11.4 mm (0.02" x 0.45")
	SSC-654A	Conical, Sharp Bent 30°, Long Reach, (Ø x L),
	SSC-754A	0.51 mm x 18.5 mm (0.02" x 0.73")
	SSC-601A	Conical, Sharp, (Ø x L),
	SSC-701A	1.0 mm x 15.2 mm (0.04" x 0.60")
Knife	MFR & SP200 Series	
	SSC-661A	Rework Knife Cartridge - For Multi-Lead
	SSC-761A	Soldering of PLCCs/SOJs, Bevel 45°, (W x L), 4.5 mm x 16.25 mm (0.18" x 0.64")
	SSC-673A	Rework Knife Cartridge - For Multi-Lead
	SSC-773A	Soldering of PLCCs/SOJs, Bevel 45°, Increased tinned area 6.1 mm, (W x L), 5.1 mm x 16.25 mm (0.24" x 0.64")

For our complete selection of tips & cartridges, visit www.metcal.com