

		8		7		6		5		4		3		2		1	

SL.NO	TCPN (\$PN)	TE Type (\$TYPE)	A (mm)	B (mm)	Safety level	Protected height (mm) (\$DHPH)	CO	Resolution (mm)	Max. Range (m)	Net weight (g)	\$WR	\$DC	\$RT	\$W T	\$NB	\$LP	\$PT	\$PC	\$PN	Models	\$CL1	\$CL2
131	1-2447904-5	SLC4-B50-151L	1563	1500	Type 4-PLe	1510	RESOLUTION	50	20	3069	0*10 / 3*20 m	≥ 0 50 mm	≤ 7 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	1-2447904-5/1-2447904-5	150x	TYPE 4	TYPE 4 - SIL 3 - PL e
132	1-2447904-6	SLC4-B50-166L	1713	1650	Type 4-PLe	1660	RESOLUTION	50	20	3349	0*10 / 3*20 m	≥ 0 50 mm	≤ 7 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	1-2447904-6/1-2447904-6	165x	TYPE 4	TYPE 4 - SIL 3 - PL e
133	1-2447904-8	SLC4-B50-181L	1863	1800	Type 4-PLe	1810	RESOLUTION	50	20	3569	0*10 / 3*20 m	≥ 0 50 mm	≤ 8 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	1-2447904-8/1-2447904-8	180x	TYPE 4	TYPE 4 - SIL 3 - PL e
134	1-2447904-9	SLC4-B50-196L	2013	1950	Type 4-PLe	1960	RESOLUTION	50	20	3829	0*10 / 3*20 m	≥ 0 50 mm	≤ 8 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	1-2447904-9/1-2447904-9	195x	TYPE 4	TYPE 4 - SIL 3 - PL e
135	2-2447904-1	SLC4-B50-211L	2163	2100	Type 4-PLe	2110	RESOLUTION	50	20	4049	0*10 / 3*20 m	≥ 0 50 mm	≤ 9 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	2-2447904-1/2-2447904-1	210x	TYPE 4	TYPE 4 - SIL 3 - PL e
136	2-2447904-2	SLC4-B50-226L	2313	2250	Type 4-PLe	2260	RESOLUTION	50	20	4349	0*10 / 3*20 m	≥ 0 50 mm	≤ 9 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	2-2447904-2/2-2447904-2	225x	TYPE 4	TYPE 4 - SIL 3 - PL e
137	2447905-3	SLC4-B90-031L	363	300	Type 4-PLe	310	RESOLUTION	90	20	849	0*10 / 3*20 m	≥ 0 90 mm	≤ 2,5 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	2447905-3/2447905-3	30x	TYPE 4	TYPE 4 - SIL 3 - PL e
138	2447905-4	SLC4-B90-046L	513	450	Type 4-PLe	460	RESOLUTION	90	20	1119	0*10 / 3*20 m	≥ 0 90 mm	≤ 3 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	2447905-4/2447905-4	45x	TYPE 4	TYPE 4 - SIL 3 - PL e
139	2447905-6	SLC4-B90-061L	663	600	Type 4-PLe	610	RESOLUTION	90	20	1409	0*10 / 3*20 m	≥ 0 90 mm	≤ 3 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	2447905-6/2447905-6	60x	TYPE 4	TYPE 4 - SIL 3 - PL e
140	2447905-7	SLC4-B90-076L	813	750	Type 4-PLe	760	RESOLUTION	90	20	1649	0*10 / 3*20 m	≥ 0 90 mm	≤ 3,5 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	2447905-7/2447905-7	75x	TYPE 4	TYPE 4 - SIL 3 - PL e
141	2447905-9	SLC4-B90-091L	963	900	Type 4-PLe	910	RESOLUTION	90	20	1889	0*10 / 3*20 m	≥ 0 90 mm	≤ 3,5 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	2447905-9/2447905-9	90x	TYPE 4	TYPE 4 - SIL 3 - PL e
142	1-2447905-0	SLC4-B90-106L	1113	1050	Type 4-PLe	1060	RESOLUTION	90	20	2189	0*10 / 3*20 m	≥ 0 90 mm	≤ 3,5 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	1-2447905-0/1-2447905-0	105x	TYPE 4	TYPE 4 - SIL 3 - PL e
143	1-2447905-2	SLC4-B90-121L	1263	1200	Type 4-PLe	1210	RESOLUTION	90	20	2509	0*10 / 3*20 m	≥ 0 90 mm	≤ 4 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	1-2447905-2/1-2447905-2	120x	TYPE 4	TYPE 4 - SIL 3 - PL e
144	1-2447905-3	SLC4-B90-136L	1413	1350	Type 4-PLe	1360	RESOLUTION	90	20	2789	0*10 / 3*20 m	≥ 0 90 mm	≤ 4 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	1-2447905-3/1-2447905-3	135x	TYPE 4	TYPE 4 - SIL 3 - PL e
145	1-2447905-5	SLC4-B90-151L	1563	1500	Type 4-PLe	1510	RESOLUTION	90	20	3069	0*10 / 3*20 m	≥ 0 90 mm	≤ 4,5 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	1-2447905-5/1-2447905-5	150x	TYPE 4	TYPE 4 - SIL 3 - PL e
146	1-2447905-6	SLC4-B90-166L	1713	1650	Type 4-PLe	1660	RESOLUTION	90	20	3349	0*10 / 3*20 m	≥ 0 90 mm	≤ 4,5 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	1-2447905-6/1-2447905-6	165x	TYPE 4	TYPE 4 - SIL 3 - PL e
147	1-2447905-8	SLC4-B90-181L	1863	1800	Type 4-PLe	1810	RESOLUTION	90	20	3569	0*10 / 3*20 m	≥ 0 90 mm	≤ 5 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	1-2447905-8/1-2447905-8	180x	TYPE 4	TYPE 4 - SIL 3 - PL e
148	1-2447905-9	SLC4-B90-196L	2013	1950	Type 4-PLe	1960	RESOLUTION	90	20	3829	0*10 / 3*20 m	≥ 0 90 mm	≤ 5,5 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	1-2447905-9/1-2447905-9	195x	TYPE 4	TYPE 4 - SIL 3 - PL e
149	2-2447905-1	SLC4-B90-211L	2163	2100	Type 4-PLe	2110	RESOLUTION	90	20	4049	0*10 / 3*20 m	≥ 0 90 mm	≤ 6 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	2-2447905-1/2-2447905-1	210x	TYPE 4	TYPE 4 - SIL 3 - PL e
150	2-2447905-2	SLC4-B90-226L	2313	2250	Type 4-PLe	2260	RESOLUTION	90	20	4349	0*10 / 3*20 m	≥ 0 90 mm	≤ 6 ms	-20+55 °C	-	-	EMITTER/RECEIVER	1W /2W	2-2447905-2/2-2447905-2	225x	TYPE 4	TYPE 4 - SIL 3 - PL e
151	2447906-5	SLC4-B2B-051L	653	590	Type 4-PLe	510	MULTIBEAM	2 Rays	20	1269	0*10 / 3*20 m	-	≤ 2,5 ms	-20+55 °C	2	500mm	EMITTER/RECEIVER	1W /2W	2447906-5/2447906-5	2B	TYPE 4	TYPE 4 - SIL 3 - PL e
152	2447906-8	SLC4-B3B-081L	953	890	Type 4-PLe	810	MULTIBEAM	3 Rays	20	1749	0*10 / 3*20 m	-	≤ 2,5 ms	-20+55 °C	3	400mm	EMITTER/RECEIVER	1W /2W	2447906-8/2447906-8	3B	TYPE 4	TYPE 4 - SIL 3 - PL e
153	2447906-9	SLC4-B4B-091L	963	900	Type 4-PLe	910	MULTIBEAM	4 Rays	20	1921	0*10 / 3*20 m	-	≤ 2,5 ms	-20+55 °C	4	300mm	EMITTER/RECEIVER	1W /2W	2447906-9/2447906-9	4B	TYPE 4	TYPE 4 - SIL 3 - PL e

MARKING SPECIFICATIONS

DATA TAB - RESOLUTION - EMITTER 01



\$TYPE

\$PT

\$PN

yywwnnnn

&WR

DETECTION CAPABILITY

PROTECTED HEIGHT

SYSTEM RESP.TIME

POWER CONSUMPTION

WORKING TEMPERATURE

\$DC

\$DHPH

\$RT

\$PC

\$WT

3

5

2

4

1

1: +24 VDC

2: SEL_RANGE_TEST0

3: 0 VDC

4: SEL_RANGE_TEST1

5: FE



MADE IN ITALY IP65 - IP67

DATA TAB - RESOLUTION - RECEIVER 01



\$TYPE

\$PT

\$PN

yywwnnnn

&WR

DETECTION CAPABILITY

PROTECTED HEIGHT

SYSTEM RESP.TIME

POWER CONSUMPTION

WORKING TEMPERATURE

\$DC

\$DHPH

\$RT

\$PC

\$WT

1

7

6

5

4

3

2

8

1: OSSD1

2: +24 VDC

3: OSSD2


4: K1_K2/RESTART

5: SEL_A

6: SEL_B

7: 0 VDC

8: FE



MADE IN ITALY IP65 - IP67

DATA TAB - MULTIBEAM - EMITTER 02



\$TYPE

\$PT

\$PN

yywwnnnn

&WR

NUMBER OF BEAMS

LENS PITCH

SYSTEM RESP.TIME

POWER CONSUMPTION

WORKING TEMPERATURE

\$NB

\$LP

\$RT

\$PC

\$WT

3

5

2

4

1

1: +24 VDC

2: SEL_RANGE_TEST0

3: 0 VDC

4: SEL_RANGE_TEST1

5: FE



MADE IN ITALY IP65 - IP67

DATA TAB - MULTIBEAM - RECEIVER 02



\$TYPE

\$PT

\$PN

yywwnnnn

&WR

NUMBER OF BEAMS

LENS PITCH

SYSTEM RESP.TIME

POWER CONSUMPTION

WORKING TEMPERATURE

\$NB

\$LP

\$RT

\$PC

\$WT

1

7

6

5

4

3

2

8

1: OSSD1

2: +24 VDC

3: OSSD2



4: K1_K2/RESTART

5: SEL_A

6: SEL_B

7: 0 VDC

8: FE




MADE IN ITALY IP65 - IP67




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL REVISION	05MAY2023	NG	RM
B		ADDED MARKING	18JUL2023	IS	RM

MARKING SPECIFICATIONS

LIGHT CURTAINS TRANSMITTER-Models with length 15x



LIGHT CURTAINS RECEIVER-Models with length 15x



LIGHT CURTAINS TRANSMITTER-Models with length >15x



LIGHT CURTAINS RECEIVER-Models with length >15x

Note:
1). Serial number compositioning (8 digits): yywwnnnn
- yy [year of manufacture]2 digits (last two digits)
- ww [week of manufacture]2 digits
- nnnn [ID code]4 digits hex

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Infan S	21APRIL2023	 TE Connectivity	
		CHK	Vishal G	21APRIL2023		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	Rafeeq Moid	21APRIL2023	NAME	SLC4-F14-016
		PRODUCT SPEC			-	
	0 PLC ± 0 1 PLC ± 1 2 PLC ± 1 3 PLC ± 1 4 PLC ± 1 ANGLES ± 1 FINISH	APPLICATION SPEC			SIZE	CAGE CODE
		SLC4-F14-016			DRAWING NO	
MATERIAL		WEIGHT		RESTRICTED TO		
-		REF. TABLE A		00779 ©= 1SNP300560-0100		
-		CUSTOMER DRAWING		SCALE 3:2		
				SHEET 5 OF 5		
				REV B2		