

USER MANUAL

LIGHT METER

PCE-LM 4

ENGLISH



User manuals in various languages (français, italiano, español, português, nederlands, türk, polski) can be found via our product search on:
www.pce-instruments.com

1. SAFETY

Read the following safety information carefully before attempting to operate or service the meter. Use the meter only as specified in this manual; otherwise, the protection provided by the meter may be impaired.

» Environment conditions:

RH≤90% (Non-Condensation)
Operating Temperature: -20°C ... 60°C
Storage Temperature: -20°C ... 60°C

» Maintenance

Repairs or servicing not covered in this manual should only be performed by qualified personnel. Wipe the unit with a dry soft cloth. Do not use abrasives or solvents on this instrument.

» Safety Symbol

 Comply with EMC

2. APPLICATION

This Light Meter is designed to meet the measurement requirements of safety Engineers, Health, Industrial safety offices and light quality control in various environments like factory, school, construction, etc.


3. FEATURES

- » High accuracy and fast response time
- » HD color LCD display
- » Ambient temperature measurement, °C/°F unit selectable
- » MAX/MIN/HOLD
- » Selectable measurement units LUX/FCREC
- » Memory for 12 readings
- » Magnet support

4. SPECIFICATIONS

Display	4 digits color LCD display
Measuring range	0 Lux~200K Lux, 0Fc~20KFc
Resolution	<1000 (0.1), >1000(1.0)
Accuracy	±3% rdg±8 dgts (<10,000Lux), ±4% rdg±10 dgts (>10,000Lux)
Temperature Range	-20°C ... 70°C / -4°F ... 158°F
Temperature Accuracy	±1.5°C /2.7°F
Data update	500ms
Over range indication	LCD displays „-OL-“
Units	LUX/FC
REC	Memory for 12 readings
HOLD/MAX/MIN	√
Magnet support	√
Battery Life	60 hours
Auto power off	With cover open, the meter shuts off automatically after 15 minutes inactivity
	With cover shut, the meter shuts off automatically after 1 minutes inactivity
Power supply	2*1.5V "AAA" batterie
Operating Conditions	-20°C ... 60°C / -4°F ... 140°F, 10% RH ...90% RH
Storage Conditions	-20°C ... 60°C / -4°F ...140°F, 10% RH ... 75%RH
Dimension(L*W*H)	174.5 × 80 × 31 mm
Weight	31g

5.METER DESCRIPTION



1. Sensor protective cover
2. Sensor
3. HOLD/MAX/MIN selection key
4. LCD display
5. Power ON/OFF key & REC key
6. Temperature sensor hole
7. Battery cover/magnetic area

6.LCD DISPLAY DESCRIPTION



1. Temperature display area
2. REC symbol
3. HOLD/MAX/MIN symbol
4. Illumination reading area
5. Illumination unit
6. Low battery symbol
7. Temperature unit symbol

7. OPERATION INSTRUCTION

7.1 Power ON/OFF function

1. Install the battery and open the protective cover, the meter will automatically turn on to measure the light intensity.
2. In the OFF mode while protective cover's removed, short press „E“ key to manually turn on the meter. Press and hold the „E“ key for 3 seconds to turn off the instrument manually.
3. The meter shuts off automatically after 15 minutes inactivity.

7.2 HOLD/MAX/MIN function

1. In measuring mode, short press the „H“ key, the „HOLD“ symbol is displayed on the top of the screen, which indicates the data is freed.
2. Press the „H“ key again, the „MAX“ symbol will be displayed at the top of the screen, the captured maximum light reading will be displayed on the LCD
3. Press the „H“ key again, the „MIN“ symbol will be displayed at the top of the screen, and the captured minimum light reading will be displayed on the LCD
4. Press the „H“ key again, the meter will exit the hold/max/min mode and return to normal measurement mode.
5. Press and hold the „H“ key for 3 seconds, the instrument will clear the record MAX/MIN value and recapture the MAX/MIN value.

7.3 REC memory function


1. In the ON mode, short press „E“ key, the instrument enters into REC mode, and the „REC“ symbol is displayed on the top left of the screen. Press „H“ key to view the record 1 to 12 measurement values in turn.
2. In the measurement mode, press „E“ and „H“ at the same time to store the desired values, which can be stored in 12 groups in cyclic memory.

7.4 °C / °F. Conversion function

In the ON mode, open the battery cover, short press „S“ key to convert the temperature unit °C / °F.

7.5 Lux/Fc conversion function

In the ON mode, open the battery cover, long press the „S“ key to convert the illuminance unit Lux/Fc



8. NOTES

1. The instrument has been calibrated before delivery. Please do not modify the calibration parameters without professional equipment and personnel.
2. [Note] This instrument has been well calibrated before delivery, the recommended calibration interval is one year.
3. Repair or maintenance should be done by professionals, not by manuals alone.
4. Wipe the case with a cloth regularly, do not use solvents or detergents to clean the meter
5. Please take out the battery when not using for a long time to avoid the battery liquid leaking out and corroding the meter.
6. When the battery power is low, LCD will show „“, symbol, then you must replace the new battery to avoid affecting the measurement accuracy.
7. Please do not use it in high temperature and high humidity place.

9. ACCESSORIES

1. User's manual
2. 2* 1.5V “AAA” batteries
3. Carrying pouch

DISPOSAL

For the disposal of batteries in the EU, the (EU) 2023/1542 directive of the European Parliament applies. Due to the contained pollutants, batteries must not be disposed of as household waste. They must be given to collection points designed for that purpose. In order to comply with the EU directive 2012/19/EU we take our devices back. We either re-use them or give them to a recycling company which disposes of the devices in line with law. For countries outside the EU, batteries and devices should be disposed of in accordance with your local waste regulations. If you have any questions, please contact PCE Instruments.

PCE INSTRUMENTS CONTACT INFORMATION

Germany

PCE Deutschland GmbH
Im Langel 26
D-59872 Meschede
Deutschland
Tel.: +49 (0) 2903 976 99 0
Fax: +49 (0) 2903 976 99 29
info@pce-instruments.com
www.pce-instruments.com/deutsch

France

PCE Instruments France EURL
23, rue de Strasbourg
67250 Soultz-Sous-Forêts
France
Téléphone: +33 (0) 972 3537 17
Numéro de fax: +33 (0) 972 3537 18
info@pce-france.fr
www.pce-instruments.com/french

Spain

PCE Ibérica S.L.
Calle Mula, 8
02500 Tobarra (Albacete)
España
Tel. : +34 967 543 548
info@pce-iberica.es
www.pce-instruments.com/espanol

United Kingdom

PCE Instruments UK Ltd
Trafford House
Chester Rd, Old Trafford
Manchester M32 0RS
United Kingdom
Tel: +44 (0) 161 464902 0
Fax: +44 (0) 161 464902 9
info@pce-instruments.co.uk
www.pce-instruments.com/english

Italy

PCE Italia s.r.l.
Via Pesciatina 878 / B-Interno 6
55010 Loc. Gragnano
Capannori (Lucca)
Italia
Telefono: +39 0583 975 114
Fax: +39 0583 974 824
info@pce-italia.it
www.pce-instruments.com/italiano

Turkey

PCE Teknik Cihazları Ltd.Şti.
Halkalı Merkez Mah.
Pehlivan Sok. No.6/C
34303 Küçükçekmece - İstanbul
Türkiye
Tel: 0212 471 11 47
Faks: 0212 705 53 93
info@pce-cihazlari.com.tr
www.pce-instruments.com/turkish

The Netherlands

PCE Brookhuis B.V.
Twentepoort West 17
7609 RD Almelo
Nederland
Telefoon: +31 (0)53 737 01 92
info@pcebenelux.nl
www.pce-instruments.com/dutch

United States of America

PCE Americas Inc.
1201 Jupiter Park Drive, Suite 8
Jupiter / Palm Beach
33458 FL
USA
Tel: +1 (561) 320-9162
Fax: +1 (561) 320-9176
info@pce-americas.com
www.pce-instruments.com/us

Denmark

PCE Instruments Denmark ApS
Birk Centerpark 40
7400 Herning
Denmark
Tel.: +45 70 30 53 08
kontakt@pce-instruments.com
www.pce-instruments.com/dansk