

# SERIES 142 ERSADUR LONGLIFE SOLDERING TIPS


**TIP'N'TURN**




tip identification  
by QR code

■ i-CON TRACE with i-TOOL TRACE soldering iron, all i-CON MK2 stations with i-TOOL MK2, i-TOOL NANO MK2 or i-TOOL PICO MK2 soldering iron


**0142PDLF01/SB**  
pencil point, recessed, 0.1 mm  $\varnothing$




**0142PDLF03/SB**  
pencil point, recessed, 0.3 mm  $\varnothing$




**0142PDLF03L/SB**  
pencil point, extended, 0.3 mm  $\varnothing$




**0142PDLF05/SB**  
pencil point, 0.5 mm  $\varnothing$




**0142PDLF08/SB**  
pencil point, 0.8 mm  $\varnothing$




**0142PDLF08L/SB**  
pencil point, extended, 0.8 mm  $\varnothing$




**0142PDLF10/SB**  
pencil point, 1.0 mm  $\varnothing$




**0142CDLF04/SB**  
chisel-shaped, 0.4 mm




**0142CDLF06/SB**  
chisel-shaped, 0.6 mm




**0142CDLF08/SB**  
chisel-shaped, 0.8 mm




**0142CDLF08A/SB**  
chisel-shaped, asymmetric, 0.8 mm




**0142CDLF10/SB**  
chisel-shaped, 1.0 mm




**0142CDLF12/SB**  
chisel-shaped, 1.2 mm




**0142CDLF16/SB**  
chisel-shaped, 1.6 mm




**0142CDLF16A/SB**  
chisel-shaped, asymmetric, 1.6 mm




**0142CDLF18L/SB**  
chisel-shaped, extended, 1.8 mm




**0142CDLF20/SB**  
chisel-shaped, 2.0 mm




**0142CDLF24/SB**  
chisel-shaped, 2.4 mm




**0142CDLF24A/SB**  
chisel-shaped, asymmetric, 2.4 mm




**0142CDLF24L/SB**  
chisel-shaped, extended, 2.4 mm




**0142CDLF32/SB**  
chisel-shaped, 3.2 mm




**0142CDLF46A/SB**  
chisel-shaped, asymmetric, 4.6 mm




**0142CDLF50/SB**  
chisel-shaped, 5.0 mm




**0142CDLF65/SB**  
chisel-shaped, 6.5 mm




**0142CDLF080/SB**  
chisel-shaped, 8.0 mm




**0142CDLF80A/SB**  
chisel-shaped, asymmetric, 8 mm



**0142CDLF100/SB**  
chisel-shaped, 10.0 mm



**0142CDLF120/SB**  
chisel-shaped, 12.0 mm



Dimensions without pre-tinning. Subject to technical changes.

# SERIES 142 ERSADUR LONGLIFE SOLDERING TIPS

**TIP'N'  
TURN**




tip identification  
by QR code

■ i-CON TRACE with i-TOOL TRACE soldering iron, all i-CON MK2 stations with i-TOOL MK2, i-TOOL NANO MK2 or i-TOOL PICO MK2 soldering iron


## 0142SDF04L/SB

pencil point, bent, extended,  
0.4 mm Ø




## 0142SDF06L/SB

pencil point, bent,  
extended, 0.6 mm Ø




## 0142SDF08L/SB

pencil point, bent,  
extended, 0.8 mm Ø




## 0142ADLF13/SB

angled face, 1.3 mm Ø




## 0142ADLF15/SB

angled face, 1.5 mm Ø




## 0142ADLF22/SB

angled face, 2.2 mm Ø




## 0142ADLF32/SB

angled face, 3.2 mm Ø




## 0142ADLF40/SB

angled face, 4.0 mm Ø




## 0142ZDLF100/SB

WICK-TIP, 10.0 mm




## 0142ZDLF150/SB

WICK-TIP, 15.0 mm




## 0142ZDLF200/SB

WICK-TIP, 20.0 mm




## 0142BDLF20/SB

PLCC blade




## 0142WDLF16/SB

PowerWell with concave portion,  
1.6 mm Ø




## 0142WDLF23/SB

PowerWell with concave portion,  
2.3 mm Ø




## 0142WDLF35/SB

PowerWell with concave portion,  
3.5 mm Ø




## 0142YDLF1224/SB

slotted, angled face, ID 1.2 mm,  
OD 2.4 mm




## 0142YDLF1852/SB

slotted, angled face, ID 1.8 mm,  
OD 5.2 mm



## 014100J

Heating element for  
i-TOOL PICO MK2, i-TOOL TRACE,  
24 V, 150 W



## 016100J

Heating element for  
TOOL NANO MK2, i-TOOL MK2,  
24 V, 150 W



Dimensions without pre-tinning. Subject to technical changes.