





MATERIAL SPECIFICATIONS

ITEM	PART NAME	MATERIAL	QTY	FINISH
1	KNOB	PA46	1	Blue
2	COVER	SUS	1	Ag Plated Over Ni Plated
3	CASE	NYLON+F.G+94V0(FR52)/BRASS STRIP	1	Black/Ag Plated Over Ni Plated
4	CONTACT	PBS C5210R-EH	1	Ag Clad

MODEL NO.

KNOB(L)

☐ MSS-1300AP



0.4 mm

☐ MSS-1300BP


1.1 mm

General specifications

Circuit	: ON-ON-ON(1P3T)
Rating	: D.C. 4V 0.3A
Contact R.[max]	: 70mΩ (initial)
Insulation R.[min]	: D.C. 500V 100MΩ
Withstand VOL.	: A.C. 500V 1minute
Timing	: Non Shorting
Operating force	: 200±100g
Life cycle[max]	: 10,000 CYCLES



SCHEMATIC



P.C.B LAYOUT

亮群股份有限公司
LIGHT COUNTRY CO.,LTD

比例 SCALE	N/A
單位 DIMENSION	m m
DO NOT SCALE DRAWING TOLERANCES UNLESS OTHERWISE	
UP TO 10	±0.3
ABOVE 10 TO 100	±0.5
ABOVE 100	±0.8
ANGULAR DIMENSIONS	±5°

品名 TITLE	MINI SLIDE SWITCH			
型號 MODEL	MSS-1300 SERIES			
繪圖 DRAWN	KTS	核准 APPROVED	HSH	
版次 REVISION	A	日期 DATE	2012/3/10	