



UT352

Sound Level Meter

meters.uni-trend.com

ENVIRONMENTAL TESTERS

UT352 sound level meter can measure noise level and output results in dB. A or C weighted modes can be selected depending on the application. UT352 consume very little power and can continuously work up to 20 hours. They are suitable for industrial and environmental sound level measurements.

Features:

- Powered by batteries or external power source
- MAX/MIN/HOLD
- A (ear)/C (machine) weighted modes
- Auto power off (cancelable)
- Data storage
- Simulated analog bar
- Over range indication
- Manual/auto range selectable



UT352

Specifications	UT352
Range	30~130dB
Accuracy	±1.5dB
Frequency	31.5Hz~8000Hz
Frequency weighting	A&C
Sampling rate (Fast)	8 times/s
Sampling rate (Slow)	1 time/s
Data storage	63
Analog outputs (AC)	0.707Vrms full scale; Output impedance: around 600Ω
Analog outputs (DC)	2Vrms full scale; 10mV/dB; Output impedance: around 100Ω

Characteristics	
Standard accessories	Windscreen, leather box, English manual, battery
Power	1.5V battery (LR6) x 4
Display	53 x 41mm
Product size	273 x 70 x 39mm
Product net weight	330g
Standard quantity per carton	10pcs
Standard carton measurement	670 x 415 x 120mm
Standard carton gross weight	7.3kg

