

PHILIPS

CertaDrive

LED driver



Datasheet

CertaDrive LED Transformer 60W 24VDC

9290 034 26506

Philips full-electronic constant voltage CertaDrive LED Transformers are designed to operate 24VDC LED solutions used in general built-in and independent applications such as non-center piece lighting, retail display lighting and linear accent lighting. They are specifically designed to ensure good performance with high cost-effectiveness.

Features

- Use for Insulation Class II applications
- Stable output voltage
- Wide ambient temperature range
- Protection against overpower and overvoltage
- Output short-circuit shutdown feature with automatic restart

Benefits

- SELV operating voltages, ensuring safety even if wiring or LED boards become damaged
- Energy savings through high efficiency
- High robustness, offering peace of mind and lower maintenance costs
- Easy to design-in and install with parallel wiring

Application

- Retail display lighting, linear accent lighting and refrigerated display lighting
- Shelf lighting
- Cove lighting
- Facade accent lighting

Logistical data

Specification item	Value
Product name	CertaDrive LED Transformer 60W 24VDC
Logistic code 12NC	9290 034 26506
Pieces per box	60

Electrical input data

Specification item	Value	Unit	Condition
Rated input voltage range	220...240	V _{ac}	Performance range
Rated input voltage	230	V _{ac}	
Rated input frequency	47...63	Hz	Performance range
Rated input current	0.3	A	@ rated output power @ rated input voltage
Max. input current	0.35	A	@ rated output power @ minimum performance input voltage
Rated input power	66.0	W	@ rated output power @ rated input voltage
Power factor	0.95		@rated output power @ rated input voltage
Total harmonic distortion	10	%	@ rated output power @ rated input voltage
Efficiency	89.0	%	@ rated output power @ rated input voltage
Input voltage AC	198...264	V _{ac}	Operational range
Input frequency AC	45...66	Hz	Operational range
Isolation input to output	Double		

Electrical output data


Specification item	Value	Unit	Condition
Regulation method	Constant Voltage		
Output voltage	24	V _{dc}	Output voltage range: 22.8 ... 25.2VDC
Output voltage max.	26	V	
Output current	250...2500	mA	
Output voltage ripple	≤ 10	%	≤ 2400 mVpp
Output power	6.0...60.0	W	
Turn-on delay	≤ 1	s	
Output voltage rise time	≤ 100	ms	
Hold-up time	≥ 10	ms	

Control interfaces

Specification item	Value	Unit	Condition
Control method	Fixed		

Wiring and Connections

Specification item	Value	Unit	Type
Input wire cross-section	0.75...1.5	mm²	solid / stranded wire
Input wire strip length	8	mm	
Output wire cross-section	0.5...1.5	mm²	solid / stranded wire
Output wire strip length	8	mm	
Maximum cable length	1	m	Total cable length between driver and LED modules per CISPR15




Isolation

Insulation per IEC61347-1	Input	Output
Input	-	Double
Output	Double	-

Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	151.5	mm	± 1
Mounting hole distance (A2)	139.5	mm	± 1
Width (B1)	40.2	mm	± 0.5
Width (B2)	28.7	mm	± 0.5
Height (C1)	31	mm	± 0.5
Mounting hole diameter (D1)	4	mm	± 0.5
Weight	182	gram	




Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-20...+50	°C	Higher ambient temperature allowed as long as Tcase-max is not exceeded
Tcase-max	90	°C	Maximum temperature measured at Tcase-point
Tcase-life	80	°C	Measured at Tcase-point
Relative humidity	10...90	%	Non-condensing

Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	30,000	hours	Measured temperature at Tcase-point is Tcase-life. Maximum failures = 10%



Maximum failures = 10%

Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-20...+80	°C	
Relative humidity	5...95	%	Non-condensing

Non-programmable features


Specification item	Value		Condition
Open load protection	Yes		Uout (open circuit) = 26V max.
Short circuit protection	Yes		Hiccup mode, automatic recovering
Over power protection	Yes		Automatic recovering
Hot wiring	Yes		
Suitable for fixtures with protection class	II		per IEC60598

Inrush current

Specification item	Value	Unit	Condition
Inrush current	36	A	Input voltage 230V
Inrush peak width	12.4	μs	Input voltage 230 V, measured at 50% height
Drivers / MCB 16A type B @230V AC	≤ 19	pcs	Input voltage 230V

Please refer to the driver design in guide if you use other MCB-types.

If several mini circuit breakers are used directly side-by-side (without distance pieces)
a correction factor of 80% has to be applied to the rated current



Driver touch current / protective conductor current / earth leakage current

Specification item	Value	Unit	Condition
Typical Touch Current (ins. Class II)	0.7	mA peak	Acc. IEC60598-1. LED module contribution not included

Surge immunity


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	1	kV	L-N acc. IEC61000-4-5. 2 Ohm
Mains surge immunity (comm. mode)	2	kV	L/N-PE, acc. IEC61000-4-5. 12 Ohm

Application Info (Approbation)


Specification item	Value
Approval marks and Certifications	CCC / CE / ENEC / MM / RCM / SELV / UKCA
Ingress Protection classification (IP)	20
Noise and hum dB(A)	20
Application	Indoor Constant Voltage
Mounting Type	Built-in / Independent

Graphs


Operating window




Power factor versus output power



Efficiency versus output power



THD versus output power



©2024 Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved.
UK importer address: Signify Commercial UK Limited, 3, Guildford Business Park, GU2 8XG.

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Date of release: May 24, 2024 v1

www.philips.com/oem