


SPT - Threaded Step Probes

mm [inch]



SPT500 RJ13 N

Minimum centers: 1.27 (.050)
Full travel: 5.00 (.196)
Working travel: 4.00 (.157)
Current rating: 3 A
Probe resistance: < 50 mΩ
Plunger material: BeCu - Gold Plated
Barrel material: Brass - Gold Plated
Spring material: MW - Gold Plated


Operating temperature: -40 °C up to +80 °C
(-40 °F up to +176 °F)

Spring force at working stroke: 1.10 N (4.0 oz)

© COPYRIGHT 2019 EQUIP-TEST KFT. ALL RIGHTS RESERVED		Name	Date	Catalog Item: SPT500 RJ13 N			
	Designed	Sz. A.	2024. 11. 21.				
	Drawed						
	Checked						
This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!	Note				Drawing No.:		 TEST = SUPPORT = INNOVATE
						A4	SHEET 2 OF 1

SPT - Threaded Step Probes

mm [inch]



Tools for the Test Probe

Tool Handle: TH3
Adjustable Torque Handle: TTS01
Insertion/Extraction Bit: TBT5071

Tools for the Receptacle

Tool Handle Insertion: TH1
Tool Handle Insertion/Extraction: TH2
Insertion Bit: TBR5035
Extraction Bit: TBR5070

© COPYRIGHT 2019 EQUIP-TEST KFT. ALL RIGHTS RESERVED		Name	Date	Catalog Item: SPT500 RJ13 N		
	Designed	Sz. A.	2024. 11. 21.			
	Drawed					
	Checked					
This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!	Note	Drawing No.:			 TEST • SUPPORT • INNOVATE	
			A4	SHEET 2 OF 2		