DATASHEET

SMD ▪ B
19-237/BHGHR6C-A03/2T

Features
- Package in 8mm tape on 7″ diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Multi-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version.
- Compliance with EU REACH.
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm).

Description
- The 19-237 SMD LED is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications
- Backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

Copyright © 2010, Everlight All Rights Reserved. Release Date : 16-Jan-2025 Issue No: DSE-0000247 Rev.4 www.everlight.com
Ver.:4 Release Date:01/20/2025 狀態:Approved(正式發行)

Device Selection Guide

Code	Chip Materials	Emitted Color	Resin Color
BH	InGaN	Blue	Water Clear
GH	InGaN	Brilliant Green	
R6	AlGaInP	Brilliant Red	

Absolute Maximum Ratings (Ta=25℃)

Parameter	Symbol	Code	Rating	Unit
Reverse Voltage	V_R		5	V
Forward Current	I_F	BH	10	mA
		GH	10	
		R6	25	
Peak Forward Current (Duty 1/10 @1KHz)	I_{FP}	BH	100	mA
		GH	100	
		R6	60	
Power Dissipation	Pd	BH	40	mW
		GH	40	
		R6	60	
Electrostatic Discharge(HBM)	ESD	BH	150	V
		GH	150	
		R6	2000	
Operating Temperature	T_{opr}		-40 ~ +85	℃
Storage Temperature	Tstg		-40 ~ +90	℃
Soldering Temperature	Tsol		Reflow Soldering : 260 ℃ for 10 sec. Hand Soldering : 350 ℃ for 3 sec.	

Copyright © 2010, Everlight All Rights Reserved. Release Date : 16-Jan-2025 Issue No: DSE-0000247 Rev.4 www.everlight.com
Ver.:4 Release Date:01/20/2025 狀態:Approved(正式發行)

Electro-Optical Characteristics (Ta=25℃)

Parameter	Symbol	Code	Min.	Typ.	Max.	Unit	Condition
Luminous Intensity	Iv	BH	57.0	-----	112	mcd	
		GH	140	-----	285		
		R6	72.0	-----	180		
Viewing Angle	$2\theta_{1/2}$		-----	120	-----	Deg	
Peak Wavelength	λ p	BH	-----	468	-----	nm	
		GH	-----	518	-----		
		R6	-----	632	-----		
Dominant Wavelength	λ d	BH	465	-----	475	nm	I_F=20mA
		GH	518	-----	528		
		R6	614	-----	628		
Spectrum Radiation Bandwidth	△λ	BH	-----	25	-----	nm	
		GH	-----	35	-----		
		R6	-----	20	-----		
Forward Voltage	V_F	BH	2.7	3.3	3.7	V	
		GH	2.7	3.3	3.7		
		R6	1.7	2.0	2.4		
Reverse Current	I_R	BH	-----	-----	50	μA	V_R=5V
		GH	-----	-----	50		
		R6	-----	-----	10		

Note:
1. Tolerance of Luminous Intensity: ±11%
2. Tolerance of Dominant Wavelength: ±1nm
3. Tolerance of Forward Voltage: ±0.1V
4. RA test @5mA.
5. Reverse voltage condition is test only. Do not reverse operation.

Copyright © 2010, Everlight All Rights Reserved. Release Date : 16-Jan-2025 Issue No: DSE-0000247 Rev.4 www.everlight.com
Ver.:4 Release Date:01/20/2025 狀態:Approved(正式發行)

BH
Bin Range of Luminous Intensity

Bin Code	Min.	Max.	Unit	Condition
P2	57	72	mcd	I_F=20mA
Q1	72	90		
Q2	90	112		

GH
Bin Range of Luminous Intensity

Bin Code	Min.	Max.	Unit	Condition
R2	140	180	mcd	I_F=20mA
S1	180	225		
S2	225	285		

R6
Bin Range of Luminous Intensity

Bin Code	Min.	Max.	Unit	Condition
Q	72	112	mcd	I_F=20mA
R	112	180		

EVERLIGHT

Copyright © 2010, Everlight All Rights Reserved. Release Date : 16-Jan-2025 Issue No: DSE-0000247 Rev.4 www.everlight.com
Ver.:4 Release Date:01/20/2025 狀態:Approved(正式發行)

Typical Electro-Optical Characteristics Curves

BH

Spectrum Distribution



Forward Current vs. Forward Voltage



Luminous Intensity vs. Ambient Temperature



Luminous Intensity vs. Forward Current



Forward Current Derating Curve



Radiation Diagram



Copyright © 2010, Everlight All Rights Reserved. Release Date : 16-Jan-2025 Issue No: DSE-0000247 Rev.4 www.everlight.com
Ver.:4 Release Date:01/20/2025 狀態:Approved(正式發行)

Typical Electro-Optical Characteristics Curves

GH

Spectrum Distribution



Forward Current vs. Forward Voltage



Luminous Intensity vs. Ambient Temperature



Luminous Intensity vs Forward Current



Forward Current Derating Curve



Radiation Diagram Ta=25°C



Copyright © 2010, Everlight All Rights Reserved. Release Date : 16-Jan-2025 Issue No: DSE-0000247 Rev.4
www.everlight.com
Ver.:4 Release Date:01/20/2025 狀態:Approved(正式發行)

Typical Electro-Optical Characteristics Curves

R6

Spectrum Distribution



Forward Current vs. Forward Voltage



Luminous Intensity vs. Ambient Temperature



Luminous Intensity vs. Forward Current



Forward Current Derating Curve



Radiation Diagram



Copyright © 2010, Everlight All Rights Reserved. Release Date : 16-Jan-2025 Issue No: DSE-0000247 Rev.4 www.everlight.com
Ver.:4 Release Date:01/20/2025 狀態:Approved(正式發行)

Package Dimension











Suggested pad dimension is just for reference only.
Please modify the pad dimension based on individual need.

Note: Tolerances unless mentioned ±0.1mm. Unit = mm

Copyright © 2010, Everlight All Rights Reserved. Release Date : 16-Jan-2025 Issue No: DSE-0000247 Rev.4 www.everlight.com
Ver.:4 Release Date:01/20/2025 狀態:Approved(正式發行)

Moisture Resistant Packing Materials

Label Explanation



- CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Chromaticity Coordinates & Dom. Wavelength Rank
- REF: Forward Voltage Rank
- LOT No: Lot Number

Reel Dimensions



Note: The tolerances unless mentioned is ±0.1mm ,Unit = mm

Copyright © 2010, Everlight All Rights Reserved. Release Date : 16-Jan-2025 Issue No: DSE-0000247 Rev.4 www.everlight.com
Ver.:4 Release Date:01/20/2025 狀態:Approved(正式發行)

Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel



Note: The tolerances unless mentioned is ±0.1mm ,Unit = mm

Moisture Resistant Packaging



Copyright © 2010, Everlight All Rights Reserved. Release Date : 16-Jan-2025 Issue No: DSE-0000247 Rev.4 www.everlight.com
Ver.:4 Release Date:01/20/2025 狀態:Approved(正式發行)

Precautions For Use

1. Over-current-proof
Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).
2. Storage
2.1 Do not open moisture proof bag before the products are ready to use.
2.2 Before opening the package: The LEDs should be kept at 30℃ or less and 90%RH or less.
2.3 After opening the package: The LED's floor life is 1 year under 30℃ or less and 60% RH or less.
If unused LEDs remain, it should be stored in moisture proof packages.
2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.
Baking treatment : 60±5℃ for 24 hours.
3. Soldering Condition
3.1 Pb-free solder temperature profile



3.2 Reflow soldering should not be done more than two times.
3.3 When soldering, do not put stress on the LEDs during heating.
3.4 After soldering, do not warp the circuit board.
4.Soldering Iron
Each terminal is to go to the tip of soldering iron temperature less than 350℃ for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing
Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



Copyright © 2010, Everlight All Rights Reserved. Release Date : 16-Jan-2025 Issue No: DSE-0000247 Rev.4 www.everlight.com
Ver.:4 Release Date:01/20/2025 狀態:Approved(正式發行)

Application Restrictions

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.

DISCLAIMER

1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

Copyright © 2010, Everlight All Rights Reserved. Release Date : 16-Jan-2025 Issue No: DSE-0000247 Rev.4 www.everlight.com
Ver.:4 Release Date:01/20/2025 狀態:Approved(正式發行)