



Product: [1502R](#) 

Media Control, 1 Pair 22 AWG TC, 2 Cond. 18 AWG, Riser

Product Description

Multimedia Control Cable, 1 Pair 22 AWG stranded (7x30) tinned copper (data) with FPE insulation, Beldfoil® shield w/ drain, 2 Conductor 18 AWG stranded (16x30) tinned copper conductor (power) with F-R PVC insulation, Riser, F-R PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Multi-Media & Lighting Automation / Control, AMX™ and Crestron® Control Systems
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	22 AWG	7x30	TC - Tinned Copper
Conductor(s)	2	18 AWG	16x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code	Notes
Pair(s)	PE - Polyethylene (Foam)	0.025 in (0.64 mm)	0.079 in (2.0 mm)	Blue & White, Red & Black	HDPE
Conductor(s)	PVC - Polyvinyl Chloride	0.013 in (0.33 mm)	0.073 in (1.9 mm)	Red & Black	

Inner Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC
	Tinned Copper (TC)		

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.039 in (0.99 mm)	0.25 in (6.4 mm)	Yes

Overall Cable Diameter (Nominal):	0.25 in (6.4 mm)
-----------------------------------	------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Inductance	Max. Current
Pair(s)	18.2 Ohm/1000ft	17.42 Ohm/1000ft (57.15 Ohm/km)	14 pF/ft (46 pF/m)	38 pF/ft (120 pF/m)	100 Ohm	0.232 µH/ft (0.761 µH/m)	6 Amps per conductor @ 30°C
Conductor(s)	6.9 Ohm/1000ft (23 Ohm/km)		29 pF/ft (95 pF/m)			0.168 µH/ft (0.551 µH/m)	14 Amps per conductor @ 30°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
----------------	-----------

75°C	-20°C to +75°C
------	----------------

Bend Radius

Stationary Min.	Installation Min.
2.5 in (64 mm)	2.5 in (64 mm)

Max. Pull Tension:	65.3 lbs (29.6 kg)
Bulk Cable Weight:	40 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL 1666 Riser, IEEE 1202 FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	1502P

Product Notes

Notes:	Sequential footage marking every two feet.
--------	--

History

Update and Revision:	Revision Number: 0.537 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1502R G75500	Aqua	Reel	500 ft	612825115953	C
1502R G751000	Aqua	Reel	1,000 ft	612825115946	C
1502R 010500	Black	Reel	500 ft	612825116004	C
1502R 0101000	Black	Reel	1,000 ft	612825115984	C
1502R 0105000	Black	Reel	5,000 ft	612825116011	
1502R 01010000	Black	Reel	10,000 ft	612825115991	
1502R 009500	White	Reel	500 ft	612825115977	C
1502R 0091000	White	Reel	1,000 ft	612825115960	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.