


AK6

6000 A Transient voltage suppressor



Product features

Note: Low slope resistance

- Very low clamping voltage
- Sharp breakdown voltage
- Glass passivated junction
- Snapback technology for superior clamping factor
- High temperature wave soldering: +265 °C /10 s at terminal
- UL 1449 recognized.
File No. : E340782 Guide VZCA2

Applications

- Consumer electronics
- Telecommunications
- Computing and servers
- Appliances
- Industrial automation
- Vac line protection

Environmental compliance and general specifications



Ordering part number

AK6 -076 C

Family name _____

V_R voltage _____

Bi-/Uni-Directional (C=Bi) _____

Alternate ordering part number

AK6 E -076 C

Family name _____

Eaton designator (optional) _____

V_R voltage _____

Bi-/Uni-Directional (C=Bi) _____

PIN configuration




Powering Business Worldwide

Absolute maximum ratings

(+25 °C, RH=45%-75%, unless otherwise noted)

Parameter	Symbol	Value	Unit
Peak current rating per 8/20 μ s IEC 61000-4-5	I_{PP}	6	kA
Operating junction temperature range	T_J	-55 to +125	°C
Storage temperature range	T_{STG}	-55 to +150	°C


Mechanical parameters- mm



Dimension	Inches	Millimeters
A	0.951 $\pm$ 0.039	24.15 $\pm$ 1.00
B	0.094 $\pm$ 0.024	2.40 $\pm$ 0.60
C	0.236 $\pm$ 0.039	6.00 $\pm$ 1.00
D	0.570 max	14.48 max
E	0.050 $\pm$ 0.002	1.27 $\pm$ 0.05
F	0.500 max	12.70 max
G	015C to 025C	0.169 $\pm$ 0.047
	030C to 042C	0.197 $\pm$ 0.047
	058C to 076C	0.228 $\pm$ 0.047
	100C	0.260 $\pm$ 0.047
	133C	0.287 $\pm$ 0.047
	170C to 190C	0.346 $\pm$ 0.047
	240C	0.406 $\pm$ 0.047
	275C to 300C	0.496 $\pm$ 0.047
	380C to 430C	0.559 $\pm$ 0.047
L_1/L_2	$L_1=L_2$ tolerance $\pm$ 0.047inch ($\pm$ 1.20 mm)	

Part marking

Standard part number marking




Side view

Part number:

AK6-015C; AK6-020C
AK6-025C; AK6-030C
AK6-042C; AK6-058C
AK6-066C; AK6-076C
AK6-100C; AK6-133C


Alternate part number marking



Side view

Part number:

AK6E-015C; AK6E-020C
AK6E-025C; AK6E-030C
AK6E-042C; AK6E-058C
AK6E-066C; AK6E-076C
AK6E-100C; AK6E-133C



Top view

Part number:

AK6-170C
AK6-190C
AK6-240C
AK6-275C
AK6-300C
AK6-380C
AK6-430C



Top view

Part number:

AK6E-170C
AK6E-190C
AK6E-240C
AK6E-275C
AK6E-300C
AK6E-380C
AK6E-430C

Packaging information (mm)

Bulk: 56 parts per box

Electrical characteristics (+25 °C)


Part number Bi-Polar	V _R (V)	V _{BR} @ I _T min (V)	max (V)	I _T (mA)	I _R @ V _R (μA)	V _C @ I _{PP} (V)	I _{PP} (A)	UL recognized
AK6-015C	15	16	19	10	10	28	6000	
*AK6-020C	20	22	24	10	10	50	6000	
*AK6-025C	25	28	30	10	10	60	6000	
AK6-030C	30	32	37	10	10	90	6000	
*AK6-042C	42	47	51	10	10	105	6000	
*AK6-058C	58	64	70	10	10	110	6000	X
*AK6-066C	66	72	80	10	10	120	6000	X
*AK6-076C	76	85	95	10	10	140	6000	X
*AK6-100C	100	110	122	10	10	165	6000	
*AK6-133C	133	147	162	10	10	220	6000	
*AK6-170C	170	180	220	10	10	260	6000	X
*AK6-190C	190	200	245	10	10	290	6000	
*AK6-240C	240	250	285	10	10	340	6000	
*AK6-275C	275	300	335	10	10	435	6000	
*AK6-300C	300	330	366	10	10	470	6000	
*AK6-380C	380	401	443	10	10	520	6000	X
*AK6-430C	430	440	490	10	10	625	6000	X

Note: Standard part numbers listed


Alternate part numbers have the addition of an E. Example standard part number AK6-015C, Alternate part number AK6E-015C

Ratings and V-I characteristic curves (+25 °C unless otherwise noted)

V- I curve characteristics (Bi-directional)



V- I curve characteristics (Bi-directional with negative resistance)



Surge waveform: 8/20 μ s

V_R : Stand-off voltage – Maximum voltage that can be applied


V_{BR} : Breakdown voltage

V_C : Clamping voltage – Peak voltage measured across the suppressor at a specified I_{PP}


I_R : Reverse leakage current

I_T : Test current


Typical V_{BR} vs junction temperature




Pulse waveform



Pulse derating curve



Wave solder profile



Reference EN 61760-1:2006

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat		
• Temperature min. (T_{smin})	100 °C	100 °C
• Temperature typ. (T_{styp})	120 °C	120 °C
• Temperature max. (T_{smax})	130 °C	130 °C
• Time (T_{smin} to T_{smax}) (t_s)	70 seconds	70 seconds
Δ preheat to max Temperature	150 °C max.	150 °C max.
Peak temperature (T_p)*	235 °C – 260 °C	250 °C – 265 °C
Time at peak temperature (t_p)	10 seconds max 5 seconds max each wave	10 seconds max 5 seconds max each wave
Ramp-down rate	~ 2 K/s min ~3.5 K/s typ ~5 K/s max	~ 2 K/s min ~3.5 K/s typ ~5 K/s max
Time 25 °C to 25 °C	4 minutes	4 minutes

Manual solder

+350 °C (4-5 seconds by soldering iron), generally manual/hand soldering is not recommended

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2024 Eaton
All Rights Reserved
Printed in USA
Publication No. 11209
September 2024

Eaton is a registered trademark.

All other trademarks are property
of their respective owners.

Follow us on social media to get the
latest product and support information.

