


ROCKER SWITCH MODEL MR2 SERIES




RATING:16(8)A 125/250V~ (cURus/ENEC15)

DIELECTRIC VOLTAGE-WITHSTAND:1,500VAC FOR 1 MINUTE

INSULATION RESISTANCE:DC 500V 100M Ω (MIN.)

CONTACT RESISTANCE:20mΩ INITIAL (MAX.)

WATERPROOF GRADE: IP68 (ABOVE THE PANEL)



PANEL THICKNESS:1.0~3.0mm



NOTE:TOLERANCES UNLESS OTHERWISE SPECIFIED:± .012/0.3 (in/mm)

REVISION	DESCRIPTION	REVISED BY	TOLERANCES	ANGLE $\frac{1}{2}^\circ$		UNIT	mm	PART NAME	DWG NO
A			DRAWN BY	楊偉韶	DESIGNED BY	蔡劍	SCALE	2/1	MR2 SPEC DRAWING
B	2025.06.18 增加螺帽	楊偉韶	CHECKED BY		APPROVED BY		DATE	2023.02.02	S9105C
C	2023.06.13 依总表修正品名	楊偉韶							
D	2023.02.02 首次出图	楊偉韶							