HENSEL

# FP AP 10

• Cover

## CONNECTION DATA

## MECHANICAL PROPERTIES

| | |
|---|---|
| Suitable for box size: | 1 |

## AMBIENT CONDITIONS

| | |
|---|---|
| Application area: | Indoor installation |
| Maximum ambient temperature 24 h: | 35 °C |
| Ambient temperature: | -5 °C up to +40 °C |
| Relative humidity: | ≤ 50 % at 40 °C, ≤ 100 % at 25 °C |

## MATERIAL PROPERTIES

| | |
|---|---|
| Material: | Polycarbonate |

## DIMENSIONS

| | |
|---|---|
| Height: | 130 mm |
| Width: | 220 mm |
| Net weight: | 0.107 kg |

## CERTIFICATES

| | |
|---|---|
| conforming to the standards: | IEC 61439-3 |



Gustav Hensel GmbH & Co. KG * Gustav-Hensel-Str. 6 * 57368 Lennestadt * Germany * Phone: +49 (0)2723/609-0

## SALES DATA

| | |
|---|---|
| Product number: | 68000052 |
| EAN: | 4012591104605 |
| Pack unit: | 1 |
| Customs tariff number: | 85371098 |
| ETIM class: | DYNAMIC: EC000201 - Built-in panel for command devices<br>ETIM-9.0: EC000201 - Built-in panel for command devices<br>ETIM-8.0: EC000201 - Built-in panel for command devices<br>ETIM-7.0: EC000201 - Built-in panel for command devices<br>ETIM-6.0: EC000201 - Built-in panel for command devices<br>ETIM-5.0: EC000201 - Built-in panel for command devices<br>ETIM-4.0: EC000201 - Built-in panel for command devices |

## DRAWINGS






Gustav Hensel GmbH & Co. KG * Gustav-Hensel-Str. 6 * 57368 Lennestadt * Germany * Phone: +49 (0)2723/609-0