



Mi 0310



- Empty box
- dimensions H x W x D: 450 x 300 x 214 mm

ELECTRICAL PROPERTIES

Rated insulation voltage:

Rated insulation voltage	Voltage type
$U_i = 690\text{ V}$	a.c.
$U_i = 1000\text{ V}$	d.c.

Protection class: II

CONNECTION DATA

MECHANICAL PROPERTIES

Protection cover according to DIN EN 61439 via lid	
Type of lid fastening:	Tool operation
Can be combined:	Yes
IP degree of protection:	IP65
Impact strength:	IK08

AMBIENT CONDITIONS

Application area:

Indoor installation

Maximum ambient temperature 24 h:

35 °C

Ambient temperature:

-25 °C up to +70 °C

MATERIAL PROPERTIES

Material:

Polycarbonate

Glow wire test according to IEC 60695-2-11:

960 °C

UV-beständig nach DIN EN 61439-1:

Yes

Halogen-free:

Yes

Silicone-free:

Yes

DIMENSIONS

Height:

450 mm

Width:

300 mm

Depth:

214 mm

Net weight:

3.075 kg

Mounting height:

425 mm

Mounting width:

275 mm

Mounting depth:

Equipping	Depth
without	195 mm
Mounting plate	191 mm
DIN rail	180 mm

COLOURS

Colour of the lid:

Transparent

Bottom part colour:

Grey

CERTIFICATES

conforming to the standards:

IEC 61439-2

SALES DATA

Product number:

EAN:

Pack unit:

Customs tariff number:

ETIM class:

2000004

4012591650041

1

85371098

DYNAMIC: EC000058 - Empty cabinet

ETIM-9.0: EC000058 - Empty cabinet

ETIM-8.0: EC000058 - Empty cabinet

ETIM-7.0: EC000058 - Empty cabinet

ETIM-6.0: EC000058 - Empty cabinet

ETIM-5.0: EC000058 - Empty cabinet


ETIM-4.0: EC000058 - Empty cabinet


Rated loading factors

Power dissipation capability:

power dissipation capability Pde	Temperature difference
P _{de} = 1.8 W	1 K

DRAWINGS





2xM20, 10xM25
 1xM32/40
 1xM20, 4xM25 1xM20, 4xM25
 1xM32/40 1xM32/40
 3xM40/50 3xM40/50
 2xM20
 10xM25, 1xM32/40