

00



tweezers with flat and thick tips for general purpose. ESD version available.

Order code	ESD code	Lenght (mm)	Lenght (")	Version
00	00ESD	120	4 3/4"	SA

00B



tweezers with flat and thick tips, externally serrated for general purpose

Order code	Lenght (mm)	Lenght (")	Version
00B	120	4 3/4"	SA

00C



tweezers with flat and thick tips for general purpose; (same as 00 but with shorter handles)

Order code	Lenght (mm)	Lenght (")	Version
00C	105	4 1/8"	SA

00D



tweezers with flat and thick tips, internally serrated (on the tips) and externally serrated (on the handles). ESD version available.

Order code	ESD code	Lenght (mm)	Lenght (")	Version
00D	00DESD	120	4 3/4"	SA

2A



tweezers with rounded and flat tips for general purpose. ESD version available.

Order code	ESD code	Lenght (mm)	Lenght (")	Version
2A	2AESD	120	4 3/4"	SA

26



tweezers with very strong and flat tips

Order code	Lenght (mm)	Lenght (")	Version
26	135	5 1/4"	SA

27



tweezers with very strong and flat tips. Same as 26 but with thinner blades

Order code	Lenght (mm)	Lenght (")	Version
27	135	5 1/4"	SA

231



tweezers with internally serrated tips for general purpose

Order code	Lenght (mm)	Lenght (")	Version
231	120	4 3/4"	SA

A



tweezers with strong and precise tips for bending wires and components

Order code	Lenght (mm)	Lenght (")	Version
A	115	4 1/2"	SA



TWEEZERS



51S



tweezers with very fine tips bent at 40° for handling of micro components

Order code	Lenght (mm)	Lenght (")	Version
51S	120	4 3/4"	SA

65A



tweezers with long, thin handles and very fine tips bent at 40°. Suitable for the gripping of generic micro chips and micro components

Order code	Lenght (mm)	Lenght (")	Version
65A	135	5 1/4"	SA

SS



tweezers with very fine tips, long and thin handles, ideal for operating close to heat sources

Order code	Lenght (mm)	Lenght (")	Version
SS	140	5 1/2"	SA

2AB



tweezers with rounded and flat tips for general purpose

Order code	Lenght (mm)	Lenght (")	Version
2AB	120	4 3/4"	SA

5A



tweezers with very fine, sharp and oblique tips

Order code	Lenght (mm)	Lenght (")	Version
5A	115	4 1/2"	SA

7



tweezers with very fine and bent tips for an easier grip in high density areas. ESD version available.

Order code	ESD code	Lenght (mm)	Lenght (")	Version
7	7ESD	120	4 3/4"	SA

7A



tweezers with very fine and bent tips for easier grip in high density areas (same as 7 but with stronger tips). ESD version available.

Order code	ESD code	Lenght (mm)	Lenght (")	Version
7A	7AESD	120	4 3/4"	SA

7B



tweezers with very fine and bent tips for easier grip in high density areas (same as 7 but with blades internally serrated)

Order code	Lenght (mm)	Lenght (")	Version
7B	120	4 3/4"	SA

7E



tweezers with very fine and bent tips for easier grip in high density areas (same as 7 but with flat tips)

Order code	Lenght (mm)	Lenght (")	Version
7E	120	4 3/4"	SA



P



tweezers with strong tips, for general purpose

Order code	Lenght (mm)	Lenght (")	Version
P	120	4 3/4"	SA

S



tweezers with fine tips for general purpose

Order code	Lenght (mm)	Lenght (")	Version
S	120	4 3/4"	SA

SA



tweezers with very strong tips for general purpose

Order code	Lenght (mm)	Lenght (")	Version
SA	120	4 3/4"	SA

SB



tweezers with very fine tips for general purpose

Order code	Lenght (mm)	Lenght (")	Version
SB	120	4 3/4"	SA

4



tweezers with very fine and sharp tips

Order code	Lenght (mm)	Lenght (")	Version
4	110	4 1/4"	SA

4A



tweezers with sharp and strong tips

Order code	Lenght (mm)	Lenght (")	Version
4A	110	4 1/4"	SA

5



tweezers with very fine and sharp tips, ideal for SMD applications. ESD version available.

Order code	ESD code	Lenght (mm)	Lenght (")	Version
5	5ESD	110	4 1/4"	SA

5B



tweezers with very fine and sharp tips, ideal for SMD applications; tips bent at 40° for a better visual of the work area

Order code	Lenght (mm)	Lenght (")	Version
5B	110	4 1/4"	SA

5C



tweezers with sharp and strong tips, ideal for SMD applications; similar to 5 but shorter

Order code	Lenght (mm)	Lenght (")	Version
5C	100	4"	SA



TWEEZERS general purpose

0



tweezers with fine tips. ESD version available.

Order code	ESD code	Lenght (mm)	Lenght (")	Version
0	0ESD	120	4 3/4"	SA

0A



tweezers with very fine tips, ideal for watch-repairers

Order code	Lenght (mm)	Lenght (")	Version
0A	120	4 3/4"	SA

0C9



flat tweezers with very fine tips and thin blades (same as "0" but 90 mm long)

Order code	Lenght (mm)	Lenght (")	Version
0C9	90	3 1/2"	SA

0C10



flat tweezers with very fine tips and thin blades (same as "0" but 100 mm long)

Order code	Lenght (mm)	Lenght (")	Version
0C10	100	4"	SA

0C11



flat tweezers with very fine tips and thin blades (same as "0" but 110 mm long)

Order code	Lenght (mm)	Lenght (")	Version
0C11	110	4 1/4"	SA

1



tweezers with strong tips and thin blades for generic purpose. ESD version available.

Order code	ESD code	Lenght (mm)	Lenght (")	Version
1	1ESD	120	4 3/4"	SA

2



tweezers with sharp blades and strong tips, for generic purpose. ESD version available.

Order code	ESD code	Lenght (mm)	Lenght (")	Version
2	2ESD	120	4 3/4"	SA

3



tweezers with strong tips and thin blades, ideal for microelectronic applications. ESD version available.

Order code	ESD code	Lenght (mm)	Lenght (")	Version
3	3ESD	120	4 3/4"	SA

3C



tweezers with strong tips and thin blades, ideal for microelectronic applications. ESD version available.

Order code	ESD code	Lenght (mm)	Lenght (")	Version
3C	3CESD	110	4 1/4"	SA