

Incremental encoders

Standard
sine wave output, highly interpolable, optical

Sendix 5814 / 5834 (shaft / hollow shaft)

SinCos



The incremental encoders Sendix 5814 and 5834 with SinCos interface are particularly suited for applications in the field of drive technology.

Thanks to their high signal quality, they are optimally suited for further interpolation.



Powerful

- With incremental SinCos tracks.
- Very high signal quality.
- Suited for motor feedback applications.

Flexible

- Shaft and hollow shaft versions.
- Cable and connector variants.
- Various mounting options available.

Order code 8.5814
Shaft version Type

- a** Flange
1 = clamping flange, $\varnothing$ 58 mm [2.28"]
- b** Shaft ($\varnothing \times L$)
2 = 10 x 20 mm [0.39 x 0.79"], with flat
- c** Output circuit / supply voltage
1 = SinCos / 5 V DC
2 = SinCos / 10 ... 30 V DC

- d** Type of connection
1 = axial cable, 1 m [3.28'] PVC
A = axial cable, special length PVC *)
2 = radial cable, 1 m [3.28'] PVC
B = radial cable, special length PVC *)
5 = axial M12 connector, 8-pin
6 = radial M12 connector, 8-pin
- *) Available special lengths (connection types A, B):
2, 3, 5, 8, 10, 15 m [6.56, 9.84, 16.40, 26.25, 32.80, 49.21']
order code expansion .XXXX = length in dm
ex.: 8.5814.122A.2048.0030 (for cable length 3 m)

- e** Pulse rate
1024, 2048
- Optional on request
- Ex 2/22 ¹⁾
- surface protection salt spray tested

Order code 8.5834
Hollow shaft Type

- a** Flange
1 = with spring element, long
5 = with stator coupling, $\varnothing$ 63 mm [2.48"]
- b** Through hollow shaft
3 = $\varnothing$ 10 mm [0.39"]
4 = $\varnothing$ 12 mm [0.47"]
5 = $\varnothing$ 14 mm [0.55"]
6 = $\varnothing$ 15 mm [0.59"]
8 = $\varnothing$ 3/8"
9 = $\varnothing$ 1/2"
Tapered shaft
K = $\varnothing$ 10 mm [0.39"]

- c** Output circuit / supply voltage
1 = SinCos / 5 V DC
2 = SinCos / 10 ... 30 V DC
- d** Type of connection
2 = radial cable, 1 m [3.28'] PVC
B = radial cable, special length PVC *)
E = tangential cable, 1 m [3.28'] PVC
F = tangential cable, special length PVC *)
6 = radial M12 connector, 8-pin
- *) Available special lengths (connection types B, F):
2, 3, 5, 8, 10, 15 m [6.56, 9.84, 16.40, 26.25, 32.80, 49.21']
order code expansion .XXXX = length in dm
ex.: 8.5834.142B.2048.0030 (for cable length 3 m)

- e** Pulse rate
1024, 2048
- Optional on request
- Ex 2/22
(not for type of connection E, F) ¹⁾
- surface protection salt spray tested

1) For the cable connection type, cable material PUR.

Incremental encoders

Standard sine wave output, highly interpolable, optical		Sendix 5814 / 5834 (shaft / hollow shaft)	SinCos
Connection technology			Order no.
Cordset, pre-assembled		M12 female connector with coupling nut, 8-pin 2 m [6.56'] PVC cable	05.00.6041.8211.002M
Connector, self-assembly (straight)		M12 female connector with coupling nut, 8-pin	05.CMB 8181-0

Further accessories can be found in the accessories section or in the accessories area of our website at: kuebler.com/accessories.
Additional connectors can be found in the connection technology section or in the connection technology area of our website at: kuebler.com/connection_technology.

Technical data	
Mechanical characteristics	
Maximum speed	12000 min ⁻¹ , 5000 min ⁻¹ (continuous)
Starting torque – at 20 °C [68 °F]	< 0.01 Nm
Mass moment of inertia	shaft 4.0 x 10 ⁻⁶ kgm ²
	hollow shaft 7.0 x 10 ⁻⁶ kgm ²
Load capacity of shaft	radial 80 N
	axial 40 N
Weight	approx. 0.45 kg [15.85 oz]
Protection acc. to EN 60529	IP65
Working temperature range	-40 °C ... +90 °C [-40 °F ... +194 °F] ¹⁾
Materials	shaft / hollow shaft stainless steel
	flange aluminum
	housing zinc die-cast
	cable PVC (PUR for Ex 2/22)
Shock resistance acc. to EN 60068-2-27	2500 m/s ² , 6 ms
Vibration resistance acc. to EN 60068-2-6	100 m/s ² , 55 ... 2000 Hz
Electrical characteristics	
Supply voltage	5 V DC (±5 %) or 10 ... 30 V DC
Current consumption (no load)	5 V DC max. 70 mA
	10 ... 30 V DC max. 45 mA
Reverse polarity protection of the supply voltage	yes
UL approval	file no. E224618
CE compliant acc. to	EMC guideline 2014/30/EU RoHS guideline 2011/65/EU
SinCos interface	
Max. frequency -3dB	400 kHz
Signal level	1 V _{pp} (±10 %)
Short circuit proof	yes ²⁾
Pulse rate	1024 / 2048 ppr

Terminal assignment

Output circuit	Type of connection	Cable (isolate unused cores individually before initial start-up)							
1, 2	1, 2, A, B, E, F	Signal:	0 V	+V	A	$\bar{A}$	B	$\bar{B}$	$\perp$
		Core color:	WH	BN	GN	YE	GY	PK	shield
Output circuit	Type of connection	M12 connector, 8-pin							
1, 2	5, 6	Signal:	0 V	+V	A	$\bar{A}$	B	$\bar{B}$	$\perp$
		Pin:	1	2	3	4	5	6	PH ³⁾

+V: Supply voltage encoder +V DC
0 V: Supply voltage encoder ground GND (0 V)
A, $\bar{A}$: Cosine signal
B, $\bar{B}$: Sine signal
PH $\perp$: Plug connector housing (shield)

Top view of mating side, male contact base



M12 connector, 8-pin

- 1) Cable version: -30 °C ... +90 °C [-22 °F ... +194 °F] fixed installation.
- 2) Short circuit to 0V or to output, one channel at a time, supply voltage correctly applied.
- 3) PH = shield is attached to connector housing.

Incremental encoders

Standard
sine wave output, highly interpolable, optical

Sendix 5814 / 5834 (shaft / hollow shaft)

SinCos


Dimensions shaft version

Dimensions in mm [inch]

Clamping flange, ø 58 [2.28]

Flange type 1 with shaft type 2
(drawing with cable)

- 1 3 x M3, 6 [0.24] deep
- 2 3 x M4, 8 [0.32] deep



D	Fit	L
10 [0.39]	f7	20 [0.79]


Dimensions hollow shaft version

Dimensions in mm [inch]

Flange with spring element, long

Flange type 1
(drawing with M12 connector)

- 1 Slot spring element, recommendation: cylindrical pin DIN 7, ø 4 [0.16]
- 2 3 x M3, 5.5 [0.22] deep
- 3 Recommended torque for the clamping ring 0.6 Nm



D	Fit
10 [0.39]	H7
12 [0.47]	H7
14 [0.55]	H7
15 [0.59]	H7
3/8"	H7
1/2"	H7

Incremental encoders

Standard
sine wave output, highly interpolable, optical

Sendix 5814 / 5834 (shaft / hollow shaft)

SinCos

Dimensions hollow shaft version

Dimensions in mm [inch]



Flange with stator coupling, $\varnothing 63$ [2.48]

and hollow shaft

Flange type 5

(drawing with M12 connector)

- 1 For (4x) M3 screw
- 2 Recommended torque for the clamping ring 0.6 Nm



D	Fit
10 [0.39]	H7
12 [0.47]	H7
14 [0.55]	H7
15 [0.59]	H7
3/8"	H7
1/2"	H7

Flange with stator coupling, $\varnothing 63$ [2.48]

and tapered shaft

Flange type 5

(drawing with tangential cable outlet)

- 1 For (4x) M3 screw
- 2 Recommended torque for central screw M5 (SW 4) 3.0 ^{+0.5} Nm (tapered shaft)

