










KIT ASSEMBLY 45





General Tolerance UNI EN 22768/1 Media (m)					Sheet:
from 0.5 to 3 ± 0.1	from 3 to 6 ± 0.1	from 6 to 30 ± 0.2	from 30 to 120 ± 0.3	from 120 to 400 ± 0.5	1
Scale:	Drawn:	Checked:	Date:	Material:	Process:
1:1	R.N.	R.N.	07/06/2024	PC/ABS	INJECTION
Derived from:				Weight:	Cod. Mold:
				25.31 gr	ST.10011022
Description: BASE RAILBOX XT VERTICAL BASE RAILBOX XT VERTICAL					Rev.: 01
Drawing nr.: 2_110_00126					A2








SECTION B-B






KIT ASSEMBLY 22.5







SECTION A-A




General Tolerance UNI EN 22768/1 Media (m)					Sheet:
from 0.5 to 3 ± 0.1	from 3 to 6 ± 0.1	from 6 to 30 ± 0.2	from 30 to 120 ± 0.3	from 120 to 400 ± 0.5	2
Scale:	Drawn:	Checked:	Date:	Material:	Process:
1:1	R.N.	R.N.	07/06/2024	PC/ABS	INJECTION
Derived from:				Weight:	Cod. Mold:
				25.31 gr	ST.10011022
Description: BASE RAILBOX XT VERTICAL BASE RAILBOX XT VERTICAL					Rev.:
Drawing nr.: 2_110_00126					01 A2







General Tolerance UNI EN 22768/1 Media (m)					Sheet:	
from 0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	1	
± 0.1	± 0.1	± 0.2	± 0.3	± 0.5		
Scale:	Drawed:	Checked:	Date:	Material:	Process:	
1:1	M.S.	R.N.	01/09/2023	PC	INJECTION	
 Dimension in mm	The present drawing cannot be reproduced or communicated to 3d parties, even partially, without the authorization of ITALTRONIC Srl. Italtronic reserves to protect its own rights according to the law.	Replaces the:	Derived from:	Weight:	Cod. Mold:	
		R-00166-02	--	3.01 gr	ST.1009002	
		Description:				
		SPORTELLLO FRONTALE RAILBOX 17 MM FRONT HINGED TRANSPARENT PANEL 17 MM				
		Drawing nr.:				
 enclosures for electronics italtronic.com					Rev.:	
2_110_00072					00	A4




SECTION A-A





General Tolerance UNI EN 22768/1 Media (m)					Sheet:
from 0.5 to 3 ± 0.1	from 3 to 6 ± 0.1	from 6 to 30 ± 0.2	from 30 to 120 ± 0.3	from 120 to 400 ± 0.5	1
Scale: 1:1	Drawed: M.S.	Checked: R.N.	Date: 09/08/2023	Material: PC/ABS	
 Dimension in mm	The present drawing cannot be reproduced or communicated to 3d parties, even partially, without the authorization of ITALTRONIC Srl. Italtronic reserves to protect its own rights according to the law.	Replaces the: R-00142-00	Derived from: --	Weight: 2.56 gr	Cod. Mold: ST.1009100
Description: PANNELLO INTERNO RAILBOX 17 MM CON SEDI LED INTERNAL PANEL 17MM					
Drawing nr.: 2_110_00043					
Rev.: 00 A4					









KIT ASSEMBLY 22.5



KIT ASSEMBLY 45







General Tolerance UNI EN 22768/1 Media (m)					Sheet:
from 0.5 to 3 ± 0.1	from 3 to 6 ± 0.1	from 6 to 30 ± 0.2	from 30 to 120 ± 0.3	from 120 to 400 ± 0.5	1
Scale: 2:1	Drawed: R.N.	Checked: R.N.	Date: 07/06/2024	Material: PC/ABS	Process: INJECTION
 Dimension in mm		Derived from:		Weight: 0.98 gr	Cod. Mold: ST.10001024
 enclosures for electronics italtronic.com			Description: COPRIFESSURA FRATTURABILE RAILBOX XT VERTICAL HOLE COVER RAILBOX XT VERTICAL BREAKABLE		
Drawing nr.: 2_110_00128					Rev.: 00 A3




KIT ASSEMBLY 22.5





KIT ASSEMBLY 45




General Tolerance UNI EN 22768/1 Media (m)					Sheet:
from 0.5 to 3 ± 0.1	from 3 to 6 ± 0.1	from 6 to 30 ± 0.2	from 30 to 120 ± 0.3	from 120 to 400 ± 0.5	1
Scale: 2:1	Drawed: R.N.	Checked: R.N.	Date: 05/11/2024	Material: PC/ABS	Process: INJECTION
 Dimension in mm	The present drawing cannot be reproduced or communicated to 3d parties, even partially, without the authorization of ITALTRONIC S.r.l. Italtronic reserves to protect its own rights according to the law.	Derived from:	Weight: 1.34 gr	Cod. Mold: ST.10001020	
 enclosures for electronics italtronic.com		Description: GANCIO RAILBOX XT HOOK RAILBOX XT			
Drawing nr.: 2_110_00136				Rev.: 00	A3




SECTION B-B








KIT ASSEMBLY 45



SECTION A-A




General Tolerance UNI EN 22768/1 Media (m)					Sheet:
from 0.5 to 3 ± 0.1	from 3 to 6 ± 0.1	from 6 to 30 ± 0.2	from 30 to 120 ± 0.3	from 120 to 400 ± 0.5	1
Scale:	Drawed:	Checked:	Date:	Material:	Process:
1:1	R.N.	R.N.	07/06/2024	PC/ABS	INJECTION
		Derived from:		Weight:	Cod. Mold:
Dimension in mm				25.65 gr	ST.10031023
 enclosures for electronics italtronic.com			Description: COPERCHIO RAILBOX XT VERTICAL 10 MM COVER RAILBOX XT VERTICAL 10 MM Drawing nr.: 2_110_00127		
			Rev.: 00 A2		




SECTION B-B

KIT ASSEMBLY 22.5



SECTION A-A



General Tolerance UNI EN 22768/1 Media (m)					Sheet:
from 0.5 to 3 ± 0.1	from 3 to 6 ± 0.1	from 6 to 30 ± 0.2	from 30 to 120 ± 0.3	from 120 to 400 ± 0.5	2
Scale:	Drawn:	Checked:	Date:	Material:	Process:
1:1	R.N.	R.N.	07/06/2024	PC/ABS	INJECTION
	The present drawing cannot be reproduced or converted to 3d profiles, even partially, without the written or electronic authorization of Italtronic, to protect its own rights according to the law.		Derived from:	Weight:	Cod. Mold:
Dimension in mm				25.65 gr	ST.10031023
 enclosures for electronics italtronic.com					
Description:					
COPERCHIO RAILBOX XT VERTICAL 10 MM					
COVER RAILBOX XT VERTICAL 10 MM					
Drawing nr.:					Rev.:
2_110_00127					00 A2
3		2		1	