






Rating [A]	Color	Volt [V]	iMaXX Reference
3	Violet	32	FM2003
4	Pink	32	FM2004
5	Tan	32	FM2005
7.5	Brown	32	FM2075
10	Red	32	FM2010
15	Blue	32	FM2015
20	Yellow	32	FM2020
25	Natural	32	FM2025
30	Green	32	FM2030

Fusing time DIN ISO 8820-12 [s]		
Load [%]	Minimum [s]	Maximum [s]
110 %	360,000	-
135 %	0.75	600
160 %	0.25	50
200 %	0.15	5
350 %	0.04	0.5
600 %	0.02	0.1

Notes	
Body	PA66, color coded with OCR printed rating
OCR print	White print on all ratings except 4, 20 & 25 A.
	OCR on 20 & 25 A fuses printed in black
Element	Zinc alloy, silver plated blades

Revisions			Date	Appr.	
	Date	Type	Drawn	04/13	GRH
a	03/16	fuse blade shape updated	Checked	07/20	BE
b	06/20	ISO norm updated	Standards		
c	07/20	added 3 & 4A ratings	Approved	07/20	AdH
			Scale	4 : 1	
			Projection	Tolerance ± 0.2 mm unless otherwise noted	
					Title
					Drawing type
					Drawing number
					Sheet
					Layers / Sheet



FM2000 series, mikrOTO blade fuse			
schematic			
FM2000 drawing 1			
1 of 1			
01	2	6	9

Sheet 01