






- A Fusing element material Zn
 B Nominal voltage stamped
 S Dimension varies with current rating

ELED ref.	RATING [A]	VOLTAGE [V]
MSU030	30	32
MSU040	40	32
MSU050	50	32
MSU060	60	32
MSU080	80	32
MSU100	100	32

FUSING TIME DIN 72581-3		
LOAD [%]	MIN [s]	MAX [s]
130	360.000	-
250	-	60

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN MILLIMETERS
 SURFACE FINISH:
 TOLERANCES: 0,2
 LINEAR:
 ANGULAR:

FINISH:

DEBUR AND
 BREAK SHARP
 EDGES

DO NOT SCALE DRAWING

REVISION

ELED® On the safe side

	NAME	SIGNATURE	DATE		
DRAWN	B.D.		12.2024		
CHK'D	R.J.		12.2024		
APPV'D	B.D.		12.2024		
MFG	www.eled.si				
Q.A				MATERIAL:	
				WEIGHT:	

TITLE:

MSU strip fuses family

DWG NO.

MSU

A4

SCALE:2:1

SHEET 1 OF 1