


P.C. MOUNTING




O.P. (MM)	P.T. (MM)
9.1 ± 0.8	3.6 MAX

O.P. = OPERATING POINT
P.T. = PER-TRAVEL



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X±0.4
X.XX±0.25
3. RATING: 5A @125/250VAC UL, CUL
- ▲ 4. OPERATING FORCE: 25±12 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS
9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 mΩ MAX.
11. ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY
E	ECO-100768	REMOVE VDE RATING AND LOGO	03/08/22	JS



E-SWITCH®

OBJECT ID
000021155

TITLE
MS0850501F025V1A

SCALE
2:1

DATE
6/30/2005

DR
JB

DWG
Q970017

REV
E

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED