



序号/RevNo.	名称/Title	文件编号/File No.
1	XY167V 塑件	QJ/XYT-2123101
2	XY305V 端子	QJ/XYT-2126101
3	XY305 簧片	QJ/XYT-2126102
4	XY167 螺丝	QJ/XYT-2123102



300V 15A 2.5mm²
Poles: 2,3-12P
Pitch: 5.0mm(.197")

Materials

Housing: PA66(UL 94V-0)
Solder Pin: Brass,Tin Plated.
Clamping: Stainless steel
Screw: M2.5,steel(A3),Zinc Plated
Torque: 0.4N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance	
 新莱亚电子 XINLAIYA ELECTRONIC CO.,LTD		图名/Title	文件编号/File No.	X. ± 0.2	X." ± 2°
		XY167V-5.0	QJ/XYT-2223100	.X ± 0.1	.X" ± 1°
		产品图	页序/Sheet	.XX ± 0.05	.XX" ± 0.5°
		备注/Remark		.XXX ± 0.01	
				单位/Units: mm	

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------