

Insulated cord end terminals, HI...ERHL type

FEATURES & BENEFITS

-  thin-walled cord end terminal Cu, with insulation sleeve, for multi-wire flexible cables
-  insulating sleeve: enhances resistance to vibrations, mitigates short-circuit risk, facilitates cable installation
-  insulation colours facilitate cross-section identification

MECHANICAL DATA

Insulation	polypropylene
Material	Cu
Halogen-free	yes
Surface	tin-plated
Operating temperature [°C]	-30 ÷ +105


CERTIFICATES & STANDARDS

UL certificate	E493579 (according to table in the technical data sheet)
Design	DIN 46228/4 (according to table in the technical data sheet)
Świadectwo uznania typu PRS	TE/1137/880567/25

NOTE!

Other lengths and colours on request.

UL certificate - for up-to-date information, visit www.ergom.com



Type	Index Ergom	Cross-section [mm²]	AWG cross-section	L ₁	L ₂	d ₁	d ₂	s ₁	s ₂	Insulation colour	DIN	UL	Quantity in package [pcs]	Weight [kg]
HI 0,14/6 ERHL (500 PCS)	E08KH-02010100100	0,14	26	10	6	0,70	1,6	0,15	0,25	grey	—	—	500	0,02
HI 0,14/6 ERHL (100 PCS)	E08KH-02010100102	0,14	26	10	6	0,70	1,6	0,15	0,25	grey	—	—	100	0,01
HI 0,14/6 F ERHL (500 PCS)	E08KH-02010100201	0,14	26	10	6	0,70	1,6	0,15	0,25	brown	—	—	500	0,02
HI 0,14/6 F ERHL (100 PCS)	E08KH-02010110201	0,14	26	10	6	0,70	1,6	0,15	0,25	brown	—	—	100	0,01
HI 0,14/8 ERHL (500 PCS)	E08KH-02010100151	0,14	26	12	8	0,70	1,6	0,15	0,25	grey	—	—	500	0,02
HI 0,14/8 ERHL (100 PCS)	E08KH-02010100153	0,14	26	12	8	0,70	1,6	0,15	0,25	grey	—	—	100	0,01
HI 0,14/8 F ERHL (500 PCS)	E08KH-02010100251	0,14	26	12	8	0,70	1,6	0,15	0,25	brown	—	—	500	0,02
HI 0,14/8 F ERHL (100 PCS)	E08KH-02010100253	0,14	26	12	8	0,70	1,6	0,15	0,25	brown	—	—	100	0,01
HI 0,25/6 ERHL (500 PCS)	E08KH-02010100301	0,25	24	10	6	0,75	1,8	0,15	0,25	blue	—	—	500	0,03
HI 0,25/6 ERHL (100 PCS)	E08KH-02010110301	0,25	24	10	6	0,75	1,8	0,15	0,25	blue	—	—	100	0,01
HI 0,25/6 DIN ERHL (500 PCS)	E08KH-02010100401	0,25	24	10	6	0,75	1,8	0,15	0,25	yellow	—	—	500	0,03
HI 0,25/6 DIN ERHL (100 PCS)	E08KH-02010110401	0,25	24	10	6	0,75	1,8	0,15	0,25	yellow	—	—	100	0,01
HI 0,25/6 F ERHL (500 PCS)	E08KH-02010100501	0,25	24	10	6	0,75	1,8	0,15	0,25	violet	—	—	500	0,03
HI 0,25/6 F ERHL (100 PCS)	E08KH-02010110501	0,25	24	10	6	0,75	1,8	0,15	0,25	violet	—	—	100	0,01
HI 0,25/8 DIN ERHL (500 PCS)	E08KH-02010100701	0,25	24	12	8	0,75	1,8	0,15	0,25	yellow	—	—	500	0,03
HI 0,25/8 DIN ERHL (100 PCS)	E08KH-02010110701	0,25	24	12	8	0,75	1,8	0,15	0,25	yellow	—	—	100	0,01
HI 0,25/8 F ERHL (100 PCS)	E08KH-02010110801	0,25	24	12	8	0,75	1,8	0,15	0,25	violet	—	—	100	0,01
HI 0,25/8 ERHL (500 PCS)	E08KH-02010100601	0,25	24	12	8	0,75	1,8	0,15	0,25	blue	—	—	500	0,03
HI 0,25/8 ERHL (100 PCS)	E08KH-02010110601	0,25	24	12	8	0,75	1,8	0,15	0,25	blue	—	—	100	0,01
HI 0,34/6 ERHL (500 PCS)	E08KH-02010100901	0,34	22	10	6	0,80	2,0	0,15	0,25	turquoise	—	—	500	0,03
HI 0,34/6 ERHL (100 PCS)	E08KH-02010110901	0,34	22	10	6	0,80	2,0	0,15	0,25	turquoise	—	—	100	0,01
HI 0,34/6 F ERHL (500 PCS)	E08KH-02010101001	0,34	22	10	6	0,80	2,0	0,15	0,25	rose	—	—	500	0,03
HI 0,34/6 F ERHL (100 PCS)	E08KH-02010111001	0,34	22	10	6	0,80	2,0	0,15	0,25	rose	—	—	100	0,01
HI 0,34/8 ERHL (500 PCS)	E08KH-02010101101	0,34	22	12	8	0,80	2,0	0,15	0,25	turquoise	—	—	500	0,03
HI 0,34/8 ERHL (100 PCS)	E08KH-02010111201	0,34	22	12	8	0,80	2,0	0,15	0,25	turquoise	—	—	100	0,01
HI 0,34/8 F ERHL (500 PCS)	E08KH-02010101201	0,34	22	12	8	0,80	2,0	0,15	0,25	rose	—	—	500	0,03
HI 0,34/8 F ERHL (100 PCS)	E08KH-02010111101	0,34	22	12	8	0,80	2,0	0,15	0,25	rose	—	—	100	0,01
HI 0,5/6 ERHL (500 PCS)	E08KH-02010101301	0,5	20	12	6	1,00	2,6	0,15	0,25	orange	—	—	500	0,04

Type	Index Ergom	Cross-section [mm ²]	AWG cross-section	L ₁	L ₂	d ₁	d ₂	s ₁	s ₂	Insulation colour	DIN	UL	Quantity in package [pcs]	Weight [kg]
HI 0,5/6 ERHL (100 PCS)	E08KH-02010111301	0,5	20	12	6	1,00	2,6	0,15	0,25	orange	—	—	100	0,01
HI 0,5/6 DIN ERHL (500 PCS)	E08KH-02010101401	0,5	20	12	6	1,00	2,6	0,15	0,25	white	✓	—	500	0,04
HI 0,5/6 DIN ERHL (100 PCS)	E08KH-02010111401	0,5	20	12	6	1,00	2,6	0,15	0,25	white	✓	—	100	0,01
HI 0,5/8 ERHL (500 PCS)	E08KH-02010101501	0,5	20	14	8	1,00	2,6	0,15	0,25	orange	—	—	500	0,04
HI 0,5/8 ERHL (100 PCS)	E08KH-02010111521	0,5	20	14	8	1,00	2,6	0,15	0,25	orange	—	—	100	0,01
HI 0,5/8 DIN ERHL (500 PCS)	E08KH-02010101601	0,5	20	14	8	1,00	2,6	0,15	0,25	white	✓	—	500	0,04
HI 0,5/8 DIN ERHL (100 PCS)	E08KH-02010111621	0,5	20	14	8	1,00	2,6	0,15	0,25	white	✓	—	100	0,01
HI 0,5/10 ERHL (500 PCS)	E08KH-02010101701	0,5	20	16	10	1,00	2,6	0,15	0,25	orange	—	—	500	0,04
HI 0,5/10 ERHL (100 PCS)	E08KH-02010111701	0,5	20	16	10	1,00	2,6	0,15	0,25	orange	—	—	100	0,01
HI 0,5/10 DIN ERHL (500 PCS)	E08KH-02010101801	0,5	20	16	10	1,00	2,6	0,15	0,25	white	✓	—	500	0,04
HI 0,5/10 DIN ERHL (100 PCS)	E08KH-02010111801	0,5	20	16	10	1,00	2,6	0,15	0,25	white	✓	—	100	0,01
HI 0,75/6 ERHL (500 PCS)	E08KH-02010101900	0,75	18	12	6	1,20	2,8	0,15	0,25	white	—	—	500	0,04
HI 0,75/6 ERHL (100 PCS)	E08KH-02010101902	0,75	18	12	6	1,20	2,8	0,15	0,25	white	—	—	100	0,01
HI 0,75/6 DIN ERHL (500 PCS)	E08KH-02010102001	0,75	18	12	6	1,20	2,8	0,15	0,25	grey	✓	—	500	0,04
HI 0,75/6 DIN ERHL (100 PCS)	E08KH-02010112001	0,75	18	12	6	1,20	2,8	0,15	0,25	grey	✓	—	100	0,01
HI 0,75/6 F ERHL (500 PCS)	E08KH-02010102101	0,75	18	12	6	1,20	2,8	0,15	0,25	blue	—	—	500	0,04
HI 0,75/6 F ERHL (100 PCS)	E08KH-02010112101	0,75	18	12	6	1,20	2,8	0,15	0,25	blue	—	—	100	0,01
HI 0,75/8 ERHL (500 PCS)	E08KH-02010102201	0,75	18	14	8	1,20	2,8	0,15	0,25	white	—	—	500	0,04
HI 0,75/8 ERHL (100 PCS)	E08KH-02010102202	0,75	18	14	8	1,20	2,8	0,15	0,25	white	—	—	100	0,01
HI 0,75/8 DIN ERHL (500 PCS)	E08KH-02010102300	0,75	18	14	8	1,20	2,8	0,15	0,25	grey	✓	✓	500	0,04
HI 0,75/8 DIN ERHL (100 PCS)	E08KH-02010102302	0,75	18	14	8	1,20	2,8	0,15	0,25	grey	✓	✓	100	0,01
HI 0,75/8 F ERHL (500 PCS)	E08KH-02010102401	0,75	18	14	8	1,20	2,8	0,15	0,25	blue	—	—	500	0,04
HI 0,75/8 F ERHL (100 PCS)	E08KH-02010112401	0,75	18	14	8	1,20	2,8	0,15	0,25	blue	—	—	100	0,01
HI 0,75/10 ERHL (500 PCS)	E08KH-02010102501	0,75	18	16	10	1,20	2,8	0,15	0,25	white	—	—	500	0,05
HI 0,75/10 ERHL (100 PCS)	E08KH-02010112501	0,75	18	16	10	1,20	2,8	0,15	0,25	white	—	—	100	0,01
HI 0,75/10 DIN ERHL (500 PCS)	E08KH-02010102601	0,75	18	16	10	1,20	2,8	0,15	0,25	grey	✓	—	500	0,05
HI 0,75/10 DIN ERHL (100 PCS)	E08KH-02010112601	0,75	18	16	10	1,20	2,8	0,15	0,25	grey	✓	—	100	0,01
HI 0,75/10 F ERHL (500 PCS)	E08KH-02010102701	0,75	18	16	10	1,20	2,8	0,15	0,25	blue	—	—	500	0,05
HI 0,75/10 F ERHL (100 PCS)	E08KH-02010112701	0,75	18	16	10	1,20	2,8	0,15	0,25	blue	—	—	100	0,01
HI 0,75/12 ERHL (500 PCS)	E08KH-02010102801	0,75	18	18	12	1,20	2,8	0,15	0,25	white	—	—	500	0,05
HI 0,75/12 ERHL (100 PCS)	E08KH-02010112801	0,75	18	18	12	1,20	2,8	0,15	0,25	white	—	—	100	0,01
HI 0,75/12 DIN ERHL (500 PCS)	E08KH-02010102901	0,75	18	18	12	1,20	2,8	0,15	0,25	grey	✓	—	500	0,05
HI 0,75/12 DIN ERHL (100 PCS)	E08KH-02010112901	0,75	18	18	12	1,20	2,8	0,15	0,25	grey	✓	—	100	0,01
HI 0,75/12 F ERHL (500 PCS)	E08KH-02010103001	0,75	18	18	12	1,20	2,8	0,15	0,25	blue	—	—	500	0,05
HI 0,75/12 F ERHL (100 PCS)	E08KH-02010113001	0,75	18	18	12	1,20	2,8	0,15	0,25	blue	—	—	100	0,01
HI 1/6 ERHL (500 PCS)	E08KH-02010103100	1	18	12	6	1,40	3,0	0,15	0,25	yellow	—	—	500	0,05
HI 1/6 ERHL (100 PCS)	E08KH-02010103102	1	18	12	6	1,40	3,0	0,15	0,25	yellow	—	—	100	0,01
HI 1/6 DIN ERHL (500 PCS)	E08KH-02010103200	1	18	12	6	1,40	3,0	0,15	0,25	red	✓	✓	500	0,05
HI 1/6 DIN ERHL (100 PCS)	E08KH-02010103202	1	18	12	6	1,40	3,0	0,15	0,25	red	✓	✓	100	0,01
HI 1/8 ERHL (500 PCS)	E08KH-02010103300	1	18	14	8	1,40	3,0	0,15	0,25	yellow	—	—	500	0,05
HI 1/8 ERHL (100 PCS)	E08KH-02010103302	1	18	14	8	1,40	3,0	0,15	0,25	yellow	—	—	100	0,01
HI 1/8 DIN ERHL (500 PCS)	E08KH-02010103400	1	18	14	8	1,40	3,0	0,15	0,25	red	✓	✓	500	0,05
HI 1/8 DIN ERHL (100 PCS)	E08KH-02010103402	1	18	14	8	1,40	3,0	0,15	0,25	red	✓	✓	100	0,01
HI 1/10 ERHL (500 PCS)	E08KH-02010103500	1	18	16	10	1,40	3,0	0,15	0,25	yellow	—	—	500	0,06
HI 1/10 ERHL (100 PCS)	E08KH-02010103502	1	18	16	10	1,40	3,0	0,15	0,25	yellow	—	—	100	0,02
HI 1/10 DIN ERHL (500 PCS)	E08KH-02010103600	1	18	16	10	1,40	3,0	0,15	0,25	red	✓	✓	500	0,06
HI 1/10 DIN ERHL (100 PCS)	E08KH-02010103602	1	18	16	10	1,40	3,0	0,15	0,25	red	✓	✓	100	0,02
HI 1/12 ERHL (500 PCS)	E08KH-02010103700	1	18	18	12	1,40	3,0	0,15	0,25	yellow	—	—	500	0,06
HI 1/12 ERHL (100 PCS)	E08KH-02010103702	1	18	18	12	1,40	3,0	0,15	0,25	yellow	—	—	100	0,02
HI 1/12 DIN ERHL (500 PCS)	E08KH-02010103800	1	18	18	12	1,40	3,0	0,15	0,25	red	✓	✓	500	0,06
HI 1/12 DIN ERHL (100 PCS)	E08KH-02010103802	1	18	18	12	1,40	3,0	0,15	0,25	red	✓	✓	100	0,02
HI 1,5/6 DIN ERHL (500 PCS)	E08KH-02010103901	1,5	16	12	6	1,70	3,5	0,15	0,25	black	—	—	500	0,07
HI 1,5/8 ERHL (500 PCS)	E08KH-02010104000	1,5	16	14	8	1,70	3,5	0,15	0,25	red	—	—	500	0,08
HI 1,5/8 ERHL (100 PCS)	E08KH-02010104002	1,5	16	14	8	1,70	3,5	0,15	0,25	red	—	—	100	0,02
HI 1,5/8 DIN ERHL (500 PCS)	E08KH-02010104100	1,5	16	14	8	1,70	3,5	0,15	0,25	black	✓	✓	500	0,08
HI 1,5/8 DIN ERHL (100 PCS)	E08KH-02010104102	1,5	16	14	8	1,70	3,5	0,15	0,25	black	✓	✓	100	0,02
HI 1,5/10 ERHL (500 PCS)	E08KH-02010104200	1,5	16	16	10	1,70	3,5	0,15	0,25	red	—	—	500	0,09
HI 1,5/10 ERHL (100 PCS)	E08KH-02010104202	1,5	16	16	10	1,70	3,5	0,15	0,25	red	—	—	100	0,02
HI 1,5/10 DIN ERHL (500 PCS)	E08KH-02010104300	1,5	16	16	10	1,70	3,5	0,15	0,25	black	✓	✓	500	0,09
HI 1,5/10 DIN ERHL (100 PCS)	E08KH-02010104302	1,5	16	16	10	1,70	3,5	0,15	0,25	black	✓	✓	100	0,02
HI 1,5/12 ERHL (500 PCS)	E08KH-02010104400	1,5	16	18	12	1,70	3,5	0,15	0,25	red	—	—	500	0,09
HI 1,5/12 ERHL (100 PCS)	E08KH-02010104402	1,5	16	18	12	1,70	3,5	0,15	0,25	red	—	—	100	0,02
HI 1,5/12 DIN ERHL (500 PCS)	E08KH-02010104500	1,5	16	18	12	1,70	3,5	0,15	0,25	black	✓	✓	500	0,09

Type	Index Ergom	Cross-section [mm ²]	AWG cross-section	L ₁	L ₂	d ₁	d ₂	s ₁	s ₂	Insulation colour	DIN	UL	Quantity in package [pcs]	Weight [kg]
HI 1,5/12 DIN ERHL (100 PCS)	E08KH-02010104502	1,5	16	18	12	1,70	3,5	0,15	0,25	black	✓	✓	100	0,02
HI 1,5/18 ERHL (100 PCS)	E08KH-02010114501	1,5	16	24	18	1,70	3,5	0,15	0,25	red	–	–	100	0,02
HI 1,5/18 ERHL (500 PCS)	E08KH-02010104601	1,5	16	24	18	1,70	3,5	0,15	0,25	red	–	–	500	0,1
HI 1,5/18 DIN ERHL (500 PCS)	E08KH-02010104701	1,5	16	24	18	1,70	3,5	0,15	0,25	black	✓	–	500	0,1
HI 1,5/18 DIN ERHL (100 PCS)	E08KH-02010114601	1,5	16	24	18	1,70	3,5	0,15	0,25	black	✓	–	100	0,02
HI 2,5/8 ERHL (500 PCS)	E08KH-02010104900	2,5	14	14	8	2,20	4,2	0,15	0,25	blue	✓	✓	500	0,08
HI 2,5/8 ERHL (100 PCS)	E08KH-02010104902	2,5	14	14	8	2,20	4,2	0,15	0,25	blue	✓	✓	100	0,02
HI 2,5/8 F ERHL (500 PCS)	E08KH-02010104800	2,5	14	14	8	2,20	4,2	0,15	0,25	grey	–	–	500	0,08
HI 2,5/8 F ERHL (100 PCS)	E08KH-02010104802	2,5	14	14	8	2,20	4,2	0,15	0,25	grey	–	–	100	0,02
HI 2,5/10 ERHL (500 PCS)	E08KH-02010105000	2,5	14	16	10	2,20	4,2	0,15	0,25	blue	–	–	500	0,09
HI 2,5/10 ERHL (100 PCS)	E08KH-02010105002	2,5	14	16	10	2,20	4,2	0,15	0,25	blue	–	–	100	0,02
HI 2,5/10 F ERHL (500 PCS)	E08KH-02010105100	2,5	14	16	10	2,20	4,2	0,15	0,25	grey	–	–	500	0,09
HI 2,5/10 F ERHL (100 PCS)	E08KH-02010105102	2,5	14	16	10	2,20	4,2	0,15	0,25	grey	–	–	100	0,02
HI 2,5/12 ERHL (500 PCS)	E08KH-02010105200	2,5	14	18	12	2,20	4,2	0,15	0,25	blue	✓	✓	500	0,1
HI 2,5/12 ERHL (100 PCS)	E08KH-02010105202	2,5	14	18	12	2,20	4,2	0,15	0,25	blue	✓	✓	100	0,02
HI 2,5/12 F ERHL (500 PCS)	E08KH-02010105300	2,5	14	18	12	2,20	4,2	0,15	0,25	grey	–	–	500	0,1
HI 2,5/12 F ERHL (100 PCS)	E08KH-02010105302	2,5	14	18	12	2,20	4,2	0,15	0,25	grey	–	–	100	0,02
HI 2,5/18 ERHL (500 PCS)	E08KH-02010105401	2,5	14	24	18	2,20	4,2	0,15	0,25	blue	✓	✓	500	0,12
HI 2,5/18 ERHL (100 PCS)	E08KH-02010115301	2,5	14	24	18	2,20	4,2	0,15	0,25	blue	✓	✓	100	0,03
HI 2,5/18 F ERHL (500 PCS)	E08KH-02010105501	2,5	14	24	18	2,20	4,2	0,15	0,25	grey	–	–	500	0,12
HI 2,5/18 F ERHL (100 PCS)	E08KH-02010115401	2,5	14	24	18	2,20	4,2	0,15	0,25	grey	–	–	100	0,03
HI 4/10 ERHL (500 PCS)	E08KH-02010105600	4	12	17	10	2,80	4,8	0,20	0,30	grey	✓	✓	500	0,13
HI 4/10 ERHL (100 PCS)	E08KH-02010105602	4	12	17	10	2,80	4,8	0,20	0,30	grey	✓	✓	100	0,03
HI 4/10 F ERHL (500 PCS)	E08KH-02010105700	4	12	17	10	2,80	4,8	0,20	0,30	orange	–	–	500	0,13
HI 4/10 F ERHL (100 PCS)	E08KH-02010105702	4	12	17	10	2,80	4,8	0,20	0,30	orange	–	–	100	0,03
HI 4/12 ERHL (500 PCS)	E08KH-02010105800	4	12	20	12	2,80	4,8	0,20	0,30	grey	✓	✓	500	0,14
HI 4/12 ERHL (100 PCS)	E08KH-02010105802	4	12	20	12	2,80	4,8	0,20	0,30	grey	✓	✓	100	0,03
HI 4/12 F ERHL (500 PCS)	E08KH-02010105900	4	12	20	12	2,80	4,8	0,20	0,30	orange	–	–	500	0,14
HI 4/12 F ERHL (100 PCS)	E08KH-02010105902	4	12	20	12	2,80	4,8	0,20	0,30	orange	–	–	100	0,04
HI 4/18 ERHL (500 PCS)	E08KH-02010106000	4	12	26	18	2,80	4,8	0,20	0,30	grey	✓	✓	500	0,19
HI 4/18 ERHL (100 PCS)	E08KH-02010106002	4	12	26	18	2,80	4,8	0,20	0,30	grey	✓	✓	100	0,04
HI 4/18 F ERHL (500 PCS)	E08KH-02010106101	4	12	26	18	2,80	4,8	0,20	0,30	orange	–	–	500	0,19
HI 4/18 F ERHL (100 PCS)	E08KH-02010116001	4	12	26	18	2,80	4,8	0,20	0,30	orange	–	–	100	0,04
HI 6/10 ERHL (100 PCS)	E08KH-02010106131	6	10	18	10	3,50	6,3	0,20	0,30	black	–	–	100	0,04
HI 6/10 DIN ERHL (100 PCS)	E08KH-02010106151	6	10	18	10	3,50	6,3	0,20	0,30	yellow	–	–	100	0,04
HI 6/10 F ERHL (100 PCS)	E08KH-02010106181	6	10	18	10	3,50	6,3	0,20	0,30	green	–	–	100	0,04
HI 6/12 ERHL (100 PCS)	E08KH-02010106200	6	10	20	12	3,50	6,3	0,20	0,30	black	–	–	100	0,04
HI 6/12 DIN ERHL (100 PCS)	E08KH-02010106300	6	10	20	12	3,50	6,3	0,20	0,30	yellow	✓	✓	100	0,04
HI 6/12 F ERHL (100 PCS)	E08KH-02010106400	6	10	20	12	3,50	6,3	0,20	0,30	green	–	–	100	0,04
HI 6/15 ERHL (100 PCS)	E08KH-02010106440	6	10	23	15	3,50	6,3	0,20	0,30	black	–	–	100	0,05
HI 6/15 F ERHL (100 PCS)	E08KH-02010106480	6	10	23	15	3,50	6,3	0,20	0,30	green	–	–	100	0,05
HI 6/18 ERHL (100 PCS)	E08KH-02010106500	6	10	26	18	3,50	6,3	0,20	0,30	black	–	–	100	0,06
HI 6/18 DIN ERHL (100 PCS)	E08KH-02010106600	6	10	26	18	3,50	6,3	0,20	0,30	yellow	✓	✓	100	0,06
HI 6/18 F ERHL (100 PCS)	E08KH-02010106701	6	10	26	18	3,50	6,3	0,20	0,30	green	–	–	100	0,06
HI 10/12 ERHL (100 PCS)	E08KH-02010106800	10	8	22	12	4,50	7,6	0,20	0,40	ivory	–	–	100	0,06
HI 10/12 DIN ERHL (100 PCS)	E08KH-02010106900	10	8	22	12	4,50	7,6	0,20	0,40	red	✓	✓	100	0,06
HI 10/12 F ERHL (100 PCS)	E08KH-02010107001	10	8	22	12	4,50	7,6	0,20	0,40	brown	–	–	100	0,06
HI 10/15 ERHL (100 PCS)	E08KH-02010107101	10	8	24	15	4,50	7,3	0,20	0,60	ivory	–	–	100	0,07
HI 10/15 DIN ERHL (100 PCS)	E08KH-02010107201	10	8	24	15	4,50	7,3	0,20	0,60	red	–	–	100	0,07
HI 10/15 F ERHL (100 PCS)	E08KH-02010107301	10	8	24	15	4,50	7,3	0,20	0,60	brown	–	–	100	0,07
HI 10/18 ERHL (100 PCS)	E08KH-02010107400	10	8	28	18	4,50	7,6	0,20	0,40	ivory	–	–	100	0,07
HI 10/18 DIN ERHL (100 PCS)	E08KH-02010107500	10	8	28	18	4,50	7,6	0,20	0,40	red	✓	✓	100	0,07
HI 10/18 F ERHL (100 PCS)	E08KH-02010107601	10	8	28	18	4,50	7,6	0,20	0,40	brown	–	–	100	0,07
HI 16/12 ERHL (100 PCS)	E08KH-02010107700	16	6	24	12	5,80	8,8	0,20	0,40	green	–	–	100	0,07
HI 16/12 DIN ERHL (100 PCS)	E08KH-02010107800	16	6	24	12	5,80	8,8	0,20	0,40	blue	✓	✓	100	0,07
HI 16/12 F ERHL (100 PCS)	E08KH-02010107900	16	6	24	12	5,80	8,8	0,20	0,40	ivory	–	–	100	0,07
HI 16/18 ERHL (100 PCS)	E08KH-02010108000	16	6	28	18	5,80	8,8	0,20	0,40	green	–	–	100	0,09
HI 16/18 DIN ERHL (100 PCS)	E08KH-02010108100	16	6	28	18	5,80	8,8	0,20	0,40	blue	✓	✓	100	0,09
HI 16/18 F ERHL (100 PCS)	E08KH-02010108201	16	6	28	18	5,80	8,8	0,20	0,40	ivory	–	–	100	0,09
HI 25/16 ERHL (50 PCS)	E08KH-02010108300	25	4	30	16	7,30	11,2	0,20	0,40	brown	–	–	50	0,06
HI 25/16 DIN ERHL (50 PCS)	E08KH-02010108400	25	4	30	16	7,30	11,2	0,20	0,40	yellow	✓	✓	50	0,06
HI 25/16 F ERHL (50 PCS)	E08KH-02010108500	25	4	30	16	7,30	11,2	0,20	0,40	black	–	–	50	0,06
HI 25/22 ERHL (50 PCS)	E08KH-02010108600	25	4	36	22	7,30	11,2	0,20	0,40	brown	–	–	50	0,08

Type	Index Ergom	Cross-section [mm²]	AWG cross-section	L ₁	L ₂	d ₁	d ₂	s ₁	s ₂	Insulation colour	DIN	UL	Quantity in package [pcs]	Weight [kg]
HI 25/22 DIN ERHL (50 PCS)	E08KH-02010108700	25	4	36	22	7,30	11,2	0,20	0,40	yellow	✓	–	50	0,08
HI 25/22 F ERHL (50 PCS)	E08KH-02010108801	25	4	36	22	7,30	11,2	0,20	0,40	black	–	–	50	0,08
HI 35/16 ERHL (50 PCS)	E08KH-02010108900	35	2	30	16	8,30	12,7	0,20	0,40	beige	–	–	50	0,07
HI 35/16 DIN ERHL (50 PCS)	E08KH-02010109000	35	2	30	16	8,30	12,7	0,20	0,40	red	✓	–	50	0,07
HI 35/18 ERHL (50 PCS)	E08KH-02010109031	35	2	30	18	8,30	12,7	0,20	0,40	beige	–	–	50	0,08
HI 35/18 DIN ERHL (50 PCS)	E08KH-02010109051	35	2	30	18	8,30	12,7	0,20	0,40	red	✓	–	50	0,08
HI 35/25 ERHL (50 PCS)	E08KH-02010109100	35	2	39	25	8,30	12,7	0,20	0,40	beige	–	–	50	0,09
HI 35/25 DIN ERHL (50 PCS)	E08KH-02010109200	35	2	39	25	8,30	12,7	0,20	0,40	red	✓	–	50	0,09
HI 50/20 ERHL (50 PCS)	E08KH-02010109300	50	1	36	20	10,30	15,0	0,30	0,50	olive	–	–	50	0,14
HI 50/20 DIN ERHL (50 PCS)	E08KH-02010109400	50	1	36	20	10,30	15,0	0,30	0,50	blue	✓	–	50	0,14
HI 50/25 ERHL (50 PCS)	E08KH-02010109500	50	1	40	25	10,30	15,0	0,30	0,50	olive	–	–	50	0,16
HI 50/25 DIN ERHL (50 PCS)	E08KH-02010109600	50	1	40	25	10,30	15,0	0,30	0,50	blue	✓	–	50	0,16
HI 70/20 ERHL (50 PCS)	E08KH-02010109700	70	2/0	37	20	13,50	16,0	0,40	0,60	yellow	–	–	50	0,2
HI 95/25 ERHL (25 PCS)	E08KH-02010109800	95	3/0	44	25	14,50	18,0	0,40	0,60	red	–	–	25	0,14
HI 120/27 ERHL (25 PCS)	E08KH-02010109900	120	4/0	48	27	16,50	20,0	0,45	0,70	blue	–	–	25	0,22
HI 150/32 ERHL (25 PCS)	E08KH-02010110000	150	300 MCM	58	32	19,50	23,0	0,50	1,00	yellow	–	–	25	0,29