



## MSE Receptacle

for multi-wire Cu cables



With copper tube and polyamid insulation

Thermal resistance: -40°C to +125°C

Material: brass

According to DIN 46245

| Nominal wire cross section [mm <sup>2</sup> ] | Cross section [mm <sup>2</sup> ] | Symbol    | b [mm] | $I_1$ [mm] | $I_2$ [mm] | $d_1$ [mm] | $a_{min}$ [mm] | $d_2$ [mm] | $d_3$ [mm] | Weight [g/pce] | Unit [pcs] | Crimping tools             |
|-----------------------------------------------|----------------------------------|-----------|--------|------------|------------|------------|----------------|------------|------------|----------------|------------|----------------------------|
| 1                                             | > 0,5 ÷ 1                        | MSE 6,3-1 | 0,8    | 21         | 7,5        | 6,7        | 4,5            | 1,6        | 3,2        | 0,92           | 100        | PR33,E11-6, RE6, PP8, PP19 |
| 2,5                                           | > 1 ÷ 2,5                        | MSE 6,3-2 | 0,8    | 21         | 7,5        | 6,7        | 4,5            | 2,3        | 3,8        | 1,09           | 100        |                            |
| 6                                             | > 2,5 ÷ 6                        | MSE 6,3-6 | 0,8    | 21         | 7,5        | 6,7        | 4,5            | 3,4        | 5,5        | 1,49           | 100        |                            |

Standard production –tinned.

VO class insulation on request – symbol e.g. MSE 6,3-1-VO.