

PRODUCT DATA SHEET

3903

Receptacles insulated – 3903 Ms sn PVC rot 6.3x0.8



Product Overview

SKU	3903
Part description	Receptacles insulated
Part designation	3903 Ms sn PVC rot 6.3x0.8

Material

Component	Brass
Surface	pure tin-plated
Insulationmaterial / Colour	PVC / red

Technical Details


Net weight kg/1000	0.970
Conductor cross-section	0.5 – 1.5mm ² / AWG 22-16
Temperatur resistance	up to 105°C (600V max.)
Maximum electrical rating AWG22	3A
Maximum electrical rating AWG20	4A
Maximum electrical rating AWG18	7A
Maximum electrical rating AWG16	10A

Marking

Approved UL	E235796
UL Standard / Flammability class	UL94 / V-0

Dimensions

L [mm]	21.00
A [mm]	10.50
D [mm]	1.70



© 2022 | Vogt AG Verbindungstechnik

The general conditions of sale of Vogt AG apply to this product. See www.vogt.ch/downloads.

This data sheet is regularly revised but is not subject to any change service.

This article is a freely available article according to the above specification. The availability of certificates according to EN 10204, others acceptance test certificates or material compliance and customer-specific part submission warrant, are to be requested by the customer and, if available, can be obtained for a fee.

You can find more information on the free available product conformities at www.vogt.ch/downloads.

Form checked and approved special field: 17.02.2022 haatob
Form created: 17.02.2022 haatob

PDS_3903_EN_V1
Content created: 13.03.23 karlea / Version: 01

Page 1 / 1
PM-FO-03 / Version: 00

Vogt AG Verbindungstechnik
+41 62 285 75 75

Duschletenstrasse 2 – 4
info@vogt.ch

4654 Lostorf / Switzerland
www.vogt.ch