


SMD Transient Voltage Suppressor Diodes

Primary characteristics		
Parameter	Value	Unit
V_R breakdown voltage	6.8 to 550	V
Peak power	600	W

Features

- **SMB (DO-214AA)** case for easy automatic insertion.
- Pb-free and **RoHS** compliant
- Approx. weight: 0.095g / 0.003oz
- Built-in strain relief
- Glass passivated junction
- Low inductance
- Excellent clamping capability
- Fast response time
- Solderable per MIL-STD-750, Method 2026
- Typical IR less than 1 μ A above 12V
- High temperature soldering: 260°C/40 seconds at terminals
- Plastic package has underwriters laboratory flammability 94V-0

Case dimensions									
									
SMB (DO-214AA)									
Unit	A	B	C	D	E	F	G	H	K
mm	3.60 -0.30 +0.35	5.3 -0.2 +0.3	2.10 -0.15 +0.10	4.30 -0.25 +0.30	1.20 -0.45 +0.40	2.20 -0.30 +0.25	0.10 -0.05 +0.10	2.30 $\pm$ 0.35	0.30 -0.15 +0.11

Part numbering system		
P6SMB ↓ Series code	24 ↓ Breakdown voltage marking (see: Characteristics table)	A ↓ Unidirectional: A Bidirectional: CA

Absolute maximum ratings and general electrical characteristics ($T_a = 25^\circ\text{C}$)			
Parameter	Symbol	Value	Unit
Peak pulse power dissipation ^{1) 2)}	P_{PPM}	600	W
Peak forward surge current ³⁾	I_{FSM}	100	A
Maximum instantaneous forward voltage at 50A for unidirectional only ⁴⁾	V_F	3.5/5.0	V
Steady state power dissipation at $T_a=50^\circ\text{C}$	$P_{M(AV)}$	5.0	W
Typical thermal resistance junction to ambient	$R_{\theta JA}$	100	$^\circ\text{C/W}$
Typical thermal resistance junction to lead	$R_{\theta JL}$	20	$^\circ\text{C/W}$
Operating junction temperature and storage temperature range	T_j, T_{stg}	-65 ~ 150	$^\circ\text{C}$
Notes:			
1) Non-repetitive current pulse, derated above $T_a=25^\circ\text{C}$			
2) Mounted on 5mm ² copper pads to each terminal			
3) Peak forward surge current : 8.3ms single half sine-wave superimposed on rated load (JEDEC method)			

Characteristics table (T_a = 25°C)


Part number (UNI)	Part number (BI)	Marking		Reverse stand off voltage	Breakdown voltage @I _T		Test current	Maximum clamping voltage @I _{PP}	Maximum peak pulse current	Maximum reverse leakage @V _R	Agency approval 
					V _{BR}						
		V _R	MIN	MAX	I _T	V _C	I _{PP}	I _R			
		UNI	BI	V	V	V	mA	V	A	μA	
P6SMB6.8A	P6SMB6.8CA	6V8A	6V8C	5.8	6.45	7.14	10	10.5	58.1	1000	X
P6SMB7.5A	P6SMB7.5CA	7V5A	7V5C	6.4	7.13	7.88	10	11.3	54	500	X
P6SMB8.2A	P6SMB8.2CA	8V2A	8V2C	7.02	7.79	8.61	10	12.1	50.4	200	X
P6SMB9.1A	P6SMB9.1CA	9V1A	9V1C	7.78	8.65	9.55	1.0	13.4	45.5	50	X
P6SMB10A	P6SMB10CA	10A	10C	8.55	9.5	10.5	1.0	14.5	42.1	10	X
P6SMB11A	P6SMB11CA	11A	11C	9.4	10.5	11.6	1.0	15.6	39.1	5.0	X
P6SMB12A	P6SMB12CA	12A	12C	10.2	11.4	12.6	1.0	16.7	36.5	5.0	X
P6SMB13A	P6SMB13CA	13A	13C	11.1	12.4	13.7	1.0	18.2	33.5	1.0	X
P6SMB15A	P6SMB15CA	15A	15C	12.8	14.3	15.8	1.0	21.2	28.8	1.0	X
P6SMB16A	P6SMB16CA	16A	16C	13.6	15.2	16.8	1.0	22.5	27.1	1.0	X
P6SMB18A	P6SMB18CA	18A	18C	15.3	17.1	18.9	1.0	25.5	24.2	1.0	X
P6SMB20A	P6SMB20CA	20A	20C	17.1	19.0	21	1.0	27.7	22	1.0	X
P6SMB22A	P6SMB22CA	22A	22C	18.8	20.9	23.1	1.0	30.6	19.9	1.0	X
P6SMB24A	P6SMB24CA	24A	24C	20.5	22.8	25.2	1.0	33.2	18.4	1.0	X
P6SMB27A	P6SMB27CA	27A	27C	23.1	25.7	28.4	1.0	37.5	16.3	1.0	X
P6SMB30A	P6SMB30CA	30A	30C	25.6	28.5	31.5	1.0	41.4	14.7	1.0	X
P6SMB33A	P6SMB33CA	33A	33C	28.2	31.4	34.7	1.0	45.7	13.3	1.0	X
P6SMB36A	P6SMB36CA	36A	36C	30.8	34.2	37.8	1.0	49.9	12.2	1.0	X
P6SMB39A	P6SMB39CA	39A	39C	33.3	37.1	41	1.0	53.9	11.3	1.0	X
P6SMB43A	P6SMB43CA	43A	43C	36.8	40.9	45.2	1.0	59.3	10.3	1.0	X
P6SMB47A	P6SMB47CA	47A	47C	40.2	44.7	49.4	1.0	64.8	9.4	1.0	X
P6SMB51A	P6SMB51CA	51A	51C	43.6	48.5	53.6	1.0	70.1	8.7	1.0	X
P6SMB56A	P6SMB56CA	56A	56C	47.8	53.2	58.8	1.0	77	7.9	1.0	X
P6SMB62A	P6SMB62CA	62A	62C	53	58.9	65.1	1.0	85	7.2	1.0	X
P6SMB68A	P6SMB68CA	68A	68C	58.1	64.6	71.4	1.0	92	6.6	1.0	X
P6SMB75A	P6SMB75CA	75A	75C	64.1	71.3	78.8	1.0	103	5.9	1.0	X
P6SMB82A	P6SMB82CA	82A	82C	70.1	77.9	86.1	1.0	113	5.4	1.0	X
P6SMB91A	P6SMB91CA	91A	91C	77.8	86.5	95.5	1.0	125	4.9	1.0	X
P6SMB100A	P6SMB100CA	100A	100C	85.5	95	105	1.0	137	4.5	1.0	X
P6SMB110A	P6SMB110CA	110A	110C	94	105	116	1.0	152	4.0	1.0	X
P6SMB120A	P6SMB120CA	120A	120C	102	114	126	1.0	165	3.7	1.0	X
P6SMB130A	P6SMB130CA	130A	130C	111	124	137	1.0	179	3.4	1.0	X
P6SMB150A	P6SMB150CA	150A	150C	128	143	158	1.0	207	2.9	1.0	X
P6SMB160A	P6SMB160CA	160A	160C	136	152	168	1.0	219	2.8	1.0	X
P6SMB170A	P6SMB170CA	170A	170C	145	162	179	1.0	234	2.6	1.0	X
P6SMB180A	P6SMB180CA	180A	180C	154	171	189	1.0	246	2.5	1.0	X
P6SMB200A	P6SMB200CA	200A	200C	171	190	210	1.0	274	2.2	1.0	X
P6SMB220A	P6SMB220CA	220A	220C	185	209	231	1.0	328	1.9	1.0	X

Characteristics table ($T_a = 25^\circ\text{C}$)


Part number (UNI)	Part number (BI)	Marking		Reverse stand off voltage	Breakdown voltage @I _T		Test current	Maximum clamping voltage @I _{PP}	Maximum peak pulse current	Maximum reverse leakage @V _R	Agency approval 
					V _{BR}						
				V _R	MIN	MAX	I _T	V _C	I _{PP}	I _R	
		UNI	BI	V	V	V	mA	V	A	μA	
P6SMB250A	P6SMB250CA	250A	250C	214	237	263	1.0	344	1.8	1.0	X
P6SMB300A	P6SMB300CA	300A	300C	256	285	315	1.0	414	1.5	1.0	X
P6SMB350A	P6SMB350CA	350A	350C	300	332	368	1.0	482	1.3	1.0	X
P6SMB400A	P6SMB400CA	400A	400C	342	380	420	1.0	548	1.1	1.0	X
P6SMB440A	P6SMB440CA	440A	440C	376	418	462	1.0	602	1.0	1.0	X
P6SMB480A	P6SMB480CA	480A	480C	408	456	504	1.0	658	0.9	1.0	
P6SMB510A	P6SMB510CA	510A	510C	434	485	535	1.0	698	0.9	1.0	
P6SMB530A	P6SMB530CA	530A	530C	477	503.5	556.5	1.0	725	0.8	1.0	
P6SMB540A	P6SMB540CA	540A	540C	486	513	567	1.0	740	0.8	1.0	
P6SMB550A	P6SMB550CA	550A	550C	495	522.5	577.5	1.0	760	0.8	1.0	

For bidirectional type having V_{RWM} of 10 volts and less, the I_R limit is double.


Peak pulse power rating




Pulse derating curve




Pulse waveform




Typical junction capacitance




Steady state power dissipation derating curve



Maximum non-repetitive peak forward surge current uni-directional only



Suggested soldering pad layout					
					
SMB (DO-214AA)					
Unit	A	B	C	D	E
mm	2.8	2.4	4.6	2.2	7.0

Ordering information				
Part number	Package	Shipping reel quantity	Box dimensions [mm/kg]	Shipping box quantity
P6SMB6.8A(CA) ~ P6SMB550A(CA)	SMB (DO-214AA)	3 000 pcs / 13" reel	365 x 365 x 360 / 14kg	48 000 pcs / box

Disclaimer

Akyga semi reserves the right to make changes without notice to any product specification herein, to make corrections, modifications, enhancements or other changes. Akyga semi or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies. Data sheet specifications and its information contained are intended to provide a product description only. "Typical" parameters which may be included on Akyga semi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. Akyga semi does not assume any liability arising out of the application or use of any product or circuit. Akyga semi products are not designed, intended or authorized for use in medical, life-saving implant or other applications intended for life-sustaining or other related applications where a failure or malfunction of component or circuitry may directly or indirectly cause injury or threaten a life without expressed written approval of Akyga semi. Customers using or selling Akyga semi components for use in such applications do so at their own risk and shall agree to fully indemnify Akyga semi and its subsidiaries harmless against all claims, damages and expenditures.