



series 272

A40 ↓98.6% ↑1.4% Φ: 6500 lm




100 x 100 cm Φ: 6500 lm

Em: 1501 lx
Emax: 1795 lx
Emin: 1137 lx



Φ: 6500 lm E: 0°



Light source

Work equipment

Connected load

Power consumption

Luminous flux

Luminous efficiency¹⁾

Light type/color

Colour temperatur

Color rendering index

Light distribution

Beam angle

Chromaticity tolerance LED

Glare control

Luminance (L65)

UGR class (4H 8H; EN 12464-1)

System of protection/Class

Technology

Operation

Housing

Light source cover

Mains lead

Fastening

Light output

Side part

Maximum ambient temperature

EAN

Weight without/incl. packaging

Dimensions (dimensional drawing)

Packaging dimensions

LED

Without

230 V; AC; 50 Hz; 60 Hz

ca. 80 W

approx. 6.500 lm

approx. 81 lm/W

Cold white

approx. 5.000 K

CRI ≥ 80

Direct; approx. 99 %

100 °

< 4 SDCM

Diffusor

≤ 18.000 cd/m²

≤ 25

IP 67; I

Switchable

External

Borosilicate glass

Borosilicate

Connector; series 272

Pipe clamp (accessory)

D=1436 mm

A with screwed cable gland

40 °C

4013330144418

ca. 6,1 kg

A=1490 mm

ca. 1.700 mm; 90 mm; 90 mm

¹⁾ For luminaires with separate control gear, the luminous efficacy refers to the luminaire head without control g