

SIMATIC S7-1200, DIGITAL OUTPUT SM 1222, 8 DO, RELAY
CHANGEOVER CONTACT



Supply voltage	
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Input current	
from backplane bus 5 V DC, max.	140 mA
Digital outputs	
from load voltage L+, max.	16.7 mA/relay coil
Power loss	
Power loss, typ.	5 W
Digital outputs	
Number of digital outputs	8
in groups of	1
Short-circuit protection	No; to be provided externally
Switching capacity of the outputs	
with resistive load, max.	2 A
on lamp load, max.	30 W with DC, 200 W with AC
Output voltage	

• Rated value (DC)	5 V DC to 30 V DC
• Rated value (AC)	5 V AC to 250 V AC
Output current	
• for signal "1" rated value	2 A
Output delay with resistive load	
• "0" to "1", max.	10 ms
• "1" to "0", max.	10 ms
Total current of the outputs (per group)	
horizontal installation	
— up to 50 °C, max.	2 A; Current per mass
Relay outputs	
• Number of relay outputs	8
• Rated supply voltage of relay coil L+ (DC)	24 V
• Number of operating cycles, max.	mechanically 10 million, at rated load voltage 100 000
Switching capacity of contacts	
— with inductive load, max.	2 A
— on lamp load, max.	30 W with DC, 200 W with AC
— with resistive load, max.	2 A
Cable length	
• shielded, max.	500 m
• unshielded, max.	150 m
Interrupts/diagnostics/status information	
Alarms	
• Diagnostic alarm	Yes
Diagnostics indication LED	
• for status of the outputs	Yes
Potential separation	
Potential separation digital outputs	
• between the channels	Relays
• between the channels, in groups of	1
• between the channels and backplane bus	1500 V AC for 1 minute
Permissible potential difference	
between different circuits	750 V AC for 1 minute
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes

cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
Marine approval	Yes

Ambient conditions

Free fall

- Fall height, max. 0.3 m; five times, in product package

Ambient temperature during operation

- min. -20 °C
- max. 60 °C; Number of simultaneously activated outputs: 4 (no adjacent points) at 60 °C horizontal or 50 °C vertical, 8 at 55 °C horizontal or 45 °C vertical
- horizontal installation, min. -20 °C
- horizontal installation, max. 60 °C
- vertical installation, min. -20 °C
- vertical installation, max. 50 °C
- permissible temperature change 5°C to 55°C, 3°C / minute

Ambient temperature during storage/transportation

- min. -40 °C
- max. 70 °C

Air pressure acc. to IEC 60068-2-13

- Storage/transport, min. 660 hPa
- Storage/transport, max. 1 080 hPa

Relative humidity

- Operation at 25 °C without condensation, max. 95 %

Connection method

required front connector	Yes
--------------------------	-----

Mechanics/material

Enclosure material (front)	
• Plastic	Yes

Dimensions

Width	70 mm
Height	100 mm
Depth	75 mm

Weights

Weight, approx.	310 g
-----------------	-------

last modified: 11/28/2017