

Spindle cable/Single core | PVC | chainflex® CF885.PE

- For flexing applications
- PVC outer jacket
- Flame retardant

Dynamic information

	Bend radius	e-chain® linear	minimum 15 x d
		flexible	minimum 12 x d
		fixed	minimum 8 x d
	Temperature	e-chain® linear	+5 °C to +70 °C
		flexible	-5 °C to +70 °C (following DIN EN 60811-504)
		fixed	-15 °C to +70 °C (following DIN EN 50305)
	v max.	unsupported	3 m/s
	a max.		20 m/s ²
	Travel distance		Unsupported travel distances up to 10 m, Class 1

Cable structure

	Conductor	Conductor consisting of bare copper wires (following DIN EN 60228).
	Core insulation	Mechanically high-quality PVC mixture.
	Core identification	Green-yellow.
	Outer jacket	Low-adhesion PVC mixture, adapted to suit the requirements in e-chains®. Colour: Pastel orange (similar to RAL 2003)

Electrical information

	Nominal voltage	600/1000 V (following DIN VDE 0298-3)
	Testing voltage	4000 V (following DIN EN 50395)

Class 3.1.1.1

Basic requirements	low	1	2	3	4	5	6	7	highest
Travel distance	unsupported	1	2	3	4	5	6	7	≥ 400 m
Oil resistance	none	1	2	3	4	5	6	7	highest
Torsion	none	1	2	3	4	5	6	7	±180°

Properties and approvals

	Flame retardant	According to IEC 60332-1-2, CEI 20-35, FT1, VW-1
	Silicone-free	Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992).
	UL/CSA	Style 10107, 600 V, 80 °C
	EAC	Certificate no. RU C-DE.ME77.B.01561 (TR ZU)
	CTP	Certificate no. C-DE.PB49.B.00450 (Fire safety)
	Lead-free	Following 2011/65/EU (RoHS-II).
	CE	Following 2014/35/EU.

Guaranteed lifetime according to guarantee conditions (Page 22-23)

Double strokes*	1 million	3 million	5 million
Temperature, from/to [°C]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]
+5/+15	17.5	18.5	19.5
+15/+60	15	16	17
+60/+70	17.5	18.5	19.5

* Higher number of double strokes? Online lifetime calculation: www.igus.eu/chainflexlife

Typical mechanical application areas

- For flexing applications
- Without influence of oil
- Preferably indoor applications
- Especially for unsupported travels
- Wood/stone processing, Packaging industry, supply systems, Handling, adjusting equipment

Part No.	Number of cores and conductor nominal cross section [mm ²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF885.PE.25.01	1G2.5	6.5	24	55
CF885.PE.40.01	1G4.0	7.0	39	75
CF885.PE.60.01	1G6.0	8.0	58	97
CF885.PE.100.01	1G10.0	9.5	96	147
CF885.PE.160.01	1G16.0	10.5	154	228
CF885.PE.250.01	1G25.0	12.0	240	328

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.
G = with green-yellow earth core x = without earth core