




SYMBOL DEFINITION			DWG STATUS	MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	17	3		
	LAST NO. USED	17			


DWG STATUS				REVISION HISTORY			AUTH	DR	APVD	APVD
DATE	STG	REV	N/P	CHG	ZONE					
17DE01	R	13	-	-		CLEARED REV COL: ALL PARTS - REVISED TOLERANCE CRIMP WINGS	210778	AFM	EDV	GM
26FE04	R	14	-	-		ALL PARTS - CREATED SOLID MODEL	241069	RAO	EAR	B6
26FE04	R	15	-	-		ALL PARTS - UPDATED MAT'L SPEC	245025	RAO	EAR	B6
180C05	R	16	-	-		REMOVED DIM # 3	272913	EFS	JVM	B6
02AU06	R	17	-	-		ALL PARTS - ADDED 3.3 MAX DIM	283169	TLD	TLD	B6
22JA08	R	18	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES	403618	MAC	MAC	B6
04FE08	R	19	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES	403722	RH	RH	B6
06AU15	R	20	-	-		15304790 MAKE OBSOLETE	429950	PCE	LES	VMR
05MY16	R	21	-	-		12124075, 76 & 12161184 - UPDATED PDM ATTRIBUTES	432949	NRM	LES	LES



VIEW TO X-X



VIEW TO X-X



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

-	-	-	0.254 X 26.97	-	15304790	03	AH	TIN PLATED COPPER ALLOY	1-0.8	2.78-2.62	17	4.3	2.7	2.8	-
-	-	-	0.254 X 26.97	-	12161184	03	AH	TIN PLATED COPPER ALLOY	1-0.8	2.4-2.03	17	4.3	2.7	-	-
-	-	-	0.254 X 26.97	-	12124076	05	AH	TIN PLATED COPPER ALLOY	0.5-0.35	2.2-1.3	21	3.2	2.2	2.1	2.8
-	-	-	0.254 X 26.97	-	12124075	05	AH	TIN PLATED COPPER ALLOY	1-0.8	2.4-2.03	17	4.3	2.7	2.8	2.9
PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SPEC	SIZE (MM²)	CABLE DIA	ID	F ±0.3	G ±0.2	CORE	INSULATION
UNPLATED					PLATED					CABLE					

PROCESS SENSITIVE DIMENSION			
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)	CHART	ID	
FROM 0 TO 12	> 12		
TOLERANCE UNLESS OTHERWISE SPECIFIED	±0.1	±0.2	
ANGULAR TOLERANCE	±2°		

THIRD ANGLE PROJECTION		DO NOT SCALE	
USE MATH DATA		USE MATH DATA	

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE	
WARREN, OH	
COPYRIGHT 1999 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DATE	
DR	
APV01 S. ALVARADO	26.JUN99
APV02 J. VILLAMIL	27.JUN99
APV03 J. VILLAMIL	27.JUN99
APV04	
APV05	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI (0944900)	
MATERIAL SEE CHART	
DRAWING NAME	
TAXI TERM F M/P 150.2 TANG	
DRAWING NUMBER	
12124077	
SIZE A0	SCALE 10:1
FRAME NO 1	SHEET NO 1 OF 2
STG REV R 21	N/P